

Datasheet

Item No. 92.932.3053.0

Male connector with strain relief GST18i3S S1 ZR1 WS

Connector GST18i3, 3 pole, male, screw connection, 250V/16A, color of coding: white, color of housing: white



| | |
|------------|---------------|
| Item No. | 92.932.3053.0 |
| EAN | 4015573721869 |
| order unit | 50 Piece(s) |

Approvals



Technical data

General

| | |
|--|--------------|
| ArticlePrice | udp_no_price |
| Rated current | 20 A |
| Rated voltage | 250 V |
| Rated impulse voltage | 4 kV |
| Pull relief | Yes |
| Pollution degree | 2 |
| Mechanical coding | Yes |
| Interlockable | Yes |
| Color of coding/ contact carrier | White |
| Color of housing inclusive strain relief | White |

Connection Data

| | |
|-----------------------------------|----------------------|
| Cable diameter | 10.5 mm |
| Cable diameter 2 | 6.5 mm |
| Connection cross section solid | 2.5 mm ² |
| Cross section solid 2 | 0.75 mm ² |
| Connection cross section stranded | 2.5 mm ² |
| Cross section stranded 2 | 0.75 mm ² |
| Terminations per pole | 1 |

Model

| | |
|-----------------|------------------|
| Model | Plug |
| Number of poles | 3 |
| Connection type | Screw connection |

| | |
|---------------------------|------|
| Degree of protection (IP) | IP40 |
|---------------------------|------|

Material

| | |
|--|------------|
| Housing material | Polyamide |
| Halogen free | Yes |
| Contact material | CuZn |
| Insulation components continuous temperature | 100 °C |
| Surface finish | Tin-plated |

Dimensions

| | |
|--------|---------|
| Length | 69.4 mm |
| Width | 28.2 mm |
| Height | 12.6 mm |

Drawings