

Datasheet

Item No. 92.954.4053.1

Male connector with strain relief GST18I5S S1 ZR1 SW

Connector GST18i5, 5 pole, male, screw connection, new version, 250/400V, 16A, color of coding: black, color of housing: black



Item No.	92.954.4053.1
EAN	4015573847057
order unit	50 Piece(s)

Approvals



Technical data

General

ArticlePrice	udp_no_price
Rated current	20 A
Rated voltage	250 V
Rated voltage 2	400 V
Rated impulse voltage	4 kV
Pull relief	Yes
Pollution degree	2
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Black
Color of housing inclusive strain relief	Black

Connection Data

Cable diameter	12.5 mm
Cable diameter 2	8 mm
Connection cross section solid	2.5 mm ²
Cross section solid 2	0.75 mm ²
Connection cross section stranded	2.5 mm ²
Cross section stranded 2	0.75 mm ²
Terminations per pole	1

Model

Model	male
Number of poles	5

Connection type	Screw connection
Degree of protection (IP)	IP20

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Tin-plated

Dimensions

Length	76.4 mm
Width	47.75 mm
Height	15 mm

Drawings