

Datasheet

Item No. Z5.531.4025.0

PCB pin header

PCB stripped header, straight, 10 -pole, solder pin: 0,8 mm diameter, colour black, suitable for pluggable terminal block series 8543, pitch: 3,5mm



Item No.	Z5.531.4025.0
EAN	4015573320475
order unit	50 Piece(s)

Approvals



Technical data

General

Modular spacing	3.5 mm
Soldering process	Wave soldering
Number of poles	10
Number of levels	1
Fastening	None
Mating direction towards (circuit) board	90°

Technical data

Rated current	6 A
Overvoltage Category I	690 V
Overvoltage Category II	250 V
Overvoltage Category III	160
Rated impulse voltage	2.5 kV

Technical Data UL/CSA

Voltage UL	300
Current field wiring	10 A
Current factory wiring	10 A
Voltage CSA	300 V
Current CSA	10 A

Other

Type of insulation material	Thermoplastic
Colour	Black
Height	13 mm
Length	35 mm
Depth	2.7 mm
Material contact base	CuZn
Material contact surface	Sn