

COMPONENTS / ACCESSORIES

HORIZONTAL RAILS

Z rail for connector IEC 60 603-2 (F)



With 84 x M2.5 threaded holes.

Material:

Extruded aluminum section


Surface finish:

Clear-chromated

Usable width (HP)	Packs of	Order No.
4	1	3684.597
8	1	3684.598
20	1	3684.599
40	1	3684.965
42	1	3684.600
63	1	3684.601
84	1	3684.602
84	2	3685.271

! Also required:

Assembly screws M2.5 x 6,
packs of 100, order no. 3654.340,
see page 164



Threaded insert (I)



With M2.5 threaded holes on an HP pitch pattern.
For sliding into the horizontal rail. There are two
threaded insert versions, which are distinguished
by their height.

Material:

Sheet steel, zinc-plated

Usable width (HP)	Packs of	Order No.	
		6 x 2 mm	5 x 2 mm
		for horizontal rails	
		Type A, A1, B, B1, B2, C3	Type A2, C5, C6, D4
4	1	3684.603	—
8	1	3684.604	—
12	1	3684.605	—
16	1	3684.606	—
20	1	3684.607	—
21	1	3686.149	—
40	1	3684.966	—
42	1	3684.608	—
63	1	3684.609	—
84	1	3684.610	9901.816

Identification strip (J)



To identify the slots on the subrack, self-adhesive.
The following versions are available:

4 mm wide:

- for front horizontal rails
- for rear horizontal rails

2 mm wide:

- for front horizontal rails (channel on front face)

For horizontal rail	Width mm	Label	Packs of	Order No.
Front	4	1 ... 84	1	3687.575
Rear	4	1 ... 168	1	3687.577
Front	4	84 ... 1	1	3687.574
Front	2	1 ... 84	1	3687.576