

Data sheet

Commercial Art.No.: 05.562.6453.0

Blank module female revos

Modular connector system blind module female



Commercial Art.No.	05.562.6453.0
EAN	4015573747951
Order Unit	10

Technical data

General

Model	Female insert
Inflammability class of insulation material acc. with UL94	V0
Color	Grey
Modular version	Yes
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Connection Data

Connection type	Other
Number of poles	0
Plus switching contacts	0
Number of pole for rated current 2	0
Number of pole for rated current 3	0
Total number of poles (without ground contact)	0
With wire protection	No
Protective contact	No

Model

With housing	No
--------------	----

Contacts

Contact material	Other
Surface	Other

Technical Data DIN EN 61984

Rated impulse voltage	1.5 kV
-----------------------	--------

Classification

ECLASS 11	
ECLASS 8.1	27440205
ETIM 7.0	EC000438
ETIM 6.0	EC000438
ETIM 5.0	EC000438
ETIM 4.0	EC000438
ETIM 3.0	EC000438

Product compliance

ROHS conformity status	Compliant
REACH-SVHC conformity status	Compliant

