

Data sheet

Commercial Art.No.: 25.350.3206.0

PCB pin header 8213 S / 2 G OB THR

PCB pin header, connection method depends on used socket part , 2 poles, with solder pin (2.6mm, tin plated), pitch: 5.08 mm, type of packing: carton, color: black, This product can be soldered by reflow and wave soldering,



Commercial Art.No.	25.350.3206.0
EAN	4015573868762
Order Unit	100

Certificates / Approvals



Technical data

General

Modular spacing	5.08 mm
Soldering process	THR
Packaging	Carton
Number of poles	2
Number of levels	1
Marking	No
Fastening	None

Technical data

Rated current	12 A
Overvoltage Category I	1000 V
Overvoltage Category II	400 V
Overvoltage Category III	250 V

Technical Data UL/CSA

Voltage UL	300 V
Current field wiring	15 A
Current factory wiring	15 A
Voltage CSA	300 V
Current CSA	15 A

Other

Type of insulation material	Thermoplastic
Color	black

Height	12 mm
Length	12.16 mm
Depth	8.4 mm
Material contact base	CuZn
Material contact surface	Sn

Classification

ECLASS 8.1	27440402
ETIM 7.0	EC002637
ETIM 6.0	EC002637
ETIM 5.0	EC002637
ETIM 4.0	EC002637

Product compliance

ROHS conformity status	Compliant
REACH-SVHC conformity status	Compliant

☐ Diese Maße werden bei Abnahme besonders geprüft

☐ Ausschließlich Prüfmaße

Mit / E gekennzeichnete Maße sind nur für interne Zwecke gültig