

# PCB screw terminal series 8142, two part PCB terminal raising cage clamp

## wiecon PCB

pitch 5.00 mm

preliminary data

IEC	200 V 4kV cat.3	1.5 A (Tin)	0.5 - 2.5 mm <sup>2</sup> (Stranded)
	320 V 4kV cat.2		0.5 - 2.5 mm <sup>2</sup> (Solid)
	1000 V 4kV cat.1		
UL	300 V	1.5 A (Tin)	20 - 14 AWG
CSA	300 V	1.5 A (Tin)	20 - 14 AWG
Wire Strip Length			6 mm
Screw Size			M3



Approvals:



**series 8142 Z RF / OB**  
pitch 5.00 mm

Box Qty	L	T	Pole
100	10	5	2
100	15	10	3
50	20	15	4

RF (Tin) pull out force < 4.0 Nm/Pin unmarked      RF (Tin) pull out force < 4.0 Nm/Pin marked

Part Number	Part Number	Part Number	Part Number
25.613.2256.1	25.613.0256.1		
25.613.2356.1	25.613.0356.1		
25.613.2456.1	25.613.0456.1		

Box Qty	G	T	Pole

Part Number	Part Number	Part Number	Part Number

Custom Marking Available  
More poles available on request  
Subject to change without notice