


## Data sheet

Commercial Art.No.: 80.010.0008.0

Relay module WRS-REL-1W-250V5A

WRS-relays, contact Assignment: 1 change-over contact, relay not plugable, with LED, open module housing WEB 1002, dimensions: 80x13 mm (HxB), control voltage: 24V DC, output: 250 V AC/5 A (Note: With jumpers, the negative pole of the control side can be bridged to the neighboring pole), if needed they have to be ordered separately).



Certificates / Approvals



## Technical data

### General

Connection type	Screw connection
Number of change-over contacts	1
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	Yes
Degree of protection (IP)	IP20

### Technical data

Type of excitation	AC/DC
Rated frequency, auxiliary-/control circuit	50 - 60
Min. rated frequency, auxiliary/control current circuit	50 Hz
Max. rated frequency, auxiliary/control current circuit	60 Hz
Min. nominal voltage DC	24 V
Lower nominal voltage DC	20.4 V
Upper nominal voltage DC	26.4 V

### Dimensions

Depth	60 mm
Width	12.5 mm
Height	80 mm

### Classification

ECLASS 11	
ECLASS 8.1	27371601
ETIM 7.0	EC001437
ETIM 6.0	EC001437
ETIM 5.0	EC001437
ETIM 4.0	EC001437

### Product compliance

ROHS conformity status	Compliant/Exempted
------------------------	--------------------

ROHS exceptions	III-6(c)
REACH-SVHC conformity status	Duty-To-Declare
REACH-SVHC substances	Lead
REACH-SVHC CAS numbers	7439-92-1