

## Data sheet

Commercial Art.No.: 98.300.1800.0

Mounting rail TS 35x7,5 PERF 18mm - l:2000mm

Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and dichromated



## Technical data

### General

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Thickness                       | 1 mm                              |
| Length                          | 2000 mm                           |
| Material                        | Steel                             |
| Type                            | DIN rail (top hat rail) 35/7.5 mm |
| Height                          | 7.5 mm                            |
| Surface finish                  | Other                             |
| Type of perforation             | Long-slot                         |
| Drill hole distance centrically | 25 mm                             |

### Accessories

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Type                            | DIN rail (top hat rail) 35/7.5 mm |
| Length                          | 2000 mm                           |
| Height                          | 7.5 mm                            |
| Thickness                       | 1 mm                              |
| Material                        | Steel                             |
| Surface finish                  | Other                             |
| Type of perforation             | Long-slot                         |
| Drill hole distance centrically | 25 mm                             |

### Classification

|            |          |
|------------|----------|
| ECLASS 11  |          |
| ECLASS 8.1 | 27141143 |
| ETIM 7.0   | EC001285 |
| ETIM 6.0   | EC001285 |
| ETIM 5.0   | EC001285 |
| ETIM 4.0   | EC001285 |
| ETIM 3.0   | EC001285 |

### Product compliance

|                              |           |
|------------------------------|-----------|
| ROHS conformity status       | Compliant |
| REACH-SVHC conformity status | Compliant |