

More Info e.g.
Specifications
/ Dimensions

IC149 Series is RoHS compliant

Part Number	IC - Package	IC-Body Size	IC-Dimensions (total)	Adapter Part No.	
IC149-044-*52-B5	QFP44 0.8 pitch	10 x 10	12.20 x 12.20	ICP-044-5	Click here
IC149-044-*49-B5	QFP44 0.8 pitch	14 x 14	17.2 x 17.2	ICP-044-2	
IC149-048-*56-B5	QFP48 0.8 pitch	10 x 10	13.10 x 13.10	-	Click here
IC149-064-*69-B5	QFP64 0.5 pitch	10 x 10	12.0 x 12.0	-	Click here
IC149-064-*75-B5	QFP64 0.5 pitch	10.4 x 10.4	12.0 x 12.0	ICP-064-6	
IC149-064-*08-B5	QFP64 0.8 pitch	14 x 14	17.2 x 17.2	ICP-064-2	
IC149-064-*01-B5	QFP64 1.0 pitch	14 x 20	17.6~20.1x23.6~26.1	-	
IC149-080-*31-B5	QFP80 0.5 pitch	12 x 12	13.6 x 13.6	ICP-080-6	Click here
IC149-080-*30-B5	QFP80 0.5 pitch	12 x 12	14 x 14	ICP-080-6	
IC149-080-*51-B5	QFP80 0.65 pitch	14 x 14	16 x 16	ICP-080-7	
IC149-080-*17-B5	QFP80 0.65 pitch	14 x 14	17.2 x 17.2	ICP-080-4	
IC149-080-*21-B5	QFP80 0.8 pitch	14 x 20	17.2 x 23.2	ICP-080-5	
IC149-080-*12-B5	QFP80 0.8 pitch	14 x 20	18.8 x 24.8	ICP-080-3	
IC149-100-*25-B5+	QFP100 0.5 pitch	14 x 14	16 x 16	ICP-100-5	Click here
IC149-100-*25-B5+	QFP100 0.5 pitch	14 x 14	16 x 16	ICP-100-5	
IC149-100-*28-B5	BQFP100 0.635 pitch	19.13 x 19.13	22.94 x 22.94	ICP-100-6	
IC149-100-*14-B5	QFP100 0.65 pitch	14 x 20	17.2 x 23.2	ICP-100-4-4	
IC149-100-*05-B5	QFP100 0.65 pitch	14 x 20	17.6~20.1x23.6~26.1	-	
IC149-112-*42-B5	QFP112 0.65 pitch	20 x 20	23.2 x 23.2	ICP-112-2	Click here
IC149-120-*43-B5	QFP120 0.4 pitch	14 x 14	16 x 16	ICP-120-2	
IC149-128-*80-B5	QFP128 0.8 pitch	28 x 28	31.2 x 31.2	ICP-128-2	
IC149-132-*15-B5	QFP132 0.635 pitch	22.36 x 22.36	27.43 x 27.43	-	
IC149-144-*45-B5	QFP144 0.5 pitch	20 x 20	22 x 22	ICP-144-1	Click here
IC149-160-*50-B5	QFP160 0.5 pitch	24 x 24	26 x 26	-	Click here
IC149-160-*23-B5	QFP160 0.65 pitch	28 x 28	32 x 32	ICP-160-1	
IC149-176-*66-B5	QFP176 0.5 pitch	24 x 24	26 x 26	-	Click here
IC149-208-*61-B5	QFP208 0.5 pitch	28 x 28	30.6 x 30.6	-	
IC149-240-*67-B5	QFP240 0.5 pitch	32 x 32	34.6 x 34.6	-	

Explanation: * in the ordering code to be replaced by **0** = without positioning pin or **1** = with positioning pin.
+ Also available without SMT metal fixing
B5 = Au-plating.