


Item no.: 862-8633
 Product description: 4-CONDUCTOR DEVICE CONNECTORS 1 SNAP-IN FOOT
 PER POLE 3 POLE N-PE-L1



Produkt kann von Bild abweichen / product may differ

Packing unit 250 pieces

| | |
|----------------------------------|--------------------------------|
| Product group | 9 (Std Chassis Mt Blocks) |
| pole count | 3 |
| Cross section [mm ²] | 0.5 - 4 mm ² |
| Cross section [AWG] | 20 - 12 AWG |
| Connection method | CONTACT CAGE CLAMP® CONNECTION |
| Measured voltage EN | 500 V |
| Measured shock voltage | 6 kV |
| Pollution degree | 3 |
| Current intensity EN | 32 A |
| Weight | 21.134 g |
| Color | white |
| No. of connection Points | 12 |
| No. of potentials | 3 |
| Height | 21.4 mm |
| Height | 0.843 in |
| Width | 36 mm |
| Width | 1.417 in |
| Depth | 35 mm |
| Depth | 1.378 in |
| Strip length from | 10 mm |

Strip length to
Strip length

11 mm
0.41 in



| Item no. | Admission office | Approval no. | Voltage [V] | Current [A] | Cross section [mm ²] |
|----------|------------------|----------------|-------------|-------------|-----------------------------------|
| 862-8633 | CSA | 154112-1505030 | 300/600 | 20/5 | 22-12 |
| 862-8633 | ENEC15 | 143856-01 | 500 | 32 | 0,5-4 |
| 862-8633 | GL | 33242-06HH | 500 | 32 | 4 |
| 862-8633 | LR | 91/20112(E6) | 500 | 32 | 4,0 |
| 862-8633 | LR | 91/20112E4 | 500 | 32 | 4 |
| 862-8633 | UR | E45172 | 300 | 20 | 22-12 |

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected