


Rev	AWO #	Description	Date	Appr
-		RELEASED	4/6/05	
A		CHANGED AMP TO 3A, WAS 1A	5/3/06	
B		REDRAWN	9/20/11	

APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



**SPECIFICATIONS:**

Material: Insulator: Nylon 66, rated UL 94V-0  
 Insulator color: Black  
 Contacts: Phosphor Bronze  
 Plating:  
 G = Gold flash over Nickel underplate overall  
 T = Tin over Copper underplate overall  
 Electrical:  
 Current rating: 3 Amp max  
 Contact resistance: 30 mohms max  
 Insulation resistance: 1,000 Mohms min  
 Dielectric withstanding voltage: 650 VAC for 1 minute  
 Operating temperature: -55°C to +105°C  
 Environmental:  
 Lead free, RoHS compliant.



**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .100 [2.54] MINI SHUNT, HANDLE TOP  
 .531 [13.50] HEIGHT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXXX ± .015
.XXX ± .015	ØXXX ± .010
APPROVALS	DATE
DRAWN SS	4/6/05
CHECKED	
APPROVED	

SIZE	PART NO.	REV.
X	MSBH-X	B
REF: S00076T	SCALE: NTS	SHEET 1 OF 1