



Quick Reference

Search by part #

Check distributor part inventory

Products

Browse Products

-By Device -

-By Product Line-

-Attachment Methods

-Interface Materials -

-Accessories -

Useful Links

[MSDS Safety Sheets](#)

[How to Order?](#)

[Find Sales Rep](#)

[Find Distributor](#)

[Sample Request](#)

[Quote Request](#)

[Catalog Request](#)

[Building a Part #](#)

[Part # Cross Ref](#)

Accessories
Standard Mounting Pads

The following Mounting Pads are for use with T08

<p>7717-157TG</p> <p>(Teflon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 6.35 (0.250)</p> <p>Thickness: 0.25 (0.010)</p> <p>RoHS Compliant</p>	
<p>7717-153DAPG</p> <p>(DAP)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 6.35 (0.250)</p> <p>Thickness: 0.97 (0.038)</p> <p>RoHS Compliant</p>	
<p>7717-153NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 6.35 (0.250)</p> <p>Thickness: 0.97 (0.038)</p> <p>RoHS Compliant</p>	
<p>7717-152DAPG</p> <p>(DAP)</p> <p>Leads: 4-Mar</p> <p>Outside Diameter mm (in): 5.08 (0.200)</p> <p>Thickness: 1.14 (0.045)</p> <p>RoHS Compliant</p>	
<p>7717-152NG</p> <p>(nylon)</p> <p>Leads: 4-Mar</p> <p>Outside Diameter mm (in): 5.08 (0.200)</p> <p>Thickness: 1.14 (0.045)</p> <p>RoHS Compliant</p>	
<p>7717-124NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 5.72 (0.225)</p> <p>Thickness: 0.51 (0.020)</p> <p>RoHS Compliant</p>	
<p>7717-7DAPG</p> <p>(DAP)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 6.35 (0.250)</p> <p>Thickness: 3.18 (0.125)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-7NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 6.35 (0.250)</p> <p>Thickness: 3.18 (0.125)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-89DAPG</p> <p>(DAP)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 6.35 (0.250)</p> <p>Thickness: 2.03 (0.080)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-89NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 6.35 (0.250)</p> <p>Thickness: 2.03 (0.080)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-108DAPG</p> <p>(DAP)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 5.26 (0.203)</p> <p>Thickness: 1.78 (0.070)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-108NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 5.26 (0.203)</p> <p>Thickness: 1.78 (0.070)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-18DAPG</p> <p>(DAP)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 5.08 (0.200)</p> <p>Thickness: 2.54 (0.100)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-18NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 5.08 (0.200)</p> <p>Thickness: 2.54 (0.100)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-16NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 5.08 (0.200)</p> <p>Thickness: 0.51 (0.020)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-16DAPG</p> <p>(DAP)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 5.08 (0.200)</p> <p>Thickness: 0.51 (0.020)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-112DAPG</p> <p>(DAP)</p> <p>Leads: 4-Mar</p> <p>Outside Diameter mm (in): 5.08 (0.200)</p> <p>Thickness: 0.64 (0.025)</p> <p>RoHS Compliant</p>	
<p>7717-220NG</p> <p>(nylon)</p> <p>Leads: 4-Mar</p> <p>Outside Diameter mm (in): 5.84 (0.230)</p> <p>Thickness: 2.03 (0.080)</p> <p>RoHS Compliant</p>	
<p>7717-239NG</p> <p>(nylon)</p> <p>Leads: 4-Mar</p> <p>Outside Diameter mm (in): 6.10 (0.240)</p> <p>Thickness: 457 (0.180)</p> <p>RoHS Compliant</p>	
<p>7717-46NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 5.08 (0.200)</p> <p>Thickness: 1.52 (0.060)</p> <p>RoHS Compliant</p>	
<p>7717-46DAPG</p> <p>(DAP)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 5.08 (0.200)</p> <p>Thickness: 1.52 (0.060)</p> <p>RoHS Compliant</p>	