



NOTES (UNLESS OTHERWISE SPECIFIED):

1. SWITCH CHARACTERISTICS
 - REST POSITION .350 MAX.
 - PRE-TRAVEL .030 TO .050
 - OPERATING POSITION .265 TO .305
 - OVER TRAVEL .100 MIN.
 - MOVEMENT DIFF. .015 MAX.
 - OPERATING FORCE grams 250 TO 425.
 - RELEASE FORCE grams 125 MIN.
 - *ALL CHARACTERISTICS MEASURED AT BUTTON
2. ELECTRICAL RATING
 - 15A, 125/250VAC; 3/4HP, 125VAC
 - 1-1/2HP, 250VAC
 - 2A, 48VDC
3. TERMINALS
 - COMMON & N.O. TERMINALS ARE
 - .250 WIDTH x .032 THICKNESS.
4. UL RECOGNIZED AND CSA CERTIFIED
5. TEMPERATURE RATING: -40°C TO $+105^\circ\text{C}$

B	17687	03-Sep-08	NV	ED
REV	ECO NO.	DATE	PREP	APVD

DWN: RPM
 APVD: G.TENAZZO
 DATE: 21-Mar-72
 THIRD ANGLE PROJECTION

THE CONFIDENTIAL AND PROPRIETARY INFORMATION CONTAINED IN THIS DOCUMENT IS OWNED BY CHERRY ELECTRICAL PRODUCTS, A DIVISION OF THE CHERRY CORPORATION WHO MUST GIVE WRITTEN PERMISSION BEFORE THE DOCUMENT OR INFORMATION CAN BE COPIED, DISCLOSED OR USED IN ANY WAY.

TOLEANCE UNLESS SPECIFIED

DWG UNITS	X .XX	X .XXX	ANGLES
INCHES	± 0.02	± 0.015	± 5.0
PRODUCT / CSR	N/A		

CHERRY 17200 BETH AVE. PLEASANT PRAIRIE, WI 53158
 ELECTRICAL PRODUCTS

SPECIFICATION DRAWING

ITEM NO. 0E1351C0

SCALE: 2:1 SH 1 OF 1

ORIGINAL ON PROVE