



Solid Locking Plug - Compatible Hole Diameter - 14.3 mm | 0.562 in ; Compatible Panel Thickness Range - 3.2 mm | 0.125 in

This domed blanking plug is made of black Nylon and is heat stabilised to UL94 -V2 to fit panel thickness of 3.2 mm. Easy to push into holes in the panel to blank and protect from sharp edges. The profile is designed with an open vent to help ventilation.



Item code: **62MP0562**

● 306000 In stock

Quantity	Unit price
1000 - 4999	\$0.0554
5000 - 9999	\$0.0528
10000 - 24999	\$0.0505
25000 - 49999	\$0.0475
50000+	\$0.0418

Total price: **\$55.40**
1000 x
\$0.0554

Quantity

Standard pack: 1000
Order in multiple of 100

Add to cart

Add item to list

Order sample:

Add sample +

[Request a quote](#)



Specifications

Compatible Hole Diameter	0.562 in
Maximum Compatible Panel Thickness	0.125 in
Minimum Compatible Panel Thickness	0.125 in
Overall Diameter	0.656 in
Overall Height	0.406 in
Color	Black
Finish	Matte
Fitting Style	Push-Fit
Full Material	Heat-Stabilized Nylon 6/6
Head Style	Dome
Material	Nylon
Material Flammability Standard	UL94 V-2

Legislation & Compliance

Can't find what you're looking for? Tell us what you are looking for...

Send us your inquiry and we'll get back to you in 24 hours.

[Contact us](#)

Recommended Products

