

### CHARACTERISTICS

Weight: 0,725 Kg / 1,6 Lb  
 Housing in ZAMAK  
 Impeller in plastic UL 94 V-0  
 L-10 life expectancy at 40°C: 80.000 hours  
 Operating temperature range: -10 / +55 °C  
 Storage temperature: -40 / +70°C  
 Connection: Terminals  
 Impedance Protected



### OPTIONS

- Speed sensor
- Other IP levels
- Flying leads connection
- Salt spray protection
- Shocks and vibrations protection
- Marine application
- Wide temperature range
- Other voltages
- Dual voltage 115-230V

Part Number	Voltage V	Frequency Hz	Nb Phases	Airflow		Pressure		Nominal speed RPM	Noise level LP dBA	Nominal current mA	Starting current mA	power W	Capacitor µF
				l/s	CFM	mm H. o	inch H. o						
125XL0282010	115	50	1	25,0	53,00	2,2	0,09	1600	30	135	145	12	
82	115	60	1	27,0	57,24	2,4	0,09	1750	32	115	125	10	
81	220	50	1	25,0	53,00	2,2	0,09	1600	30	75	90	12	
81	220	60	1	27,0	57,24	2,4	0,09	1750	32	65	75	10	
125LG0282010	115	50	1	35,0	74,20	5	0,20	2200	38	200	260	16	
82	115	60	1	40,0	84,80	5,5	0,22	2500	40,5	160	220	13	
81	220	50	1	35,0	74,20	5	0,20	2200	38	110	140	18	
81	220	60	1	40,0	84,80	5,5	0,22	2500	40,5	90	120	15	
125XR0282090	115	50	1	44,0	93,28	9,5	0,37	2800	44	200	310	16	
82	115	60	1	53,0	112,36	10,5	0,41	3200	48	180	260	15	
81	220	50	1	44,0	93,28	9,5	0,37	2800	44	125	170	18	
81	220	60	1	53,0	112,36	10,5	0,41	3200	48	105	150	15	

