

Terminal strips for printed circuit boards


type 8191

12 AWG


spacing 10 mm

UL Ratings:

12-30 AWG	30A(factory)
12-22 AWG	20A(field)
600V	



clamp direction parallel to PC board




clamp direction vertical to PC board

See accessories page 171


Wire strip length: 6.5mm

G	T	Poles	part no. marked			
			with insulating plate with fixing bolts	with insulating plate without fixing bolts	without insulating plate	with insulating plate horizontal
15.85	10	2	25.168.6253.0	25.168.2253.0	25.168.0253.0	25.168.4253.0
25.85	20	3	25.168.6353.0	25.168.2353.0	25.168.0353.0	25.168.4353.0
35.85	30	4		25.168.2453.0	25.168.0453.0	25.168.4453.0
45.85	40	5		25.168.2553.0	25.168.0553.0	25.168.4553.0
55.85	50	6		25.168.2653.0	25.168.0653.0	25.168.4653.0
65.85	60	7		25.168.2753.0	25.168.0753.0	25.168.4753.0
75.85	70	6		25.168.2853.0	25.168.0853.0	25.168.4853.0
85.85	80	9		25.168.2953.0	25.168.0953.0	25.168.4953.0
95.85	90	10		25.168.3053.0	25.168.1053.0	25.168.5053.0
105.85	100	11		25.168.3153.0	25.168.1153.0	25.168.5153.0
115.85	110	12		25.168.3253.0	25.168.1253.0	25.168.5253.0


G	T	Poles	part no. unmarked			
15.85	10	2	25.169.6253.0	25.169.2253.0	25.169.0253.0	25.169.4253.0
25.85	20	3	25.169.6353.0	25.169.2353.0	25.169.0353.0	25.169.4353.0
35.85	30	4		25.169.2453.0	25.169.0453.0	25.169.4453.0
45.85	40	5		25.169.2553.0	25.169.0553.0	25.169.4553.0
55.85	50	6		25.169.2653.0	25.169.0653.0	25.169.4653.0
65.85	60	7		25.169.2753.0	25.169.0753.0	25.169.4753.0
75.85	70	6		25.169.2853.0	25.169.0853.0	25.169.4853.0
85.85	80	9		25.169.2953.0	25.169.0953.0	25.169.4953.0
95.85	90	10		25.169.3053.0	25.169.1053.0	25.169.5053.0
105.85	100	11		25.169.3153.0	25.169.1153.0	25.169.5153.0
115.85	110	12		25.169.3253.0	25.169.1253.0	25.169.5253.0




without insulating plate



with insulating plate without fixing bolts



with insulating plate with fixing bolts



with insulating plate horizontal

bore hole plan for version with fixing bolts

