

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
20 X 20 X 6	AD2005DX-K70	HYPRO	5	0.06	0.30	7000	0.4	0.022	12.0	4	0	CE	600	12.28
20 X 20 X 6	AD2005LX-K70	HYPRO	5	0.10	0.50	10500	0.6	0.066	19.5	4	0	TUV,CE	600	12.28
20 X 20 X 6	AD2005MX-K70	HYPRO	5	0.15	0.75	14000	0.7	0.103	26.9	4	0	CE	600	12.28
20 X 20 X 6	AD2005MX-K73	HYPRO	5	0.12	0.60	14000	0.7	0.130	26.0	4	3	CE	600	12.28
20 X 20 X 6	AD2005DB-K70(S)	1B,1S	5	0.04	0.20	7000	0.4	0.022	12.0	4	0	CE	600	12.28
20 X 20 X 6	AD2005LB-K70(S)	1B,1S	5	0.05	0.25	10500	0.6	0.066	19.5	4	0	TUV,CE	600	12.28
20 X 20 X 6	AD2005MB-K70(S)	1B,1S	5	0.13	0.65	14000	0.7	0.103	26.9	4	0	CE	600	12.28
20 X 20 X 6	AD2012LX-K70	HYPRO	12	0.06	0.72	10500	0.6	0.066	19.5	4	0	CE	600	12.28
20 X 20 X 6	AD2012MX-K70	HYPRO	12	0.07	0.84	14000	0.7	0.103	26.9	4	0	CE	600	12.28
20 X 20 X 6	AD2012LB-K70(S)	1B,1S	12	0.06	0.72	10500	0.6	0.066	19.5	4	0	CE	600	12.28
20 X 20 X 6	AD2012MB-K70(S)	1B,1S	12	0.07	0.84	14000	0.7	0.103	26.9	4	0	CE	600	12.28
20 X 20 X 10	AD2005MX-G70	HYPRO	5	0.14	0.70	11500	0.8	0.072	26.0	6	0	UL,CUL,CE	900	17.60
20 X 20 X 10	AD2005MX-G73	HYPRO	5	0.11	0.55	10000	0.8	0.072	26.0	6	3	CE	900	17.60
20 X 20 X 10	AD2005LB-G70	Bor1B1S	5	0.06	0.30	9000	0.6	0.055	26.0	6	0	UL,CUL,CE	900	17.60
20 X 20 X 10	AD2005LB-G73	BALL	5	0.08	0.40	8000	0.4	0.039	11.0	6	3	CE	900	17.60
20 X 20 X 10	AD2005MB-G70	Bor1B1S	5	0.07	0.35	11500	0.8	0.072	20.0	6	0	UL,CUL,TUV,CE	900	17.60
20 X 20 X 10	AD2005MB-G73	Bor1B1S	5	0.08	0.40	10000	0.8	0.072	26.0	6	3	CE	900	17.60
20 X 20 X 10	AD2012LX-G70	HYPRO	12	0.06	0.72	9000	0.6	0.055	20.0	6	0	UL,CUL,CE	900	17.60
20 X 20 X 10	AD2012LB-G70	BALL	12	0.07	0.84	9000	0.6	0.055	20.0	6	0	CE	900	17.60
20 X 20 X 10	AD2012LM-G70	BALL	12	0.06	0.72	11500	0.8	0.072	26.0	6	0	CE	900	17.60
25 X 25 X 6	AD0205LX-K50	HYPRO	5	0.08	0.40	9000	1.8	0.100	20.5	5	0	TUV,CE	600	13.60
25 X 25 X 6	AD0205LX-K53	HYPRO	5	0.06	0.30	9000	1.8	0.100	20.5	5	3	CE	600	13.60
25 X 25 X 6	AD0205MX-K50	HYPRO	5	0.13	0.65	12000	2.4	0.185	26.0	5	0	CE	600	13.60
25 X 25 X 6	AD0205MX-K53	HYPRO	5	0.12	0.60	12000	2.4	0.185	26.0	5	3	CE	600	13.60
25 X 25 X 6	AD0205LB-K50(S)	1B,1S	5	0.05	0.25	9000	1.8	0.100	20.5	5	0	TUV,CE	600	13.60
25 X 25 X 6	AD0205LB-K53(S)	1B,1S	5	0.05	0.25	9000	1.8	0.100	20.5	5	3	CE	600	13.60
25 X 25 X 6	AD0205MB-K50(S)	1B,1S	5	0.09	0.45	12000	2.4	0.185	26.0	5	0	CE	600	13.60
25 X 25 X 6	AD0205MB-K53(S)	1B,1S	5	0.07	0.35	12000	2.4	0.185	26.0	5	3	UL,CUL,TUV,CE	600	13.60
25 X 25 X 6	AD0205HB-K50(S)	1B,1S	5	0.09	0.45	12000	2.4	0.185	26.0	5	0	CE	600	13.60
25 X 25 X 6	AD0212LX-K50	HYPRO	12	0.06	0.72	9000	1.8	0.100	20.5	5	0	CE	600	13.60
25 X 25 X 6	AD0212MX-K50	HYPRO	12	0.09	1.08	12000	2.4	0.185	26.0	5	0	CE	600	13.60
25 X 25 X 6	AD0212LB-K50(S)	BALL	12	0.06	0.72	9000	1.8	0.100	20.5	5	0	CE	600	13.60
25 X 25 X 6	AD0212MB-K50(S)	BALL	12	0.07	0.84	12000	2.4	0.185	26.0	5	0	CE	600	13.60
25 X 25 X 10	AD0205LX-G50	HYPRO	5	0.10	0.50	8000	1.8	0.116	15.6	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205LX-G50(D)	HYPRO	5	0.08	0.40	4500	1.0	0.034	2.4	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205LX-G53GL	HYPRO	5	0.08	0.40	8000	1.8	0.116	15.6	8	3	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205MX-G50GL	HYPRO	5	0.12	0.60	10000	2.3	0.173	23.1	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205MX-G53GL	HYPRO	5	0.12	0.60	10000	2.3	0.173	23.1	8	3	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205HX-G50	HYPRO	5	0.18	0.90	12000	2.8	0.236	28.0	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205LB-G50GL	BALL	5	0.10	0.50	8000	1.8	0.116	15.6	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0205LB-G50(D)	BALL	5	0.07	0.35	6500	1.4	0.064	12.0	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0205LB-G53GL	BALL	5	0.06	0.30	8000	1.8	0.116	15.6	8	3	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205MB-G50GL	BALL	5	0.12	0.60	10000	2.3	0.173	23.1	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0205MB-G53	BALL	5	0.07	0.35	10000	2.3	0.173	23.1	8	3	TUV,CE	600	

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
25 X 25 X 10	AD0205HB-G50GL	BALL	5	0.14	0.70	12000	2.8	0.236	28.0	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0205HB-G53	BALL	5	0.12	0.60	12000	2.8	0.236	28.0	8	3	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0212LX-G50	HYPRO	12	0.07	0.84	8000	1.8	0.116	15.6	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0212MX-G50GL	HYPRO	12	0.08	0.96	10000	2.3	0.173	23.1	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0212HX-G50GL	HYPRO	12	0.09	1.08	12000	2.8	0.236	28.0	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0212LB-G50	BALL	12	0.07	0.84	8000	1.8	0.116	15.6	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0212MB-G50	BALL	12	0.08	0.96	10000	2.3	0.173	23.1	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0212HB-G50	BALL	12	0.09	1.08	12000	2.8	0.236	28.0	8	0	UL,CUL,CE	600	
25 X 25 X 15	AD0205LX-D50	HYPRO	5	0.08	0.40	5000	1.2	0.040	7.2	8	0	CE		
25 X 25 X 15	AD0205LB-D50	BALL	5	0.06	0.30	5000	1.2	0.040	7.2	8	0	CE		
25 X 25 X 15	AD0205MB-D50	BALL	5	0.09	0.45	6000	1.4	0.054	10.0	8	0	CE		
25 X 25 X 15	AD0205HB-D50	BALL	5	0.13	0.65	8000	1.9	0.114	19.2	8	0	CE		
25 X 25 X 15	AD0205HB-D53	BALL	5	0.13	0.65	8000	1.9	0.114	19.2	8	3	UL,CUL,TUV,CE		
25 X 25 X 15	AD0205HB-D53(A)	BALL	5	0.13	0.65	7500	1.8	0.091	16.7	8	3	UL,CUL,TUV,CE		
30 X 30 X 6	AD0305LX-K70	HYPRO	5	0.09	0.45	7500	2.5	0.082	20.0	6	0	UL,CUL,TUV,CE	400	12.30
30 X 30 X 6	AD0305LX-K73	HYPRO	5	0.07	0.35	7500	2.5	0.082	20.0	6	3	CE	400	12.30
30 X 30 X 6	AD0305MX-K70	HYPRO	5	0.12	0.60	9000	3.3	0.138	27.9	6	0	CE	400	12.30
30 X 30 X 6	AD0305MX-K73	HYPRO	5	0.10	0.50	8000	8.3	0.196	34.7	11	3	CE	400	12.30
30 X 30 X 6	AD0305HX-K70	HYPRO	5	0.18	0.90	10500	3.6	0.164	32.1	6	0	CE	400	12.30
30 X 30 X 6	AD0305HX-K73	HYPRO	5	0.11	0.55	10500	3.6	0.164	32.1	6	3	CE	400	12.30
30 X 30 X 6	AD0305LB-K70(S)	1B,1S	5	0.06	0.30	7500	2.5	0.082	20.0	6	0	UL,CUL,TUV,CE	400	12.30
30 X 30 X 6	AD0305LB-K73(S)	1B,1S	5	0.05	0.25	7500	2.5	0.082	20.0	6	3	CE	400	12.30
30 X 30 X 6	AD0305MB-K70(S)	BALL	5	0.08	0.40	9000	3.3	0.138	27.9	6	0	CE	400	12.30
30 X 30 X 6	AD0305MB-K73(S)	1B,1S	5	0.06	0.30	9000	3.3	0.138	27.9	6	3	CE	400	12.30
30 X 30 X 6	AD0305MB-K73(Y)	1B,1S	5	0.08	0.40	9000	7.2	0.120	34.0	6	3	CE	400	12.30
30 X 30 X 6	AD0305HB-K73(S)	1B,1S	5	0.07	0.35	10500	3.6	0.164	32.1	6	3	CE	400	12.30
30 X 30 X 6	AD0312LX-K70	HYPRO	12	0.06	0.72	7500	2.5	0.082	20.0	6	0	UL,CUL,TUV,CE	400	12.30
30 X 30 X 6	AD0312MX-K70	HYPRO	12	0.10	1.20	9000	3.3	0.138	27.9	6	0	CE	400	12.30
30 X 30 X 6	AD0312HX-K70	HYPRO	12	0.08	0.96	10500	3.6	0.164	32.1	6	0	CE	400	12.30
30 X 30 X 6	AD0312LB-K70(S)	BALL	12	0.06	0.72	7500	2.5	0.082	20.0	6	0	CE	400	12.30
30 X 30 X 6	AD0312MB-K70(S)	BALL	12	0.06	0.72	9000	3.3	0.138	27.9	6	0	UL,CUL,TUV,CE	400	12.30
30 X 30 X 6	AD0312HB-K70(S)	BALL	12	0.09	1.08	10500	3.6	0.164	32.1	6	0	CE	400	12.30
30 X 30 X 10	AD0305DX-G50	HYPRO	5	0.09	0.45	5500	1.8	0.080	17.0	8	0	UL,CUL,CE	400	14.00
30 X 30 X 10	AD0305LX-G50	HYPRO	5	0.12	0.60	8000	3.0	0.115	20.2	8	0	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0305LX-G53	HYPRO	5	0.09	0.45	8000	3.0	0.115	20.2	8	3	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0305MX-G53	HYPRO	5	0.11	0.55	9000	4.1	0.148	27.9	8	3	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0305HX-G50	HYPRO	5	0.17	0.85	10500	4.2	0.210	30.7	8	0	CE	400	14.00
30 X 30 X 10	AD0305DB-G50	BALL	5	0.06	0.30	5500	1.8	0.080	17.0	8	0	UL,CUL,CE	400	14.00
30 X 30 X 10	AD0305LB-G50	BALL	5	0.12	0.60	8000	3.0	0.115	20.2	8	0	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0305LB-G53	BALL	5	0.08	0.40	8000	3.0	0.115	20.2	8	3	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0305MB-G50	Bor1B1S	5	0.13	0.65	9000	4.1	0.148	27.9	8	0	UL,CUL,CE	400	14.00
30 X 30 X 10	AD0305MB-G53	Bor1B1S	5	0.11	0.55	9000	4.1	0.148	27.9	8	3	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0305DX-G50	HYPRO	5	0.06	0.72	6000	2.5	0.068	16.0	8	0	CE	400	14.00

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
30 X 30 X 10	AD0312LX-G50	HYPRO	12	0.07	0.84	8000	3.0	0.115	20.2	8	0	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0312MX-G50	HYPRO	12	0.12	1.44	9000	4.1	0.148	27.9	8	0	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0312DB-G50	Bor1B1S	12	0.05	0.60	6000	2.5	0.068	16.0	8	0	UL,CUL,CE	400	14.00
30 X 30 X 10	AD0312LB-G50	BALL	12	0.06	0.72	8000	3.0	0.115	20.2	8	0	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0312MB-G50	Bor1B1S	12	0.12	1.44	9000	4.1	0.148	27.9	8	0	UL,CUL,CE	400	14.00
30 X 30 X 10	AD0312HB-G50	Bor1B1S	12	0.11	1.32	10500	4.2	0.210	30.7	8	0	CE	400	14.00
30 X 30 X 15	AD0305LB-D50	BALL	5	0.07	0.35	4500	2.2	0.045	10.0	10	0	CE		
30 X 30 X 15	AD0305MB-D50	BALL	5	0.08	0.40	5500	2.6	0.074	16.0	10	0	CE		
30 X 30 X 15	AD0305MB-D50(S)	1B,1S	5	0.10	0.50	5500	2.6	0.074	16.0	10	0	CE		
30 X 30 X 15	AD0305MB-D53	BALL	5	0.06	0.30	5500	2.6	0.074	16.0	10	3	UL,CUL,TUV,CE		
30 X 30 X 15	AD0305HB-D50	Bor1B1S	5	0.13	0.65	7000	3.7	0.110	22.5	10	0	CE		
30 X 30 X 15	AD0305HB-D53	BALL	5	0.10	0.50	7000	3.7	0.110	22.5	10	3	UL,CUL,TUV,CE		
35 X 35 X 6	AD3505LX-K70	HYPRO	5	0.10	0.50	6500	3.5	0.063	19.0	7	0	TUV,CE	400	13.00
35 X 35 X 6	AD3505LX-K73	HYPRO	5	0.08	0.40	6500	3.5	0.063	19.0	7	3	CE	400	13.00
35 X 35 X 6	AD3505MX-K70	HYPRO	5	0.14	0.70	8000	4.7	0.111	28.0	7	0	CE	400	13.00
35 X 35 X 6	AD3505MX-KBO	HYPRO	5	0.14	0.70	7000	3.6	0.097	29.0	4	0	CE	400	13.00
35 X 35 X 6	AD3505LB-K70(S)	1B,1S	5	0.06	0.30	6500	3.5	0.063	19.0	7	0	TUV,CE	400	13.00
35 X 35 X 6	AD3505MB-K70(S)	1B,1S	5	0.10	0.50	8000	4.7	0.111	28.0	7	0	CE	400	13.00
35 X 35 X 6	AD3505MB-K73(S)	1B,1S	5	0.08	0.40	8000	4.7	0.111	28.0	7	3	CE	400	13.00
35 X 35 X 6	AD3505HB-K70(S)	1B,1S	5	0.13	0.65	9500	4.9	0.150	35.0	7	0	CE	400	13.00
35 X 35 X 6	AD3505HB-K73(S)	1B,1S	5	0.09	0.45	9500	4.9	0.150	35.0	7	3	CE	400	13.00
35 X 35 X 6	AD3512LX-K70	HYPRO	12	0.06	0.72	6500	3.5	0.063	19.0	7	0	TUV,CE	400	13.00
35 X 35 X 6	AD3512MX-K70	HYPRO	12	0.08	0.96	8000	4.7	0.111	28.0	7	0	CE	400	13.00
35 X 35 X 6	AD3512HX-K70	HYPRO	12	0.10	1.20	9500	4.9	0.150	35.0	7	0	CE	400	13.00
35 X 35 X 6	AD3512LB-K70(S)	BALL	12	0.05	0.60	6500	3.5	0.063	19.0	7	0	TUV,CE	400	13.00
35 X 35 X 6	AD3512MB-K70(S)	BALL	12	0.06	0.72	8000	4.7	0.111	28.0	7	0	TUV,CE	400	13.00
35 X 35 X 6	AD3512HB-K70	BALL	12	0.08	0.96	9500	4.9	0.150	35.0	7	0	CE	400	13.00
35 X 35 X 10	AD3505LX-G53	HYPRO	5	0.09	0.45	7000	5.1	0.100	27.5	9	3	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505MX-G50	HYPRO	5	0.17	0.85	8000	6.0	0.131	30.0	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505MX-G53	HYPRO	5	0.13	0.65	8000	6.0	0.138	30.0	9	3	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505HX-G53	HYPRO	5	0.17	0.85	9500	7.1	0.174	37.6	9	3	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505LB-G50	BALL	5	0.12	0.60	7000	5.1	0.100	27.5	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505MB-G50	BALL	5	0.13	0.65	8000	6.0	0.131	30.0	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505MB-G53	BALL	5	0.13	0.65	8000	6.2	0.160	27.0	9	3	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505MB-G53(S)	1B,1S	5	0.13	0.65	8000	6.0	0.138	30.0	9	3	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512LX-G50	HYPRO	12	0.08	0.96	7000	5.1	0.100	27.5	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512MX-G50	HYPRO	12	0.09	1.08	8000	6.0	0.138	30.0	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512HX-G50	HYPRO	12	0.11	1.32	9500	7.1	0.174	37.6	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512LB-G50	BALL	12	0.08	0.96	7000	5.1	0.100	27.5	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512MB-G50	BALL	12	0.09	1.08	8000	6.0	0.138	30.0	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512HB-G50	BALL	12	0.11	1.32	9500	7.1	0.174	37.6	9	0	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405LX-K90	HYPRO	5	0.05	0.25	4500	4.2	0.044	19.5	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405LX-KCO	HYPRO	5	0.11	0.55	4500	3.6	0.061	22.4	9	0	UL,CUL,TUV,CE	400	13.20

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 6	AD0405LX-KC3	HYPRO	5	0.08	0.40	4500	4.6	0.068	27.1	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MX-K90	HYPRO	5	0.09	0.45	5500	5.2	0.064	23.8	9	0,6	UL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MX-KC0	HYPRO	5	0.20	1.00	5500	4.6	0.093	28.6	9	0,3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MX-KC3(Y)	HYPRO	5	0.11	0.55	5500	4.6	0.093	28.6	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HX-K90	HYPRO	5	0.12	0.60	6300	6.0	0.079	27.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HX-KC0	HYPRO	5	0.23	1.15	6000	5.0	0.110	31.2	9	0	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HX-KC3	HYPRO	5	0.13	0.65	6000	5.0	0.110	31.2	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405LB-K90(S)	1B,1S	5	0.05	0.25	4800	4.5	0.051	19.9	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MB-K90(S)	1B,1S	5	0.09	0.45	5800	5.5	0.067	25.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MB-KC3	BALL	5	0.11	0.55	5800	4.9	0.102	30.0	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HB-K90(S)	1B,1S	5	0.12	0.60	6600	6.0	0.090	30.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MS-K90	S	5	0.09	0.45	5500	5.2	0.064	23.8	9	0	CE	400	13.20
40 X 40 X 6	AD0412LX-K90	HYPRO	12	0.06	0.72	4500	4.4	0.049	20.9	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412MX-K90	HYPRO	12	0.06	0.72	5500	5.2	0.064	23.8	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412HX-K90	HYPRO	12	0.08	0.96	6300	5.9	0.079	27.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412LB-K90(S)	1B,1S	12	0.06	0.72	4800	4.7	0.049	21.6	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412MB-K90(S)	1B,1S	12	0.06	0.72	5800	5.5	0.067	25.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412HB-K90(S)	1B,1S	12	0.08	0.96	6600	6.0	0.090	30.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 8	AD0405LX-J90	HYPRO	5	0.12	0.60	4100	5.1	0.058	20.0	5	0	CE		
40 X 40 X 8	AD0405MX-J90	HYPRO	5	0.16	0.80	5500	6.3	0.094	28.7	5	0	CE		
40 X 40 X 8	AD0405MX-J93	HYPRO	5	0.15	0.75	5500	6.8	0.098	29.0	5	3	CE		
40 X 40 X 8	AD0405HX-J91	HYPRO	5	0.23	1.15	6000	7.5	0.110	31.0	5	1,3	CE		
40 X 40 X 8	AD0405MB-J90	BALL	5	0.20	1.00	5000	6.1	0.089	26.0	5	0	CE		
40 X 40 X 8	AD0412MX-J90	HYPRO	12	0.13	1.56	5000	6.1	0.089	26.0	5	0	CE		
40 X 40 X 9	AD0405HX-RA3	HYPRO	5	0.25	1.25	6000	3.1	0.334	40.3	5	3	CE		
40 X 40 X 10	AD0405DX-G70	HYPRO	5	0.07	0.35	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0405LX-G70	HYPRO	5	0.08	0.40	4200	4.7	0.060	14.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405LX-G76	HYPRO	5	0.08	0.40	4200	4.7	0.060	14.0	24	6	UL,CUL,CE	700	
40 X 40 X 10	AD0405MX-G70	HYPRO	5	0.11	0.55	4800	5.7	0.780	19.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MX-G7	HYPRO	5	0.11	0.55	4800	5.7	0.078	20.0	24	6	UL,CUL,CE	700	
40 X 40 X 10	AD0405HX-G70	HYPRO	5	0.19	0.95	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405DB-G70	BALL	5	0.07	0.35	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0405LB-G70	BALL	5	0.08	0.40	4600	5.0	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MB-G70	BALL	5	0.11	0.55	4800	5.7	0.078	20.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MB-G72	BALL	5	0.15	0.75	4800	5.7	0.078	20.0	24	2	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MB-G73	BALL	5	0.15	0.75	4800	5.7	0.078	20.0	24	3	CE	700	
40 X 40 X 10	AD0405MB-G76	BALL	5	0.11	0.55	5000	6.0	0.080	20.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405HB-G70	BALL	5	0.19	0.95	6000	6.8	0.100	25.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405HB-G72	BALL	5	0.25	1.25	6000	6.7	0.100	25.0	24	2	CE	700	
40 X 40 X 10	AD0405HB-G76	BALL	5	0.19	0.95	6000	6.8	0.100	25.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405LS-G70	S	5	0.08	0.40	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MS-G70	S	5	0.11	0.55	4800	5.7	0.078	20.0	24	0,2,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405HS-G70	S	5	0.19	0.95	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 10	AD0405HS-G7B	S	5	0.15	0.75	6000	6.7	0.100	25.0	24	0	CE	700	
40 X 40 X 10	AD0409HS-G70	S	9	0.13	1.17	6000	6.8	0.100	25.0	24	0	UL,CE	700	
40 X 40 X 10	AD0409LS-G70	S	9	0.08	0.72	4200	4.7	0.060	14.0	24	0	CE	700	
40 X 40 X 10	AD0409MS-G70	S	9	0.10	0.90	4800	5.6	0.080	19.0	24	0	CE	700	
40 X 40 X 10	AD0409US-G70	S	9	0.15	1.35	7000	7.7	0.068	29.7	24	0	CE	700	
40 X 40 X 10	AD0412DX-G70	HYPRO	12	0.07	0.84	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0412LX-G70	HYPRO	12	0.07	0.84	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MX-G70	HYPRO	12	0.08	0.96	4800	5.7	0.078	19.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HX-G70	HYPRO	12	0.10	1.20	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HX-G71	HYPRO	12	0.10	1.20	6000	6.7	0.100	25.0	24	1	CE	700	
40 X 40 X 10	AD0412DB-G70	BALL	12	0.07	0.84	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0412LB-G70	BALL	12	0.07	0.84	4600	5.0	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MB-G70	BALL	12	0.08	0.96	5000	5.9	0.080	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MB-G72	BALL	12	0.09	1.08	5000	6.0	0.080	20.0	24	2	CE	700	
40 X 40 X 10	AD0412MB-G73	BALL	12	0.09	1.08	4800	5.7	0.078	20.0	24	3	CE	700	
40 X 40 X 10	AD0412HB-G70	BALL	12	0.10	1.20	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HB-G70(U)	BALL	12	0.10	1.20	6800	7.9	0.129	28.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HB-G72	BALL	12	0.10	1.20	6000	6.7	0.100	25.0	24	2,3	CE	700	
40 X 40 X 10	AD0412UB-G70	BALL	12	0.10	1.20	6800	7.9	0.129	28.0	24	0,6	CE	700	
40 X 40 X 10	AD0412DS-G70	S	12	0.07	0.84	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0412LS-G70	S	12	0.07	0.84	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MS-G70	S	12	0.08	0.96	4800	5.7	0.078	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HS-G70	S	12	0.10	1.20	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424LX-G70(T)	HYPRO	24	0.07	1.68	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MX-G70	HYPRO	24	0.05	1.20	4200	4.7	0.068	17.2	24	0	CE	700	
40 X 40 X 10	AD0424MX-G70(T)	HYPRO	24	0.08	1.92	4800	5.7	0.078	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424HX-G70	HYPRO	24	0.09	2.16	6000	6.8	0.100	25.0	24	0	UL,CUL,CSA,TUV,CE	700	
40 X 40 X 10	AD0424HX-G76(T)	HYPRO	24	0.09	2.16	6000	6.7	0.100	25.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424LB-G70	BALL	24	0.07	1.68	4600	5.0	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MB-G70	BALL	24	0.08	1.92	4800	5.7	0.078	20.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MB-G76	BALL	24	0.08	1.92	5000	5.9	0.080	20.0	24	6	CE	700	
40 X 40 X 10	AD0424HB-G70	BALL	24	0.09	2.16	6000	6.7	0.100	25.0	24	0	UL,CUL,CSA,TUV,CE	700	
40 X 40 X 10	AD0424HB-G76	BALL	24	0.09	2.16	6000	6.7	0.100	25.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424LS-G70	S	24	0.07	1.68	4200	4.7	0.060	14.0	24	0	CE	700	
40 X 40 X 10	AD0424LS-G76	S	24	0.07	1.68	4200	4.7	0.060	14.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MS-G70	S	24	0.08	1.92	4800	5.7	0.078	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424HS-G70	S	24	0.09	2.16	6000	6.7	0.100	25.0	24	0	UL,CUL,CSA,TUV,CE	700	
40 X 40 X 10	AD0424HS-G76	S	24	0.09	2.16	6000	6.7	0.100	25.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 15	AD0412LX-D50	HYPRO	12	0.08	0.96	6000	6.8	0.161	30.3	27	0	CE	700	44.00
40 X 40 X 15	AD0412LX-D52	HYPRO	12	0.10	1.20	6000	6.8	0.161	30.3	27	2	UL,CUL,TUV,CE	700	44.00
40 X 40 X 15	AD0412LX-D56	HYPRO	12	0.08	0.96	6000	6.8	0.161	30.3	27	6	UL,CUL,CE	700	44.00
40 X 40 X 15	AD0412MX-D50	HYPRO	12	0.10	1.20	7000	8.1	0.210	31.8	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412MX-D52	HYPRO	12	0.12	1.44	7000	8.1	0.210	31.8	27	2	UL,CUL,TUV,CE	500	44.00

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 15	AD0412HX-D50	HYPRO	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LB-D50	BALL	12	0.08	0.96	6000	6.8	0.161	30.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LB-D50(S)	1B & 1S	12	0.08	0.96	6500	7.3	0.183	30.6	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LB-D52	BALL	12	0.10	1.20	6000	6.8	0.161	30.3	27	2	UL,CUL,TUV,CE	500	44.00
40 X 40 X 15	AD0412MB-D50	BALL	12	0.10	1.20	7000	8.1	0.210	31.8	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412MB-D50(S)	1B & 1S	12	0.10	1.20	7500	8.5	0.231	33.5	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412MB-D52	BALL	12	0.12	1.44	7000	8.1	0.210	31.8	27	2	UL,CUL,TUV,CE	500	44.00
40 X 40 X 15	AD0412HB-D50	BALL	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412HB-D50(S)	1B & 1S	12	0.12	1.44	8500	10.2	0.298	39.8	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412HB-D52	BALL	12	0.15	1.80	8000	9.2	0.287	39.3	27	2	UL,CUL,TUV,CE	500	44.00
40 X 40 X 15	AD0412HB-D56	BALL	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LS-D50	S	12	0.08	0.96	6000	6.8	0.161	30.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412MS-D50	S	12	0.10	1.20	7000	8.1	0.210	31.8	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412HS-D50	S	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 20	AD0405LX-C50	HYPRO	5	0.14	0.70	5700	7.2	0.142	22.4	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405MX-C50	HYPRO	5	0.16	0.80	6300	7.8	0.171	26.3	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HX-C50	HYPRO	5	0.29	1.45	7500	9.2	0.250	31.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HX-C52	HYPRO	5	0.40	2.00	7500	9.2	0.250	31.0	28	2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405DB-C50	BALL	5	0.12	0.60	4200	4.9	0.080	16.5	28	0,6	CE	500	36.96
40 X 40 X 20	AD0405LB-C50	BALL	5	0.14	0.70	6000	7.2	0.142	22.4	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405MB-C50	BALL	5	0.16	0.80	6500	8.1	0.171	27.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HB-C50	BALL	5	0.29	1.45	7800	9.9	0.256	31.9	28	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HB-C52	BALL	5	0.40	2.00	7800	9.9	0.256	31.9	28	2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HB-C56	BALL	5	0.29	1.45	7800	9.9	0.256	31.9	28	6	CE	500	36.96
40 X 40 X 20	AD0405DS-C50	S	5	0.12	0.60	3700	4.7	0.064	10.0	28	0	CE	500	36.96
40 X 40 X 20	AD0405LS-C50	S	5	0.14	0.70	5700	7.2	0.142	22.4	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405MS-C50	S	5	0.16	0.80	6300	7.8	0.171	26.3	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HS-C50	S	5	0.29	1.45	7500	9.2	0.250	31.0	28	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HS-C56	S	5	0.29	1.45	7500	9.2	0.250	31.0	28	6	CE	500	36.96
40 X 40 X 20	AD0412DX-C50	HYPRO	12	0.05	0.60	3700	4.7	0.064	10.0	27	0,6	UL,CUL,CE	500	36.96
40 X 40 X 20	AD0412LX-C50	HYPRO	12	0.07	0.84	6000	7.5	0.154	23.9	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MX-C50	HYPRO	12	0.08	0.96	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MX-C53	HYPRO	12	0.13	1.56	6700	8.3	0.180	27.5	28	3	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HX-C50	HYPRO	12	0.11	1.32	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412DB-C50	BALL	12	0.05	0.60	4200	4.9	0.080	16.5	27	0	UL,CUL,CE	500	36.96
40 X 40 X 20	AD0412LB-C50	BALL	12	0.07	0.84	6200	7.7	0.165	25.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412LB-C51	BALL	12	0.11	1.32	6200	7.7	0.165	25.0	28	1,2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MB-C50	BALL	12	0.08	0.96	6900	8.5	0.190	28.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MB-C52	BALL	12	0.13	1.56	6900	8.5	0.190	28.5	28	2,3	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HB-C50	BALL	12	0.10	1.20	7800	10.1	0.263	31.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HB-C52	BALL	12	0.15	1.80	7800	10.1	0.263	31.9	28	2	CE	500	36.96
40 X 40 X 20	AD0412HB-C53	BALL	12	0.15	1.80	7800	10.1	0.263	31.9	28	3	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412UB-C50	BALL	12	0.14	1.68	8500	10.6	0.325	36.1	28	0,6	UL,CUL,TUV,CE	500	36.96

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 20	AD0412DS-C56	S	12	0.05	0.60	3700	4.7	0.064	10.0	27	6	UL,CUL,CE	500	36.96
40 X 40 X 20	AD0412LS-C50	S	12	0.07	0.84	6000	7.5	0.154	23.9	27	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412LS-C56	S	12	0.07	0.84	6000	7.5	0.154	23.9	27	6	CE	500	36.96
40 X 40 X 20	AD0412MS-C50	S	12	0.08	0.96	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HS-C50	S	12	0.11	1.32	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HS-C52	S	12	0.15	1.80	7500	9.6	0.240	31.0	28	2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412US-C50	S	12	0.14	1.68	8200	10.3	0.305	35.0	28	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LX-C50	B or S	24	0.06	1.44	6000	7.5	0.154	23.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MX-C50	B or S	24	0.07	1.68	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HX-C50	B or S	24	0.09	2.16	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LB-C50	BALL	24	0.06	1.44	6200	7.7	0.165	25.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MB-C50	BALL	24	0.07	1.68	6900	8.5	0.190	28.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HB-C50	BALL	24	0.09	2.16	7800	10.1	0.263	31.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LS-C50	S	24	0.06	1.44	6000	7.5	0.154	23.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MS-C50	S	24	0.07	1.68	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HS-C50	S	24	0.09	2.16	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96

NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires

**ALL RIGHTS RESERVED**