

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
20 X 20 X 6	AD2005DX-K70	HYPRO	5	0.06	0.30	7000	0.4	0.022	12.0	4	0	CE	600	12.28
20 X 20 X 6	AD2005LX-K70	HYPRO	5	0.10	0.50	10500	0.6	0.066	19.5	4	0	TUV,CE	600	12.28
20 X 20 X 6	AD2005MX-K70	HYPRO	5	0.15	0.75	14000	0.7	0.103	26.9	4	0	CE	600	12.28
20 X 20 X 6	AD2005MX-K73	HYPRO	5	0.12	0.60	14000	0.7	0.130	26.0	4	3	CE	600	12.28
20 X 20 X 6	AD2005DB-K70(S)	1B,1S	5	0.04	0.20	7000	0.4	0.022	12.0	4	0	CE	600	12.28
20 X 20 X 6	AD2005LB-K70(S)	1B,1S	5	0.05	0.25	10500	0.6	0.066	19.5	4	0	TUV,CE	600	12.28
20 X 20 X 6	AD2005MB-K70(S)	1B,1S	5	0.13	0.65	14000	0.7	0.103	26.9	4	0	CE	600	12.28
20 X 20 X 6	AD2012LX-K70	HYPRO	12	0.06	0.72	10500	0.6	0.066	19.5	4	0	CE	600	12.28
20 X 20 X 6	AD2012MX-K70	HYPRO	12	0.07	0.84	14000	0.7	0.103	26.9	4	0	CE	600	12.28
20 X 20 X 6	AD2012LB-K70(S)	1B,1S	12	0.06	0.72	10500	0.6	0.066	19.5	4	0	CE	600	12.28
20 X 20 X 6	AD2012MB-K70(S)	1B,1S	12	0.07	0.84	14000	0.7	0.103	26.9	4	0	CE	600	12.28
20 X 20 X 10	AD2005MX-G70	HYPRO	5	0.14	0.70	11500	0.8	0.072	26.0	6	0	UL,CUL,CE	900	17.60
20 X 20 X 10	AD2005MX-G73	HYPRO	5	0.11	0.55	10000	0.8	0.072	26.0	6	3	CE	900	17.60
20 X 20 X 10	AD2005LB-G70	Bor1B1S	5	0.06	0.30	9000	0.6	0.055	26.0	6	0	UL,CUL,CE	900	17.60
20 X 20 X 10	AD2005LB-G73	BALL	5	0.08	0.40	8000	0.4	0.039	11.0	6	3	CE	900	17.60
20 X 20 X 10	AD2005MB-G70	Bor1B1S	5	0.07	0.35	11500	0.8	0.072	20.0	6	0	UL,CUL,TUV,CE	900	17.60
20 X 20 X 10	AD2005MB-G73	Bor1B1S	5	0.08	0.40	10000	0.8	0.072	26.0	6	3	CE	900	17.60
20 X 20 X 10	AD2012LX-G70	HYPRO	12	0.06	0.72	9000	0.6	0.055	20.0	6	0	UL,CUL,CE	900	17.60
20 X 20 X 10	AD2012LB-G70	BALL	12	0.07	0.84	9000	0.6	0.055	20.0	6	0	CE	900	17.60
20 X 20 X 10	AD2012LM-G70	BALL	12	0.06	0.72	11500	0.8	0.072	26.0	6	0	CE	900	17.60
25 X 25 X 6	AD0205LX-K50	HYPRO	5	0.08	0.40	9000	1.8	0.100	20.5	5	0	TUV,CE	600	13.60
25 X 25 X 6	AD0205LX-K53	HYPRO	5	0.06	0.30	9000	1.8	0.100	20.5	5	3	CE	600	13.60
25 X 25 X 6	AD0205MX-K50	HYPRO	5	0.13	0.65	12000	2.4	0.185	26.0	5	0	CE	600	13.60
25 X 25 X 6	AD0205MX-K53	HYPRO	5	0.12	0.60	12000	2.4	0.185	26.0	5	3	CE	600	13.60
25 X 25 X 6	AD0205LB-K50(S)	1B,1S	5	0.05	0.25	9000	1.8	0.100	20.5	5	0	TUV,CE	600	13.60
25 X 25 X 6	AD0205LB-K53(S)	1B,1S	5	0.05	0.25	9000	1.8	0.100	20.5	5	3	CE	600	13.60
25 X 25 X 6	AD0205MB-K50(S)	1B,1S	5	0.09	0.45	12000	2.4	0.185	26.0	5	0	CE	600	13.60
25 X 25 X 6	AD0205MB-K53(S)	1B,1S	5	0.07	0.35	12000	2.4	0.185	26.0	5	3	UL,CUL,TUV,CE	600	13.60
25 X 25 X 6	AD0205HB-K50(S)	1B,1S	5	0.09	0.45	12000	2.4	0.185	26.0	5	0	CE	600	13.60
25 X 25 X 6	AD0212LX-K50	HYPRO	12	0.06	0.72	9000	1.8	0.100	20.5	5	0	CE	600	13.60
25 X 25 X 6	AD0212MX-K50	HYPRO	12	0.09	1.08	12000	2.4	0.185	26.0	5	0	CE	600	13.60
25 X 25 X 6	AD0212LB-K50(S)	BALL	12	0.06	0.72	9000	1.8	0.100	20.5	5	0	CE	600	13.60
25 X 25 X 6	AD0212MB-K50(S)	BALL	12	0.07	0.84	12000	2.4	0.185	26.0	5	0	CE	600	13.60
25 X 25 X 10	AD0205LX-G50	HYPRO	5	0.10	0.50	8000	1.8	0.116	15.6	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205LX-G50(D)	HYPRO	5	0.08	0.40	4500	1.0	0.034	2.4	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205LX-G53GL	HYPRO	5	0.08	0.40	8000	1.8	0.116	15.6	8	3	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205MX-G50GL	HYPRO	5	0.12	0.60	10000	2.3	0.173	23.1	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205MX-G53GL	HYPRO	5	0.12	0.60	10000	2.3	0.173	23.1	8	3	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205HX-G50	HYPRO	5	0.18	0.90	12000	2.8	0.236	28.0	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205LB-G50GL	BALL	5	0.10	0.50	8000	1.8	0.116	15.6	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0205LB-G50(D)	BALL	5	0.07	0.35	6500	1.4	0.064	12.0	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0205LB-G53GL	BALL	5	0.06	0.30	8000	1.8	0.116	15.6	8	3	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0205MB-G50GL	BALL	5	0.12	0.60	10000	2.3	0.173	23.1	8	0	UL,CUL,CE	600	

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
25 X 25 X 10	AD0205MB-G53	BALL	5	0.07	0.35	10000	2.3	0.173	23.1	8	3	TUV,CE	600	
25 X 25 X 10	AD0205HB-G50GL	BALL	5	0.14	0.70	12000	2.8	0.236	28.0	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0205HB-G53	BALL	5	0.12	0.60	12000	2.8	0.236	28.0	8	3	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0212LX-G50	HYPRO	12	0.07	0.84	8000	1.8	0.116	15.6	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0212MX-G50GL	HYPRO	12	0.08	0.96	10000	2.3	0.173	23.1	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0212HX-G50GL	HYPRO	12	0.09	1.08	12000	2.8	0.236	28.0	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0212LB-G50	BALL	12	0.07	0.84	8000	1.8	0.116	15.6	8	0	UL,CUL,CE	600	
25 X 25 X 10	AD0212MB-G50	BALL	12	0.08	0.96	10000	2.3	0.173	23.1	8	0	UL,CUL,TUV,CE	600	
25 X 25 X 10	AD0212HB-G50	BALL	12	0.09	1.08	12000	2.8	0.236	28.0	8	0	UL,CUL,CE	600	
25 X 25 X 15	AD0205LX-D50	HYPRO	5	0.08	0.40	5000	1.2	0.040	7.2	8	0	CE		
25 X 25 X 15	AD0205LB-D50	BALL	5	0.06	0.30	5000	1.2	0.040	7.2	8	0	CE		
25 X 25 X 15	AD0205MB-D50	BALL	5	0.09	0.45	6000	1.4	0.054	10.0	8	0	CE		
25 X 25 X 15	AD0205HB-D50	BALL	5	0.13	0.65	8000	1.9	0.114	19.2	8	0	CE		
25 X 25 X 15	AD0205HB-D53	BALL	5	0.13	0.65	8000	1.9	0.114	19.2	8	3	UL,CUL,TUV,CE		
25 X 25 X 15	AD0205HB-D53(A)	BALL	5	0.13	0.65	7500	1.8	0.091	16.7	8	3	UL,CUL,TUV,CE		
30 X 30 X 6	AD0305LX-K70	HYPRO	5	0.09	0.45	7500	2.5	0.082	20.0	6	0	UL,CUL,TUV,CE	400	12.30
30 X 30 X 6	AD0305LX-K73	HYPRO	5	0.07	0.35	7500	2.5	0.082	20.0	6	3	CE	400	12.30
30 X 30 X 6	AD0305MX-K70	HYPRO	5	0.12	0.60	9000	3.3	0.138	27.9	6	0	CE	400	12.30
30 X 30 X 6	AD0305MX-K73	HYPRO	5	0.10	0.50	8000	8.3	0.196	34.7	11	3	CE	400	12.30
30 X 30 X 6	AD0305HX-K70	HYPRO	5	0.18	0.90	10500	3.6	0.164	32.1	6	0	CE	400	12.30
30 X 30 X 6	AD0305HX-K73	HYPRO	5	0.11	0.55	10500	3.6	0.164	32.1	6	3	CE	400	12.30
30 X 30 X 6	AD0305LB-K70(S)	1B,1S	5	0.06	0.30	7500	2.5	0.082	20.0	6	0	UL,CUL,TUV,CE	400	12.30
30 X 30 X 6	AD0305LB-K73(S)	1B,1S	5	0.05	0.25	7500	2.5	0.082	20.0	6	3	CE	400	12.30
30 X 30 X 6	AD0305MB-K70(S)	BALL	5	0.08	0.40	9000	3.3	0.138	27.9	6	0	CE	400	12.30
30 X 30 X 6	AD0305MB-K73(S)	1B,1S	5	0.06	0.30	9000	3.3	0.138	27.9	6	3	CE	400	12.30
30 X 30 X 6	AD0305MB-K73(Y)	1B,1S	5	0.08	0.40	9000	7.2	0.120	34.0	6	3	CE	400	12.30
30 X 30 X 6	AD0305HB-K73(S)	1B,1S	5	0.07	0.35	10500	3.6	0.164	32.1	6	3	CE	400	12.30
30 X 30 X 6	AD0312LX-K70	HYPRO	12	0.06	0.72	7500	2.5	0.082	20.0	6	0	UL,CUL,TUV,CE	400	12.30
30 X 30 X 6	AD0312MX-K70	HYPRO	12	0.10	1.20	9000	3.3	0.138	27.9	6	0	CE	400	12.30
30 X 30 X 6	AD0312HX-K70	HYPRO	12	0.08	0.96	10500	3.6	0.164	32.1	6	0	CE	400	12.30
30 X 30 X 6	AD0312LB-K70(S)	BALL	12	0.06	0.72	7500	2.5	0.082	20.0	6	0	CE	400	12.30
30 X 30 X 6	AD0312MB-K70(S)	BALL	12	0.06	0.72	9000	3.3	0.138	27.9	6	0	UL,CUL,TUV,CE	400	12.30
30 X 30 X 6	AD0312HB-K70(S)	BALL	12	0.09	1.08	10500	3.6	0.164	32.1	6	0	CE	400	12.30
30 X 30 X 10	AD0305DX-G50	HYPRO	5	0.09	0.45	5500	1.8	0.080	17.0	8	0	UL,CUL,CE	400	14.00
30 X 30 X 10	AD0305LX-G50	HYPRO	5	0.12	0.60	8000	3.0	0.115	20.2	8	0	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0305LX-G53	HYPRO	5	0.09	0.45	8000	3.0	0.115	20.2	8	3	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0305MX-G53	HYPRO	5	0.11	0.55	9000	4.1	0.148	27.9	8	3	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0305HX-G50	HYPRO	5	0.17	0.85	10500	4.2	0.210	30.7	8	0	CE	400	14.00
30 X 30 X 10	AD0305DB-G50	BALL	5	0.06	0.30	5500	1.8	0.080	17.0	8	0	UL,CUL,CE	400	14.00
30 X 30 X 10	AD0305LB-G50	BALL	5	0.12	0.60	8000	3.0	0.115	20.2	8	0	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0305LB-G53	BALL	5	0.08	0.40	8000	3.0	0.115	20.2	8	3	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0305MB-G50	Bor1B1S	5	0.13	0.65	9000	4.1	0.148	27.9	8	0	UL,CUL,CE	400	14.00
30 X 30 X 10	AD0305MB-G53	Bor1B1S	5	0.11	0.55	9000	4.1	0.148	27.9	8	3	UL,CUL,TUV,CE	400	14.00

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
30 X 30 X 10	AD0305DX-G50	HYPRO	5	0.06	0.72	6000	2.5	0.068	16.0	8	0	CE	400	14.00
30 X 30 X 10	AD0312LX-G50	HYPRO	12	0.07	0.84	8000	3.0	0.115	20.2	8	0	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0312MX-G50	HYPRO	12	0.12	1.44	9000	4.1	0.148	27.9	8	0	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0312DB-G50	Bor1B1S	12	0.05	0.60	6000	2.5	0.068	16.0	8	0	UL,CUL,CE	400	14.00
30 X 30 X 10	AD0312LB-G50	BALL	12	0.06	0.72	8000	3.0	0.115	20.2	8	0	UL,CUL,TUV,CE	400	14.00
30 X 30 X 10	AD0312MB-G50	Bor1B1S	12	0.12	1.44	9000	4.1	0.148	27.9	8	0	UL,CUL,CE	400	14.00
30 X 30 X 10	AD0312HB-G50	Bor1B1S	12	0.11	1.32	10500	4.2	0.210	30.7	8	0	CE	400	14.00
30 X 30 X 15	AD0305LB-D50	BALL	5	0.07	0.35	4500	2.2	0.045	10.0	10	0	CE		
30 X 30 X 15	AD0305MB-D50	BALL	5	0.08	0.40	5500	2.6	0.074	16.0	10	0	CE		
30 X 30 X 15	AD0305MB-D50(S)	1B,1S	5	0.10	0.50	5500	2.6	0.074	16.0	10	0	CE		
30 X 30 X 15	AD0305MB-D53	BALL	5	0.06	0.30	5500	2.6	0.074	16.0	10	3	UL,CUL,TUV,CE		
30 X 30 X 15	AD0305HB-D50	Bor1B1S	5	0.13	0.65	7000	3.7	0.110	22.5	10	0	CE		
30 X 30 X 15	AD0305HB-D53	BALL	5	0.10	0.50	7000	3.7	0.110	22.5	10	3	UL,CUL,TUV,CE		
35 X 35 X 6	AD3505LX-K70	HYPRO	5	0.10	0.50	6500	3.5	0.063	19.0	7	0	TUV,CE	400	13.00
35 X 35 X 6	AD3505LX-K73	HYPRO	5	0.08	0.40	6500	3.5	0.063	19.0	7	3	CE	400	13.00
35 X 35 X 6	AD3505MX-K70	HYPRO	5	0.14	0.70	8000	4.7	0.111	28.0	7	0	CE	400	13.00
35 X 35 X 6	AD3505MX-KBO	HYPRO	5	0.14	0.70	7000	3.6	0.097	29.0	4	0	CE	400	13.00
35 X 35 X 6	AD3505LB-K70(S)	1B,1S	5	0.06	0.30	6500	3.5	0.063	19.0	7	0	TUV,CE	400	13.00
35 X 35 X 6	AD3505MB-K70(S)	1B,1S	5	0.10	0.50	8000	4.7	0.111	28.0	7	0	CE	400	13.00
35 X 35 X 6	AD3505MB-K73(S)	1B,1S	5	0.08	0.40	8000	4.7	0.111	28.0	7	3	CE	400	13.00
35 X 35 X 6	AD3505HB-K70(S)	1B,1S	5	0.13	0.65	9500	4.9	0.150	35.0	7	0	CE	400	13.00
35 X 35 X 6	AD3505HB-K73(S)	1B,1S	5	0.09	0.45	9500	4.9	0.150	35.0	7	3	CE	400	13.00
35 X 35 X 6	AD3512LX-K70	HYPRO	12	0.06	0.72	6500	3.5	0.063	19.0	7	0	TUV,CE	400	13.00
35 X 35 X 6	AD3512MX-K70	HYPRO	12	0.08	0.96	8000	4.7	0.111	28.0	7	0	CE	400	13.00
35 X 35 X 6	AD3512HX-K70	HYPRO	12	0.10	1.20	9500	4.9	0.150	35.0	7	0	CE	400	13.00
35 X 35 X 6	AD3512LB-K70(S)	BALL	12	0.05	0.60	6500	3.5	0.063	19.0	7	0	TUV,CE	400	13.00
35 X 35 X 6	AD3512MB-K70(S)	BALL	12	0.06	0.72	8000	4.7	0.111	28.0	7	0	TUV,CE	400	13.00
35 X 35 X 6	AD3512HB-K70	BALL	12	0.08	0.96	9500	4.9	0.150	35.0	7	0	CE	400	13.00
35 X 35 X 10	AD3505LX-G53	HYPRO	5	0.09	0.45	7000	5.1	0.100	27.5	9	3	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505MX-G50	HYPRO	5	0.17	0.85	8000	6.0	0.131	30.0	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505MX-G53	HYPRO	5	0.13	0.65	8000	6.0	0.138	30.0	9	3	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505HX-G53	HYPRO	5	0.17	0.85	9500	7.1	0.174	37.6	9	3	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505LB-G50	BALL	5	0.12	0.60	7000	5.1	0.100	27.5	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505MB-G50	BALL	5	0.13	0.65	8000	6.0	0.131	30.0	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505MB-G53	BALL	5	0.13	0.65	8000	6.2	0.160	27.0	9	3	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3505MB-G53(S)	1B,1S	5	0.13	0.65	8000	6.0	0.138	30.0	9	3	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512LX-G50	HYPRO	12	0.08	0.96	7000	5.1	0.100	27.5	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512MX-G50	HYPRO	12	0.09	1.08	8000	6.0	0.138	30.0	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512HX-G50	HYPRO	12	0.11	1.32	9500	7.1	0.174	37.6	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512LB-G50	BALL	12	0.08	0.96	7000	5.1	0.100	27.5	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512MB-G50	BALL	12	0.09	1.08	8000	6.0	0.138	30.0	9	0	UL,CUL,TUV,CE	400	13.20
35 X 35 X 10	AD3512HB-G50	BALL	12	0.11	1.32	9500	7.1	0.174	37.6	9	0	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405LX-K90	HYPRO	5	0.05	0.25	4500	4.2	0.044	19.5	9	0,6	UL,CUL,TUV,CE	400	13.20

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 6	AD0405LX-KC0	HYPRO	5	0.11	0.55	4500	3.6	0.061	22.4	9	0	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405LX-KC3	HYPRO	5	0.08	0.40	4500	4.6	0.068	27.1	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MX-K90	HYPRO	5	0.09	0.45	5500	5.2	0.064	23.8	9	0,6	UL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MX-KC0	HYPRO	5	0.20	1.00	5500	4.6	0.093	28.6	9	0,3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MX-KC3(Y)	HYPRO	5	0.11	0.55	5500	4.6	0.093	28.6	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HX-K90	HYPRO	5	0.12	0.60	6300	6.0	0.079	27.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HX-KC0	HYPRO	5	0.23	1.15	6000	5.0	0.110	31.2	9	0	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HX-KC3	HYPRO	5	0.13	0.65	6000	5.0	0.110	31.2	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405LB-K90(S)	1B,1S	5	0.05	0.25	4800	4.5	0.051	19.9	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MB-K90(S)	1B,1S	5	0.09	0.45	5800	5.5	0.067	25.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MB-KC3	BALL	5	0.11	0.55	5800	4.9	0.102	30.0	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HB-K90(S)	1B,1S	5	0.12	0.60	6600	6.0	0.090	30.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MS-K90	S	5	0.09	0.45	5500	5.2	0.064	23.8	9	0	CE	400	13.20
40 X 40 X 6	AD0412LX-K90	HYPRO	12	0.06	0.72	4500	4.4	0.049	20.9	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412MX-K90	HYPRO	12	0.06	0.72	5500	5.2	0.064	23.8	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412HX-K90	HYPRO	12	0.08	0.96	6300	5.9	0.079	27.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412LB-K90(S)	1B,1S	12	0.06	0.72	4800	4.7	0.049	21.6	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412MB-K90(S)	1B,1S	12	0.06	0.72	5800	5.5	0.067	25.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412HB-K90(S)	1B,1S	12	0.08	0.96	6600	6.0	0.090	30.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 8	AD0405LX-J90	HYPRO	5	0.12	0.60	4100	5.1	0.058	20.0	5	0	CE		
40 X 40 X 8	AD0405MX-J90	HYPRO	5	0.16	0.80	5500	6.3	0.094	28.7	5	0	CE		
40 X 40 X 8	AD0405MX-J93	HYPRO	5	0.15	0.75	5500	6.8	0.098	29.0	5	3	CE		
40 X 40 X 8	AD0405HX-J91	HYPRO	5	0.23	1.15	6000	7.5	0.110	31.0	5	1,3	CE		
40 X 40 X 8	AD0405MB-J90	BALL	5	0.20	1.00	5000	6.1	0.089	26.0	5	0	CE		
40 X 40 X 8	AD0412MX-J90	HYPRO	12	0.13	1.56	5000	6.1	0.089	26.0	5	0	CE		
40 X 40 X 9	AD0405HX-RA3	HYPRO	5	0.25	1.25	6000	3.1	0.334	40.3	5	3	CE		
40 X 40 X 10	AD0405DX-G70	HYPRO	5	0.07	0.35	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0405LX-G70	HYPRO	5	0.08	0.40	4200	4.7	0.060	14.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405LX-G76	HYPRO	5	0.08	0.40	4200	4.7	0.060	14.0	24	6	UL,CUL,CE	700	
40 X 40 X 10	AD0405MX-G70	HYPRO	5	0.11	0.55	4800	5.7	0.780	19.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MX-G7	HYPRO	5	0.11	0.55	4800	5.7	0.078	20.0	24	6	UL,CUL,CE	700	
40 X 40 X 10	AD0405HX-G70	HYPRO	5	0.19	0.95	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405DB-G70	BALL	5	0.07	0.35	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0405LB-G70	BALL	5	0.08	0.40	4600	5.0	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MB-G70	BALL	5	0.11	0.55	4800	5.7	0.078	20.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MB-G72	BALL	5	0.15	0.75	4800	5.7	0.078	20.0	24	2	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MB-G73	BALL	5	0.15	0.75	4800	5.7	0.078	20.0	24	3	CE	700	
40 X 40 X 10	AD0405MB-G76	BALL	5	0.11	0.55	5000	6.0	0.080	20.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405HB-G70	BALL	5	0.19	0.95	6000	6.8	0.100	25.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405HB-G72	BALL	5	0.25	1.25	6000	6.7	0.100	25.0	24	2	CE	700	
40 X 40 X 10	AD0405HB-G76	BALL	5	0.19	0.95	6000	6.8	0.100	25.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405LS-G70	S	5	0.08	0.40	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MS-G70	S	5	0.11	0.55	4800	5.7	0.078	20.0	24	0,2,6	UL,CUL,TUV,CE	700	

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 10	AD0405HS-G70	S	5	0.19	0.95	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405HS-G7B	S	5	0.15	0.75	6000	6.7	0.100	25.0	24	0	CE	700	
40 X 40 X 10	AD0409HS-G70	S	9	0.13	1.17	6000	6.8	0.100	25.0	24	0	UL,CE	700	
40 X 40 X 10	AD0409LS-G70	S	9	0.08	0.72	4200	4.7	0.060	14.0	24	0	CE	700	
40 X 40 X 10	AD0409MS-G70	S	9	0.10	0.90	4800	5.6	0.080	19.0	24	0	CE	700	
40 X 40 X 10	AD0409US-G70	S	9	0.15	1.35	7000	7.7	0.068	29.7	24	0	CE	700	
40 X 40 X 10	AD0412DX-G70	HYPRO	12	0.07	0.84	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0412LX-G70	HYPRO	12	0.07	0.84	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MX-G70	HYPRO	12	0.08	0.96	4800	5.7	0.078	19.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HX-G70	HYPRO	12	0.10	1.20	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HX-G71	HYPRO	12	0.10	1.20	6000	6.7	0.100	25.0	24	1	CE	700	
40 X 40 X 10	AD0412DB-G70	BALL	12	0.07	0.84	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0412LB-G70	BALL	12	0.07	0.84	4600	5.0	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MB-G70	BALL	12	0.08	0.96	5000	5.9	0.080	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MB-G72	BALL	12	0.09	1.08	5000	6.0	0.080	20.0	24	2	CE	700	
40 X 40 X 10	AD0412MB-G73	BALL	12	0.09	1.08	4800	5.7	0.078	20.0	24	3	CE	700	
40 X 40 X 10	AD0412HB-G70	BALL	12	0.10	1.20	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HB-G70(U)	BALL	12	0.10	1.20	6800	7.9	0.129	28.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HB-G72	BALL	12	0.10	1.20	6000	6.7	0.100	25.0	24	2,3	CE	700	
40 X 40 X 10	AD0412UB-G70	BALL	12	0.10	1.20	6800	7.9	0.129	28.0	24	0,6	CE	700	
40 X 40 X 10	AD0412DS-G70	S	12	0.07	0.84	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0412LS-G70	S	12	0.07	0.84	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MS-G70	S	12	0.08	0.96	4800	5.7	0.078	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HS-G70	S	12	0.10	1.20	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424LX-G70(T)	HYPRO	24	0.07	1.68	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MX-G70	HYPRO	24	0.05	1.20	4200	4.7	0.068	17.2	24	0	CE	700	
40 X 40 X 10	AD0424MX-G70(T)	HYPRO	24	0.08	1.92	4800	5.7	0.078	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424HX-G70	HYPRO	24	0.09	2.16	6000	6.8	0.100	25.0	24	0	UL,CUL,CSA,TUV,CE	700	
40 X 40 X 10	AD0424HX-G76(T)	HYPRO	24	0.09	2.16	6000	6.7	0.100	25.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424LB-G70	BALL	24	0.07	1.68	4600	5.0	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MB-G70	BALL	24	0.08	1.92	4800	5.7	0.078	20.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MB-G76	BALL	24	0.08	1.92	5000	5.9	0.080	20.0	24	6	CE	700	
40 X 40 X 10	AD0424HB-G70	BALL	24	0.09	2.16	6000	6.7	0.100	25.0	24	0	UL,CUL,CSA,TUV,CE	700	
40 X 40 X 10	AD0424HB-G76	BALL	24	0.09	2.16	6000	6.7	0.100	25.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424LS-G70	S	24	0.07	1.68	4200	4.7	0.060	14.0	24	0	CE	700	
40 X 40 X 10	AD0424LS-G76	S	24	0.07	1.68	4200	4.7	0.060	14.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MS-G70	S	24	0.08	1.92	4800	5.7	0.078	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424HS-G70	S	24	0.09	2.16	6000	6.7	0.100	25.0	24	0	UL,CUL,CSA,TUV,CE	700	
40 X 40 X 10	AD0424HS-G76	S	24	0.09	2.16	6000	6.7	0.100	25.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 15	AD0412LX-D50	HYPRO	12	0.08	0.96	6000	6.8	0.161	30.3	27	0	CE	700	44.00
40 X 40 X 15	AD0412LX-D52	HYPRO	12	0.10	1.20	6000	6.8	0.161	30.3	27	2	UL,CUL,TUV,CE	700	44.00
40 X 40 X 15	AD0412LX-D56	HYPRO	12	0.08	0.96	6000	6.8	0.161	30.3	27	6	UL,CUL,CE	700	44.00
40 X 40 X 15	AD0412MX-D50	HYPRO	12	0.10	1.20	7000	8.1	0.210	31.8	27	0,6	UL,CUL,CE	500	44.00

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 15	AD0412MX-D52	HYPRO	12	0.12	1.44	7000	8.1	0.210	31.8	27	2	UL,CUL,TUV,CE	500	44.00
40 X 40 X 15	AD0412HX-D50	HYPRO	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LB-D50	BALL	12	0.08	0.96	6000	6.8	0.161	30.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LB-D50(S)	1B & 1S	12	0.08	0.96	6500	7.3	0.183	30.6	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LB-D52	BALL	12	0.10	1.20	6000	6.8	0.161	30.3	27	2	UL,CUL,TUV,CE	500	44.00
40 X 40 X 15	AD0412MB-D50	BALL	12	0.10	1.20	7000	8.1	0.210	31.8	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412MB-D50(S)	1B & 1S	12	0.10	1.20	7500	8.5	0.231	33.5	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412MB-D52	BALL	12	0.12	1.44	7000	8.1	0.210	31.8	27	2	UL,CUL,TUV,CE	500	44.00
40 X 40 X 15	AD0412HB-D50	BALL	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412HB-D50(S)	1B & 1S	12	0.12	1.44	8500	10.2	0.298	39.8	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412HB-D52	BALL	12	0.15	1.80	8000	9.2	0.287	39.3	27	2	UL,CUL,TUV,CE	500	44.00
40 X 40 X 15	AD0412HB-D56	BALL	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412LS-D50	S	12	0.08	0.96	6000	6.8	0.161	30.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412MS-D50	S	12	0.10	1.20	7000	8.1	0.210	31.8	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 15	AD0412HS-D50	S	12	0.12	1.44	8000	9.2	0.287	39.3	27	0,6	UL,CUL,CE	500	44.00
40 X 40 X 20	AD0405LX-C50	HYPRO	5	0.14	0.70	5700	7.2	0.142	22.4	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405MX-C50	HYPRO	5	0.16	0.80	6300	7.8	0.171	26.3	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HX-C50	HYPRO	5	0.29	1.45	7500	9.2	0.250	31.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HX-C52	HYPRO	5	0.40	2.00	7500	9.2	0.250	31.0	28	2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405DB-C50	BALL	5	0.12	0.60	4200	4.9	0.080	16.5	28	0,6	CE	500	36.96
40 X 40 X 20	AD0405LB-C50	BALL	5	0.14	0.70	6000	7.2	0.142	22.4	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405MB-C50	BALL	5	0.16	0.80	6500	8.1	0.171	27.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HB-C50	BALL	5	0.29	1.45	7800	9.9	0.256	31.9	28	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HB-C52	BALL	5	0.40	2.00	7800	9.9	0.256	31.9	28	2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HB-C56	BALL	5	0.29	1.45	7800	9.9	0.256	31.9	28	6	CE	500	36.96
40 X 40 X 20	AD0405DS-C50	S	5	0.12	0.60	3700	4.7	0.064	10.0	28	0	CE	500	36.96
40 X 40 X 20	AD0405LS-C50	S	5	0.14	0.70	5700	7.2	0.142	22.4	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405MS-C50	S	5	0.16	0.80	6300	7.8	0.171	26.3	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HS-C50	S	5	0.29	1.45	7500	9.2	0.250	31.0	28	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0405HS-C56	S	5	0.29	1.45	7500	9.2	0.250	31.0	28	6	CE	500	36.96
40 X 40 X 20	AD0412DX-C50	HYPRO	12	0.05	0.60	3700	4.7	0.064	10.0	27	0,6	UL,CUL,CE	500	36.96
40 X 40 X 20	AD0412LX-C50	HYPRO	12	0.07	0.84	6000	7.5	0.154	23.9	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MX-C50	HYPRO	12	0.08	0.96	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MX-C53	HYPRO	12	0.13	1.56	6700	8.3	0.180	27.5	28	3	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HX-C50	HYPRO	12	0.11	1.32	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412DB-C50	BALL	12	0.05	0.60	4200	4.9	0.080	16.5	27	0	UL,CUL,CE	500	36.96
40 X 40 X 20	AD0412LB-C50	BALL	12	0.07	0.84	6200	7.7	0.165	25.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412LB-C51	BALL	12	0.11	1.32	6200	7.7	0.165	25.0	28	1,2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MB-C50	BALL	12	0.08	0.96	6900	8.5	0.190	28.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MB-C52	BALL	12	0.13	1.56	6900	8.5	0.190	28.5	28	2,3	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HB-C50	BALL	12	0.10	1.20	7800	10.1	0.263	31.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HB-C52	BALL	12	0.15	1.80	7800	10.1	0.263	31.9	28	2	CE	500	36.96
40 X 40 X 20	AD0412HB-C53	BALL	12	0.15	1.80	7800	10.1	0.263	31.9	28	3	UL,CUL,TUV,CE	500	36.96

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 20	AD0412UB-C50	BALL	12	0.14	1.68	8500	10.6	0.325	36.1	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412DS-C56	S	12	0.05	0.60	3700	4.7	0.064	10.0	27	6	UL,CUL,CE	500	36.96
40 X 40 X 20	AD0412LS-C50	S	12	0.07	0.84	6000	7.5	0.154	23.9	27	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412LS-C56	S	12	0.07	0.84	6000	7.5	0.154	23.9	27	6	CE	500	36.96
40 X 40 X 20	AD0412MS-C50	S	12	0.08	0.96	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HS-C50	S	12	0.11	1.32	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HS-C52	S	12	0.15	1.80	7500	9.6	0.240	31.0	28	2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412US-C50	S	12	0.14	1.68	8200	10.3	0.305	35.0	28	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LX-C50	B or S	24	0.06	1.44	6000	7.5	0.154	23.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MX-C50	B or S	24	0.07	1.68	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HX-C50	B or S	24	0.09	2.16	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LB-C50	BALL	24	0.06	1.44	6200	7.7	0.165	25.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MB-C50	BALL	24	0.07	1.68	6900	8.5	0.190	28.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HB-C50	BALL	24	0.09	2.16	7800	10.1	0.263	31.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LS-C50	S	24	0.06	1.44	6000	7.5	0.154	23.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MS-C50	S	24	0.07	1.68	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HS-C50	S	24	0.09	2.16	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96
45 X 45 X 6	AD4505LX-K90	HYPRO	5	0.10	0.50	4300	6.2	0.056	23.0	24	0	CE	560	19.30
45 X 45 X 6	AD4505MX-K90	HYPRO	5	0.12	0.60	5000	7.1	0.074	25.5	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505HX-K90	HYPRO	5	0.14	0.70	6000	9.2	0.103	32.6	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505LB-K90(S)	1B & 1S	5	0.10	0.50	4500	6.5	0.059	23.3	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505MB-K90(S)	1B & 1S	5	0.12	0.60	5500	7.2	0.085	26.5	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505HB-K90(S)	1B & 1S	5	0.14	0.70	6200	9.5	0.111	33.0	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512LX-K90	HYPRO	12	0.08	0.96	4300	6.2	0.056	23.0	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512MX-K90	HYPRO	12	0.09	1.08	5000	7.1	0.074	25.5	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512HX-K90	HYPRO	12	0.10	1.20	6000	9.2	0.103	32.6	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512LB-K90(S)	1B & 1S	12	0.08	0.96	4500	6.5	0.059	23.3	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512MB-K90(S)	1B & 1S	12	0.09	1.08	5500	7.2	0.085	26.5	24	0	CE	560	19.30
45 X 45 X 6	AD4512HB-K90(S)	1B & 1S	12	0.10	1.20	6200	9.5	0.111	33.0	24	0,6	CE	560	19.30
45 X 45 X 7	AD4505MX-QA0	HYPRO	5	0.09	0.45	5000	1.6	0.224	25.5	23	0	CE	480	
45 X 45 X 7	AD4505HX-QA0	HYPRO	5	0.14	0.70	5700	1.8	0.332	28.5	23	0,6	CE	480	
45 X 45 X 7	AD4505HX-QA3	HYPRO	5	0.12	0.60	6200	2.1	0.397	31.2	23	3	CE	480	
45 X 45 X 7	AD4505HB-QA3	BALL	5	0.12	0.60	6200	2.1	0.397	31.2	23	3	CE	480	
45 X 45 X 9	AD4505HX-RB3	HYPRO	5	0.22	1.10	4500	3.1	0.213	31.8	26	3	CE	500	
45 X 45 X 10	AD4505LX-G70(T)	HYPRO	5	0.16	0.80	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MX-G70	HYPRO	5	0.10	0.50	4200	6.9	0.069	21.6	24	0,6	CE	500	24.64
45 X 45 X 10	AD4505MX-G70(T)	HYPRO	5	0.18	0.90	4500	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MX-GD0	HYPRO	5	0.25	1.25	4200	2.0	0.290	22.0	26	0,6	CE	500	24.64
45 X 45 X 10	AD4505MX-GD1	HYPRO	5	0.15	0.75	5000	2.3	0.342	31.1	26	1	CE	500	24.64
45 X 45 X 10	AD4505HX-G70	HYPRO	5	0.20	1.00	5500	9.1	0.107	27.4	24	0	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505HX-G76	HYPRO	5	0.20	1.00	5500	9.1	0.109	28.6	24	6	CE	500	24.64
45 X 45 X 10	AD4505HX-GD0	HYPRO	5	0.22	1.10	5200	2.7	0.434	27.4	26	0,3	CE	500	24.64
45 X 45 X 10	AD4505HX-GD1	HYPRO	5	0.17	0.85	4800	7.0	0.050	28.9	26	1	CE	500	24.64

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
45 X 45 X 10	AD4505LB--G70	BALL	5	0.16	0.80	4200	7.0	0.066	20.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MB-G70	BALL	5	0.16	0.80	4200	6.9	0.069	21.6	24	0	CE	500	24.64
45 X 45 X 10	AD4505MB-G76	BALL	5	0.18	0.90	4500	7.5	0.078	22.0	24	6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MB-GD0	BALL	5	0.25	1.25	4200	2.0	0.290	22.0	26	0,6	CE	500	24.64
45 X 45 X 10	AD4505HB-G70	BALL	5	0.20	1.00	5000	8.2	0.101	26.2	24	0	CE	500	24.64
45 X 45 X 10	AD4505HB-G70(S)	1B & 1S	5	0.20	1.00	5500	9.8	0.116	27.5	24	0	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505HB-G70(T)	BALL	5	0.20	1.00	5500	9.1	0.107	27.4	24	0,6	CE	500	24.64
45 X 45 X 10	AD4505HB-GD0	BALL	5	0.22	1.10	5200	2.7	0.434	35.3	26	0,6	CE	500	24.64
45 X 45 X 10	AD4505LS-G70(T)	S	5	0.16	0.80	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MS-G70	S	5	0.16	0.80	4200	6.9	0.069	21.6	24	0	CE	500	24.64
45 X 45 X 10	AD4505MS-G76	S	5	0.18	0.90	4500	7.5	0.078	22.0	24	6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505HS-G70	S	5	0.20	1.00	5500	9.1	0.107	27.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505HS-GD0(Y)	S	5	0.22	1.10	5200	2.7	0.434	35.3	26	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512LX-G70(T)	HYPRO	12	0.06	0.72	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MX-G70	HYPRO	12	0.07	0.84	4200	6.9	0.069	21.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MX-G70(T)	HYPRO	12	0.07	0.84	4500	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512HX-G70	HYPRO	12	0.09	1.08	6500	10.4	0.145	31.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512HX-G70(T)	HYPRO	12	0.09	1.08	5500	9.1	0.107	27.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512LB-G70	BALL	12	0.06	0.72	4200	7.0	0.066	20.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MB-G70	Bor1B1S	12	0.07	0.84	4200	6.9	0.069	21.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MB-G70(T)	BALL	12	0.07	0.84	4500	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MB-G72(S)	1B & 1S	12	0.08	0.96	4800	7.9	0.081	23.7	24	2	CE	500	24.64
45 X 45 X 10	AD4512HB-G70	Bor1B1S	12	0.09	1.08	5000	8.3	0.097	26.1	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512HB-G70(T)	BALL	12	0.09	1.08	5500	9.1	0.107	27.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512LS-G70(T)	S	12	0.06	0.72	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MS-G70	S	12	0.07	0.84	4200	6.9	0.069	21.6	24	0	CE	500	24.64
45 X 45 X 10	AD4512MS-G76	S	12	0.07	0.84	4200	6.9	0.069	21.6	24	6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MS-G70(T)	S	12	0.07	0.84	4500	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512HS-G70	S	12	0.09	1.08	5000	8.3	0.097	26.1	24	0	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512HS-G70(T)	S	12	0.09	1.08	5500	9.1	0.109	28.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524LX-G70(T)	HYPRO	24	0.06	1.44	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524MX-G70(T)	HYPRO	24	0.07	1.68	4800	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524HX-G70(T)	HYPRO	24	0.08	1.92	5500	9.1	0.109	28.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524LB-G70(T)	BALL	24	0.06	1.44	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524LB-G70(S)	BALL	24	0.06	1.44	4200	7.0	0.066	20.4	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524MB-G70(T)	BALL	24	0.09	2.16	4500	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524MB-G70(S)	BALL	24	0.07	1.68	4800	7.9	0.081	23.7	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524HB-G70(T)	BALL	24	0.08	1.92	5500	9.1	0.109	28.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524LS-G70(T)	BALL	24	0.06	1.44	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524MS-G70(T)	BALL	24	0.07	1.68	4800	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524HS-G70(T)	BALL	24	0.08	1.92	5500	9.1	0.109	28.6	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4524HB-G70(S)	BALL	24	0.08	1.92	5700	9.8	0.107	27.4	24	0,6	UL,CUL,TUV,CE	500	24.64
50 X 50 X 15	AD5005MS-D70	S	5	0.24	1.20	4300	12.6	0.113	29.0	55	0	CE		

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED



**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
50 X 50 X 15	AD5012LX-D70	HYPRO	12	0.08	0.96	3600	10.8	0.084	23.6	55	0	CE		
50 X 50 X 15	AD5012MX-D70	HYPRO	12	0.10	1.20	4300	12.6	0.113	29.0	55	0	CE		
50 X 50 X 15	AD5012HX-D70	HYPRO	12	0.14	1.68	4800	14.4	0.141	30.7	55	0,6	CE		
50 X 50 X 15	AD5012UX-D76	HYPRO	12	0.20	2.40	5500	16.5	0.181	33.8	55	6	CE		
50 X 50 X 15	AD5012LB-D70	BALL	12	0.08	0.96	3600	10.8	0.084	23.6	55	0,6	CE		
50 X 50 X 15	AD5012MB-D70	BALL	12	0.10	1.20	4300	12.6	0.113	29.0	55	0,6	CE		
50 X 50 X 15	AD5012MB-D76(S)	1B & 1S	12	0.10	1.20	4500	28.5	0.126	13.4	55	6	CE		
50 X 50 X 15	AD5012HB-D70	BALL	12	0.14	1.68	4800	14.4	0.141	30.7	55	0,6	CE		
50 X 50 X 15	AD5012HB-D70(S)	1B & 1S	12	0.14	1.68	500	15.0	0.152	31.4	55	0,6	CE		
50 X 50 X 15	AD5012UB-D70	BALL	12	0.20	2.40	5500	16.5	0.181	33.8	55	0,6	CE		
50 X 50 X 15	AD5012UB-D70(S)	1B & 1S	12	0.20	2.40	5700	17.1	0.194	34.5	55	0,6	CE		
50 X 50 X 15	AD5012LS-D70	S	12	0.08	0.96	3600	10.8	0.084	23.6	55	0	CE		
50 X 50 X 15	AD5012MS-D70	S	12	0.10	1.20	4300	12.6	0.113	29.0	55	0,6	CE		
50 X 50 X 15	AD5012HS-D76	S	12	0.14	1.68	4800	14.4	0.141	30.7	55	6	CE		
50 X 50 X 15	AD5012US-D76	S	12	0.20	2.40	5500	16.5	0.181	33.8	55	6	CE		
52 X 52 X 9	AD0505MX-RB1	HYPRO	5	0.17	0.85	4800	3.0	0.320	34.0	28	0,3	CE		
52 X 52 X 9	AD0505HX-RB0	HYPRO	5	0.22	1.10	5000	3.2	0.320	34.0	28	0,3	CE		
52 X 52 X 9	AD0505HX-RB1	HYPRO	5	0.22	1.10	5000	9.5	0.100	31.7	28	1	CE		
52 X 52 X 9	AD0505MB-RB1	BALL	5	0.17	0.85	4800	3.0	0.320	34.0	28	1	CE		
52 X 52 X 9	AD0512MX-RB0	HYPRO	12	0.10	1.20	4800	3.0	0.320	34.0	28	0	CE		
52 X 52 X 10	AD0505LX-G70(T)	HYPRO	5	0.12	0.60	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0505MX-G70	HYPRO	5	0.18	0.90	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0505MX-G90	HYPRO	5	0.12	0.60	3300	8.5	0.068	24.9	24	0	UL,CUL,CE		
52 X 52 X 10	AD0505HX-G70(T)	HYPRO	5	0.23	1.15	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0505HX-G90	HYPRO	5	0.15	0.75	3800	9.8	0.082	28.6	50	0	UL,CUL,CE		
52 X 52 X 10	AD0505LB-G70(T)	BALL	5	0.12	0.60	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0505LB-G70(TS)	1B & 1S	5	0.12	0.60	3900	9.4	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0505MB-G70	BALL	5	0.14	0.70	4600	10.5	0.100	24.0	18	0	CE		
52 X 52 X 10	AD0505MB-G70(T)	BALL	5	0.18	0.90	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0505MB-G70(TS)	1B & 1S	5	0.18	0.90	4500	10.8	0.100	25.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0505HB-G70(T)	BALL	5	0.23	1.15	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0505HB-G90	BALL	5	0.15	0.75	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
52 X 52 X 10	AD0505HB-G96	BALL	5	0.15	0.75	3800	9.8	0.082	28.6	24	6	CE		
52 X 52 X 10	AD0505LS-G70	S	5	0.12	0.60	3700	9.0	0.060	20.0	18	0	TUV,CE		
52 X 52 X 10	AD0505LS-G76	S	5	0.12	0.60	3700	9.0	0.060	20.0	18	0	UL,CUL,TUV,CE		
52 X 52 X 10	AD0505MS-G70(T)	S	5	0.18	0.90	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0505MS-G90	S	5	0.12	0.60	3300	8.5	0.068	24.9	24	0	UL,CUL,CE		
52 X 52 X 10	AD0505HS-G70	S	5	0.18	0.90	5200	11.9	0.130	28.0	18	0	UL,CUL,TUV,CE		
52 X 52 X 10	AD0505HS-G70(T)	S	5	0.23	1.15	500	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512LX-G70(T)	HYPRO	12	0.10	0.72	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512MX-G70(T)	HYPRO	12	0.07	0.84	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512MX-G72	HYPRO	12	0.10	1.20	4300	10.5	0.100	24.0	18	2	CE		
52 X 52 X 10	AD0512MX-G90	HYPRO	12	0.07	0.84	3300	8.5	0.068	24.9	50	0	UL,CUL,CE		

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
52 X 52 X 10	AD0512HX-G70	HYPRO	12	0.09	1.08	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512HX-G76(UT	HYPRO	12	0.09	1.08	5600	12.4	0.112	26.4	18	6	CE		
52 X 52 X 10	AD0512HX-G90	HYPRO	12	0.08	0.96	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
52 X 52 X 10	AD0512LB-G70	BALL	12	0.06	0.72	3900	9.4	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512LB-G72	BALL	12	0.09	1.08	3700	9.0	0.060	20.0	18	2	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512LB-G73	BALL	12	0.06	0.72	3900	9.4	0.067	20.0	18	3	CE		
52 X 52 X 10	AD0512MB-G70(S)	Bor1B1S	12	0.07	0.84	4600	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512MB-G73	BALL	12	0.10	1.20	4300	10.5	0.100	24.0	18	3	CE		
52 X 52 X 10	AD0512MB-G90(S)	Bor1B1S	12	0.07	0.84	3300	8.5	0.068	24.9	24	0	UL,CUL,CE		
52 X 52 X 10	AD0512MB-G96(S)	1B & 1S	12	0.07	0.84	3300	8.5	0.068	24.9	24	6	CE		
52 X 52 X 10	AD0512HB-G70(S)	Bor1B1S	12	0.09	1.08	5200	11.9	0.130	28.0	18	0	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512HB-G72	BALL	12	0.11	1.32	5000	11.2	0.130	26.0	18	2	CE		
52 X 52 X 10	AD0512HB-G73(S)	1B & 1S	12	0.09	1.08	5200	11.9	0.130	28.0	18	3	CE		
52 X 52 X 10	AD0512HB-G76	BALL	12	0.09	1.08	5000	11.2	0.130	26.0	18	6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512HB-G90(S)	Bor1B1S	12	0.08	0.96	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
52 X 52 X 10	AD0512LS-G70	S	12	0.06	0.72	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512MS-G70	S	12	0.07	0.84	4600	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512MS-G90	S	12	0.08	0.96	3300	8.5	0.068	24.9	24	0,6	UL,CUL,CE		
52 X 52 X 10	AD0512HS-G70	S	12	0.09	1.08	5200	11.9	0.130	28.0	18	0	CE		
52 X 52 X 10	AD0512HS-G70(T)	S	12	0.09	1.08	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512HS-G70(U)	S	12	0.09	1.08	5600	12.4	0.112	26.4	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0512HS-G90	S	12	0.08	0.96	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
52 X 52 X 10	AD0512HS-G96	S	12	0.08	0.96	3800	9.8	0.082	28.6	24	6	CE		
52 X 52 X 10	AD0524LX-G70	HYPRO	24	0.07	1.68	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0524MX-G70	HYPRO	24	0.08	1.92	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0524HX-G70	HYPRO	24	0.09	2.16	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0524LB-G70	BALL	24	0.07	1.68	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0524LB-G70(S)	1B & 1S	24	0.07	1.68	3900	9.4	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0524MB-G70(S)	Bor1B1S	24	0.10	2.40	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0524MB-G90	BALL	24	0.06	1.44	3300	8.3	1.650	27.5	50	0	CE		
52 X 52 X 10	AD0524HB-G70	BALL	24	0.11	2.64	5000	11.2	0.130	26.0	18	0,6	CE		
52 X 52 X 10	AD0524HB-G70(S)	1B & 1S	24	0.09	2.16	5200	11.8	0.130	27.0	18	0,6	CE		
52 X 52 X 10	AD0524HB-G90	BALL	24	0.09	2.16	3800	9.8	0.082	28.6	50	0	CE		
52 X 52 X 10	AD0524LS-G70	S	24	0.07	1.68	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 10	AD0524MS-G70	S	24	0.08	1.92	4300	10.5	0.100	24.0	18	0	UL,CUL,TUV,CE		
52 X 52 X 10	AD0524HS-G70	S	24	0.09	2.16	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 15	AD0505HX-D71	HYPRO	5	0.26	1.30	4600	12.0	0.166	28.7	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0505MB-D71	BALL	5	0.16	0.80	3700	9.7	0.106	22.6	55	1	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HB-D70	BALL	5	0.20	1.00	4600	12.0	0.166	28.7	36	0	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HB-D71	BALL	5	0.26	1.30	4600	12.0	0.166	28.7	36	1	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505MS-D71	S	5	0.16	0.80	3700	9.7	0.106	22.6	36	1	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HS-D70	S	5	0.20	1.00	4600	12.0	0.166	28.7	55	0	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HS-D71	S	5	0.26	1.30	4600	12.0	0.166	28.7	36	1	CUL,UL,TUV,CE	480	46.20

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
52 X 52 X 15	AD0512MX-D70	HYPRO	12	0.09	1.08	3700	9.7	0.106	22.6	55	0	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512MX-D71	HYPRO	12	0.09	1.08	3700	9.7	0.106	22.6	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512MX-D72	HYPRO	12	0.09	1.08	3700	9.7	0.106	22.6	36	2	CE+	480	46.20
52 X 52 X 15	AD0512HX-D71	HYPRO	12	0.10	1.20	4600	12.0	0.166	28.7	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512HX-D76	HYPRO	12	0.10	1.20	4600	12.0	0.166	28.7	36	6	CE	480	46.20
52 X 52 X 15	AD0512LB-D70	BALL	12	0.06	0.72	2800	6.3	0.059	14.4	55	0	CE	480	46.20
52 X 52 X 15	AD0512MB-D70	BALL	12	0.09	1.08	3700	9.7	0.106	22.6	55	0,6	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512MB-D71(S)	Bor1B1S	12	0.09	1.08	3700	9.7	0.106	22.6	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512MB-D72	BALL	12	0.09	1.08	3700	9.7	0.106	22.6	36	2,3	CE	480	46.20
52 X 52 X 15	AD0512HB-D70	BALL	12	0.10	1.20	4600	12.0	0.166	28.7	55	0	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512HB-D71	Bor1B1S	12	0.10	1.20	4600	12.0	0.166	28.7	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512HB-D73	Bor1B1S	12	0.10	1.20	4600	12.0	0.166	28.7	36	3,6	CE	480	46.20
53 X 52 X 15	AD0512UB-D71	BALL	12	0.11	1.32	5300	13.0	0.200	35.0	36	1	CE	480	46.20
54 X 52 X 15	AD0512UB-D72	BALL	12	0.11	1.32	5300	12.5	0.200	33.3	36	2	CE	480	46.20
52 X 52 X 15	AD0512MS-D70	S	12	0.09	1.08	3700	9.7	0.106	22.6	55	0	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512MS-D71	S	12	0.09	1.08	3700	9.7	0.106	22.6	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512HS-D70	S	12	0.10	1.20	4600	12.0	0.166	28.7	55	0	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512HS-D71	S	12	0.10	1.20	4600	12.0	0.166	28.7	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512HS-D76	S	12	0.10	1.20	4600	12.0	0.166	28.7	36	6	CE	480	46.20
52 X 52 X 15	AD0524HX-D71	HYPRO	24	0.08	1.92	4600	12.0	0.166	28.7	36	1	CE	480	46.20
52 X 52 X 15	AD0524HB-D71	BALL	24	0.08	1.92	4600	12.0	0.166	28.7	55	1	CE	480	46.20
52 X 52 X 15	AD0524HS-D71	S	24	0.08	1.92	4600	12.0	0.166	28.7	36	1	CE	480	46.20
60 X 60 X 10	AD0605LX-G90	HYPRO	5	0.15	0.75	3000	11.9	0.060	23.1	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0605LX-G70	HYPRO	5	0.13	0.65	3500	10.0	0.060	23.0	30	0	CE	480	35.50
60 X 60 X 10	AD0605MX-G70	HYPRO	5	0.15	0.75	4200	12.0	0.090	28.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0605LB-G70	BALL	5	0.13	0.65	3500	10.0	0.060	23.0	30	0	CE	480	35.50
60 X 60 X 10	AD0605MB-G70	BALL	5	0.15	0.75	4200	12.0	0.090	28.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0605HB-G90	BALL	5	0.27	1.35	4200	16.6	0.115	32.8	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0605LS-G70	S	5	0.13	0.65	3500	10.0	0.060	23.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0605LS-G90	S	5	0.14	0.70	3000	11.9	0.060	23.1	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0605MS-G70	S	5	0.15	0.75	4200	12.0	0.090	28.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0605HS-G90	S	5	0.27	1.35	4200	16.6	0.115	32.8	30	0	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612LX-G70	HYPRO	12	0.11	1.32	3500	11.7	0.050	23.0	30	0	TUV,CE	480	35.50
60 X 60 X 10	AD0612LX-G76	HYPRO	12	0.11	1.32	3500	11.7	0.050	23.0	30	6	CE	480	35.50
60 X 60 X 10	AD0612MX-G70	HYPRO	12	0.13	1.56	4200	12.0	0.090	28.0	23	0,6	TUV,CE	480	35.50
60 X 60 X 10	AD0612MX-G90	HYPRO	12	0.12	1.44	3600	14.1	0.086	28.5	30	0,6	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0612MX-G96	HYPRO	12	0.12	1.44	3600	14.1	0.086	28.5	30	6	CE	480	35.50
60 X 60 X 10	AD0612HX-G70	HYPRO	12	0.15	1.80	4900	14.5	0.108	32.0	23	0,6	TUV,CE	480	35.50
60 X 60 X 10	AD0612HX-G90	HYPRO	12	0.14	1.68	4200	16.6	0.115	32.8	30	0	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612LB-G70(S)	Bor1B1S	12	0.11	1.32	3500	11.7	0.050	23.0	30	0,6	TUV,CE	480	35.50
60 X 60 X 10	AD0612LB-G90	BALL	12	0.11	1.32	3000	11.9	0.060	23.1	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0612LB-G96	BALL	12	0.11	1.32	3000	11.9	0.060	23.1	30	6	TUV,CE	480	35.50
60 X 60 X 10	AD0612MB-G70(S)	Bor1B1S	12	0.13	1.56	4200	12.0	0.090	28.0	23	0,6	TUV,CE	480	35.50

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
60 X 60 X 10	AD0612MB-G90(S)	Bor1B1S	12	0.12	1.44	3600	14.1	0.086	28.5	30	0,6	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612MB-GA6	BALL	12	0.19	2.28	4000	17.3	0.127	31.7	30	6	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612HB-G70(S)	Bor1B1S	12	0.15	1.80	4900	14.5	0.108	32.0	23	0,6	TUV,CE	480	35.50
60 X 60 X 10	AD0612HB-G90(S)	Bor1B1S	12	0.14	1.68	4200	16.6	0.115	32.8	30	0	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612HB-G96(S)	1B & 1S	12	0.14	1.68	4200	16.6	0.115	32.8	30	6	CE	480	35.50
60 X 60 X 10	AD0612HB-GA6(S)	1B & 1S	12	0.25	3.00	4600	21.0	0.165	35.8	30	6	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612LS-G70	S	12	0.11	1.32	3500	11.7	0.050	23.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0612LS-G90	S	12	0.11	1.32	300	11.9	0.060	23.1	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0612LS-G96	S	12	0.11	1.32	300	11.9	0.060	23.1	30	6	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612MS-G70	S	12	0.13	1.56	4200	12.0	0.090	28.0	23	0,6	TUV,CE	480	35.50
60 X 60 X 10	AD0612HS-G90	S	12	0.15	1.80	4900	14.5	0.108	32.0	23	0	TUV,CE	480	35.50
60 X 60 X 10	AD0612HS-G96	S	12	0.15	1.80	4900	14.5	0.108	32.0	23	6	UL,CUL,TUV,CE	480	35.50
60 X 60 X 10	AD0612HS-G90	S	12	0.14	1.68	4200	16.6	0.115	32.8	30	0	UL,CUL,CE	480	35.50
60 X 60 X 10	AD0612HS-G96	S	12	0.14	1.68	4200	16.6	0.115	32.8	30	6	CE	480	35.50
60 X 60 X 15	AD0605LB-D70GL	BALL	5	0.20	1.00	3500	12.0	0.010	27.2	38	0,1	CE	300	25.70
60 X 60 X 15	AD0605MB-D71GL	BALL	5	0.25	1.25	3900	14.2	0.118	28.8	38	1,2,3	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0605HB-D70GL	BALL	5	0.25	1.25	4500	15.7	0.163	33.2	38	0	CE	300	25.70
60 X 60 X 15	AD0605HB-D71GL	BALL	5	0.37	1.85	4500	16.6	0.152	32.4	38	1,2	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0605HB-D73GL	BALL	5	0.37	1.85	4500	16.6	0.152	32.4	38	3	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0605MS-D71GL	S	5	0.25	1.25	3900	14.2	0.118	28.8	38	1	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0605HS-D70GL	S	5	0.25	1.25	4500	15.7	0.163	33.2	38	0	CE	300	25.70
60 X 60 X 15	AD0605HS-D71GL	S	5	0.37	1.85	4500	16.6	0.152	32.4	38	1	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612DX-D70GL	HYPRO	12	0.07	0.84	3100	12.2	0.086	24.9	38	0,6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612LX-D70GL	HYPRO	12	0.09	1.08	3500	12.0	0.010	27.2	38	0	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612LX-D76GL	HYPRO	12	0.09	1.08	3500	12.0	0.010	27.2	38	6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612MX-D70GL	HYPRO	12	0.11	1.32	3900	14.2	0.118	28.8	38	0,1,2,3	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612MX-D76GL	B,S,or X	12	0.11	1.32	3900	14.2	0.118	28.8	38	6	CE	300	25.70
60 X 60 X 15	AD0612HX-D70GL	HYPRO	12	0.13	1.56	4500	16.6	0.152	32.4	38	0,1,6	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612HX-D72GL	HYPRO	12	0.13	1.56	4500	16.6	0.152	32.4	38	2,3	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612DB-D70GL	BALL	12	0.07	0.84	3100	12.2	0.086	24.9	38	0,2	CE	300	25.70
60 X 60 X 15	AD0612DB-D70(T)	BALL	12	0.07	0.84	3100	10.7	0.086	23.8	38	0,6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612LB-D70GL	BALL	12	0.09	1.08	3500	12.0	0.010	27.2	38	0,1	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612LB-D76GL	BALL	12	0.09	1.08	3500	12.0	0.010	27.2	38	6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612MB-D70GL	BALL	12	0.11	1.32	3900	14.2	0.118	28.8	38	0,1,3	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612MB-D76GL	BALL	12	0.11	1.32	3900	14.2	0.118	28.8	38	6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0612HB-D70GL	BALL	12	0.13	1.56	4500	16.6	0.152	32.4	38	0,1,2,3,6	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612UB-D71GL	BALL	12	0.16	1.92	5100	18.0	0.176	39.3	38	1,2,6	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612UB-D73GL	BALL	12	0.16	1.92	5100	18.0	0.176	39.3	38	3	CE	300	25.70
60 X 60 X 15	AD0612UB-D96	BALL	12	0.31	3.72	6000	28.5	0.231	40.4	38	6	CE	300	25.70
60 X 60 X 15	AD0612LS-D70GL	S	12	0.09	1.08	3500	12.0	0.010	27.2	38	0,1	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612MS-D70GL	S	12	0.11	1.32	3900	14.2	0.118	28.8	38	0,1,6	UL,CUL,TUV,CE	300	25.70
60 X 60 X 15	AD0612MS-D72GL	S	12	0.11	1.32	3900	14.2	0.118	28.8	38	2	CE	300	25.70
60 X 60 X 15	AD0612HS-D70GL	S	12	0.13	1.56	4500	16.6	0.152	32.4	38	0,1,6	UL,CUL,TUV,CE	300	25.70

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
60 X 60 X 15	AD0612HS-D73GL	S	12	0.13	1.56	4500	16.6	0.152	32.4	38	3	CE	300	25.70
60 X 60 X 15	AD0624LX-D70GL	HYPRO	24	0.05	1.20	3500	12.0	0.010	27.2	38	0	CE	300	25.70
60 X 60 X 15	AD0624MX-D71GL	HYPRO	24	0.07	1.68	3900	15.0	0.138	30.7	38	1	CE	300	25.70
60 X 60 X 15	AD0624HX-D71GL	HYPRO	24	0.09	2.16	4500	17.0	0.173	33.3	38	1	TUV,CE	300	25.70
60 X 60 X 15	AD0624MB-D70GL	BALL	24	0.07	1.68	3900	15.0	0.138	30.7	38	0	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624MB-D71GL	BALL	24	0.07	1.68	3900	15.0	0.138	30.7	38	1	CE	300	25.70
60 X 60 X 15	AD0624MB-D72GL	BALL	24	0.07	1.68	3900	15.0	0.138	30.7	38	2	TUV,CE	300	25.70
60 X 60 X 15	AD0624HB-D70GL	BALL	24	0.09	2.16	4500	17.0	0.173	33.3	38	0,6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624HB-D71GL	BALL	24	0.09	2.16	4500	17.0	0.173	33.3	38	1,2	TUV,CE	300	25.70
60 X 60 X 15	AD0624HB-D73GL	BALL	24	0.09	2.16	4500	17.0	0.173	33.3	38	3	CE	300	25.70
60 X 60 X 15	AD0624LS-D70GL	S	24	0.05	1.20	3500	13.0	0.110	27.2	38	0	CE	300	25.70
60 X 60 X 15	AD0624MS-D70GL	S	24	0.07	1.68	3900	15.0	0.138	30.7	38	0	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624MS-D71GL	S	24	0.07	1.68	3900	15.0	0.138	30.7	38	1	TUV,CE	300	25.70
60 X 60 X 15	AD0624HS-D70GL	S	24	0.09	2.16	4500	17.0	0.173	33.3	38	0	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624HS-D71GL	S	24	0.09	2.16	4500	17.0	0.173	33.3	38	1	TUV,CE	300	25.70
60 X 60 X 20	AD0605HX-C70GL	HYPRO	5	0.25	1.25	4500	16.3	0.156	29.8	49	0	CE	300	40.00
60 X 60 X 20	AD0605MB-C70GL	BALL	5	0.24	1.20	3900	14.5	0.111	25.7	49	0	CE	300	40.00
60 X 60 X 20	AD0605HB-C70GL	BALL	5	0.30	1.50	4500	16.4	0.139	29.7	49	0	TUV,CE	300	40.00
60 X 60 X 20	AD0605HB-C72GL	BALL	5	0.30	1.50	4500	16.4	0.139	29.7	49	2	CE	300	40.00
60 X 60 X 20	AD0605HS-C70GL	HYPRO	5	0.30	1.50	4500	16.4	0.139	29.7	49	0	CE	300	40.00
60 X 60 X 20	AD0612DX-C76GL	HYPRO	12	0.07	0.84	3000	10.7	0.054	18.4	49	6	CE	300	40.00
60 X 60 X 20	AD0612LX-C70GL	HYPRO	12	0.08	0.96	3500	13.3	0.096	21.6	49	0,6	UL,CSA,CE	300	40.00
60 X 60 X 20	AD0612MX-C70GL	HYPRO	12	0.13	1.56	3900	14.5	0.111	25.7	49	0	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612MX-C72GL	HYPRO	12	0.13	1.56	3900	14.5	0.111	25.7	49	2,3,6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612HX-C70GL	HYPRO	12	0.16	1.92	4500	16.4	0.139	29.7	49	0	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612HX-C72GL	HYPRO	12	0.16	1.92	4500	16.4	0.139	29.7	49	2	CE	300	40.00
60 X 60 X 20	AD0612HX-C73GL	HYPRO	12	0.16	1.92	4500	16.4	0.139	29.7	49	3,6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612DB-C76GL	BALL	12	0.07	0.84	3000	10.7	0.054	18.4	49	6	CE	300	40.00
60 X 60 X 20	AD0612LB-C70GL	BALL	12	0.08	0.96	3500	13.3	0.096	21.6	49	0,1	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612LB-C73GL	BALL	12	0.08	0.96	3500	13.3	0.096	21.6	49	3	CE	300	40.00
60 X 60 X 20	AD0612LB-C76GL	BALL	12	0.08	0.96	3500	13.3	0.096	21.6	49	6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612MB-C70GL	BALL	12	0.13	1.56	3900	14.5	0.111	25.7	49	0,3	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612MB-C72GL	BALL	12	0.13	1.56	3900	14.5	0.111	25.7	49	2,6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612HB-C70GL	BALL	12	0.16	1.92	4600	16.4	0.139	29.7	49	0,1,6	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612HB-C72GL	BALL	12	0.16	1.92	4600	16.4	0.139	29.7	49	2,3	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612UB-C71GL	BALL	12	0.17	2.04	5100	18.7	0.160	34.6	49	1	CE	300	40.00
60 X 60 X 20	AD0612LS-C70GL	S	12	0.08	0.96	3500	13.3	0.096	21.6	49	0	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612LS-C71GL	S	12	0.08	0.96	3500	13.3	0.096	21.6	49	1	UL,CUL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612LS-C76GL	S	12	0.08	0.96	3500	13.3	0.096	21.6	49	6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612MS-C70GL	S	12	0.13	1.56	3900	14.5	0.111	25.7	49	0,1,6	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612MS-C72GL	S	12	0.13	1.56	3900	14.5	0.111	25.7	49	2,3	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612HS-C70GL	BALL	12	0.16	1.92	4500	16.4	0.139	29.7	49	0,1,6	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612HS-C72GL	BALL	12	0.16	1.92	4500	16.4	0.139	29.7	49	2,3	UL,CUL,CE	300	40.00

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
60 X 60 X 20	AD0624MX-C70GL	HYPRO	24	0.08	1.92	3900	14.5	0.111	25.7	49	0	UL,CUL,TUV,CE	300	40.00
60 X 60 X 20	AD0624HX-C70GL	HYPRO	24	0.09	2.16	4500	16.4	0.139	29.7	49	0	UL,CUL,TUV,CE	300	40.00
60 X 60 X 20	AD0624MB-C70GL	BALL	24	0.08	1.92	3900	14.5	0.111	25.7	49	0	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0624HB-C70GL	BALL	24	0.09	2.16	4500	16.4	0.139	29.7	49	0,1	UL,CUL,TUV,CE	300	40.00
60 X 60 X 20	AD0624HB-C70(T)	BALL	24	0.09	2.16	4500	16.4	0.139	29.7	49	0,6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0624MS-C70GL	S	24	0.08	1.92	3900	14.5	0.111	25.7	49	0	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0624HS-C70GL	S	24	0.09	2.16	4500	16.4	0.139	29.7	49	0	UL,CUL,TUV,CE	300	40.00
60 X 60 X 25	AD0605MX-A70GL	HYPRO	5	0.32	1.60	3500	18.0	0.118	24.0	68	0	UL,CUL,CE	300	44.00
60 X 60 X 25	AD0605MB-A70GL	BALL	5	0.32	1.60	3500	18.0	0.188	24.0	68	0	UL,TUV,CE	300	40.00
60 X 60 X 25	AD0605HB-A70GL	BALL	5	0.45	2.25	4500	23.2	0.188	32.3	68	0,2	TUV,CE	300	44.00
60 X 60 X 25	AD0605HB-A73GL	BALL	5	0.45	2.25	4500	23.2	0.188	32.3	68	3	CE	300	44.00
60 X 60 X 25	AD0605MS-A70GL	S	5	0.32	1.60	3500	18.0	0.188	24.0	68	0	UL,CUL,CE	300	40.00
60 X 60 X 25	AD0605HS-A71GL	S	5	0.60	3.00	4500	23.2	0.188	32.3	68	1	CE	300	40.00
60 X 60 X 25	AD0612LX-A70GL	HYPRO	12	0.08	0.96	2500	13.2	0.063	16.1	68	0	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612LX-A72GL	HYPRO	12	0.08	0.96	2500	13.2	0.063	16.1	68	2,3	UL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612MX-A70GL	HYPRO	12	0.14	1.68	3500	18.0	0.188	24.0	68	0,6	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612MX-A73GL	HYPRO	12	0.14	1.68	3500	18.0	0.188	24.0	68	3	UL,CUL,TUV,CE	300	44.00
60 X 60 X 25	AD0612HX-A70GL	HYPRO	12	0.23	2.76	4500	23.2	0.188	32.3	68	0,1,2	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612HX-A73GL	HYPRO	12	0.23	2.76	4500	23.2	0.188	32.3	68	3,6	UL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612UX-A70GL	HYPRO	12	0.25	3.00	5000	28.3	0.250	37.0	68	0	CE	300	44.00
60 X 60 X 25	AD0612UX-A71GL	HYPRO	12	0.27	3.24	5300	28.3	0.250	37.0	68	1	UL,CUL,CE	300	44.00
60 X 60 X 25	AD0612UX-A72GL	HYPRO	12	0.27	3.24	5300	28.3	0.250	37.0	68	2,3	CE	300	44.00
60 X 60 X 25	AD0612LB-A70GL	BALL	12	0.08	0.96	2500	13.2	0.063	16.1	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612LB-A70(T)	BALL	12	0.08	0.96	2300	10.7	0.041	14.5	68	0,6	UL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612MB-A70GL	BALL	12	0.14	1.68	3500	18.0	0.118	24.0	68	0	UL,CUL,TUV,CE	300	44.00
60 X 60 X 25	AD0612MB-A71GL	BALL	12	0.14	1.68	3500	18.0	0.118	24.0	68	1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612MB-A72GL	BALL	12	0.14	1.68	3500	18.0	0.118	24.0	68	2,3	UL,CUL,TUV,CE	300	44.00
60 X 60 X 25	AD0612MB-A76GL	BALL	12	0.14	1.68	3500	18.0	0.118	24.0	68	6	CE	300	44.00
60 X 60 X 25	AD0612HB-A70GL	BALL	12	0.23	2.76	4500	23.2	0.188	32.3	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612HB-A72GL	BALL	12	0.23	2.76	4500	23.2	0.188	32.3	68	2,3,6	UL,CUL,TUV,CE	300	44.00
60 X 60 X 25	AD0612UB-A70GL	BALL	12	0.25	3.00	5000	28.3	0.250	37.0	68	0	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612UB-A71GL	BALL	12	0.25	3.00	5000	28.3	0.250	37.0	68	1	UL,CUL,TUV,CE	300	44.00
60 X 60 X 25	AD0612UB-A72GL	BALL	12	0.25	3.00	5000	28.3	0.250	37.0	68	2,3	UL,CUL,CE	300	44.00
60 X 60 X 25	AD0612UB-A76GL	BALL	12	0.25	3.00	5000	28.3	0.250	37.0	68	6	CE	300	44.00
60 X 60 X 25	AD0612XB-A71GL	BALL	12	0.38	4.56	6100	31.4	0.320	42.9	68	1,2,3	CE	300	44.00
60 X 60 X 25	AD0612XB-A72/UP	BALL	12	0.65	7.80	7400	38.1	0.500	47.8	68	2	CE	300	44.00
60 X 60 X 25	AD0612LS-A70GL	S	12	0.08	0.96	2500	13.2	0.063	16.1	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612LS-A73GL	S	12	0.08	0.96	2500	13.2	0.063	16.1	68	3	UL,CUL,TUV,CE	300	44.00
60 X 60 X 25	AD0612LS-A76GL	S	12	0.08	0.96	2500	13.2	0.063	16.1	68	6	CE	300	44.00
60 X 60 X 25	AD0612MS-A70GL	S	12	0.14	1.68	3500	18.0	0.118	24.0	68	0	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612MS-A76GL	S	12	0.14	1.68	3500	18.0	0.118	24.0	68	6	TUV,CE	300	44.00
60 X 60 X 25	AD0612HS-A70GL	S	12	0.23	2.76	4500	23.2	0.188	32.3	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0612HS-A72GL	S	12	0.23	2.76	4500	23.2	0.188	32.3	68	2,6	CE	300	44.00

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
60 X 60 X 25	AD0612HS-A73GL	S	12	0.23	2.76	4500	23.2	0.188	32.3	68	3	UL,CE	300	44.00
60 X 60 X 25	AD0612US-A70GL	S	12	0.25	3.00	5000	28.3	0.250	37.0	68	0,6	CE	300	44.00
60 X 60 X 25	AD0612US-A71GL	S	12	0.27	3.24	5300	28.3	0.250	37.0	68	1	TUV,CE	300	44.00
60 X 60 X 25	AD0612US-A73GL	S	12	0.27	3.24	5300	28.3	0.250	37.0	68	3	CE	300	44.00
60 X 60 X 25	AD0624MX-A70GL	HYPRO	24	0.08	1.92	3500	18.0	0.118	24.0	68	0	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624MX-A76GL	HYPRO	24	0.08	1.92	3500	18.0	0.118	24.0	68	6	CE	300	44.00
60 X 60 X 25	AD0624HX-A70GL	HYPRO	24	0.15	3.60	4500	23.2	0.188	32.3	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624HX-A72GL	HYPRO	24	0.15	3.60	4500	23.2	0.188	32.3	68	2	CE	300	44.00
60 X 60 X 25	AD0624UX-A71GL	HYPRO	24	0.16	3.84	5000	28.3	0.250	37.0	68	1,2	CE	300	44.00
60 X 60 X 25	AD0624LB-A70GL	BALL	24	0.05	1.20	2500	16.0	0.079	16.1	68	0	UL,CUL,CE	300	44.00
60 X 60 X 25	AD0624MB-A70GL	BALL	24	0.08	1.92	3500	18.0	0.118	24.0	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624HB-A70GL	BALL	24	0.15	3.60	4500	23.2	0.188	32.3	68	0	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624HB-A71GL	BALL	24	0.15	3.60	4500	23.2	0.188	32.3	68	1	UL,CSA,TUV,CE	300	44.00
60 X 60 X 25	AD0624HB-A72GL	BALL	24	0.15	3.60	4500	23.2	0.188	32.3	68	2,3	UL,CUL,CE	300	44.00
60 X 60 X 25	AD0624HB-A76GL	BALL	24	0.15	3.60	4500	23.2	0.188	32.3	68	6	CE	300	44.00
60 X 60 X 25	AD0624UB-A70GL	BALL	24	0.16	3.84	5000	26.5	0.204	38.1	68	0,1,2,3	CE	300	44.00
60 X 60 X 25	AD0624LS-A70GL	S	24	0.05	1.20	2500	16.0	0.079	16.1	68	0	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624MS-A70GL	S	24	0.08	1.92	3500	18.0	0.118	24.0	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624MS-A72GL	S	24	0.08	1.92	3500	18.0	0.118	24.0	68	2	CE	300	44.00
60 X 60 X 25	AD0624HS-A70GL	S	24	0.15	3.60	4500	23.2	0.188	32.3	68	0,1	UL,CUL,TUV,CSA,CE	300	44.00
60 X 60 X 25	AD0624HS-A72GL	S	24	0.15	3.60	4500	23.2	0.188	32.3	68	2	CE	300	44.00
60 X 60 X 25	AD0624HS-A73GL	S	24	0.15	3.60	4500	23.2	0.188	32.3	68	3	UL,CE	300	44.00
60 X 60 X 25	AD0624US-A71GL	S	24	0.16	3.84	5000	28.3	0.250	37.0	68	1	TUV,CE	300	44.00
70 X 70 X 15	AD0712HB-DA6	BALL	12	0.27	3.24	4200	32.3	0.164	37.3	54	6	CE		
70 X 70 X 15	AD0712UB-DA6	BALL	12	0.30	3.60	4500	34.8	0.193	43.4	54	6	CE		
70 X 70 X 25	AD0705MX-A76GL	HYPRO	5	0.30	1.50	3800	31.0	0.176	32.0	61	6	CE		
70 X 70 X 25	AD0705MB-A76GL	BALL	5	0.30	1.50	3800	31.0	0.176	32.0	61	6	CE		
70 X 70 X 25	AD0712-LX-A70GL	HYPRO	12	0.12	1.44	3300	27.0	0.134	28.0	61	0	CE		
70 X 70 X 25	AD0712-MX-A70GL	HYPRO	12	0.16	1.92	3800	31.0	0.176	32.0	61	0	CE		
70 X 70 X 25	AD0712-HX-A70GL	HYPRO	12	0.19	2.28	4200	34.0	0.217	35.5	61	0	CE		
70 X 70 X 25	AD0712LB-A70GL	BALL	12	0.12	1.44	3300	27.0	0.134	28.0	61	0	CE		
70 X 70 X 25	AD0712MB-A70GL	BALL	12	0.16	1.92	3800	31.0	0.176	32.0	61	0,6	CE		
70 X 70 X 25	AD0712HB-A70GL	BALL	12	0.19	2.28	4200	34.0	0.217	35.5	61	0,6	CE		
70 X 70 X 25	AD0712UB-A76GL	BALL	12	0.24	2.88	4500	38.4	0.239	37.8	61	6	CE		
70 X 70 X 25	AD0712LS-A70GL	S	12	0.12	1.44	3300	27.0	0.134	28.0	61	0	CE		
70 X 70 X 25	AD0712MS-A70GL	S	12	0.16	1.92	3800	31.0	0.176	32.0	61	0	CE		
70 X 70 X 25	AD0712HS-A70GL	S	12	0.19	2.28	4200	34.0	0.217	35.5	61	0,6	CE		
70 X 70 X 25	AD0712US-A76GL	S	12	0.24	2.88	4500	38.4	0.239	37.8	61	6	CE		
70 X 70 X 25	AD0724HB-A70GL	BALL	24	0.13	3.12	4200	34.0	0.218	35.5	61	0	CE		
75 X 75 X 30	AD7512MX	HYPRO	12	0.20	2.40	2600	7.8	0.228	34.9	80	0	CE		
75 X 75 X 30	AD7512HX	HYPRO	12	0.30	3.60	3000	10.3	0.350	38.5	80	1	UL,CUL,CE		
75 X 75 X 30	AD7512HX	HYPRO	12	0.30	3.60	3000	10.3	0.350	38.5	80	3	CE		
75 X 75 X 30	AD7512UX	HYPRO	12	0.55	6.60	4200	13.1	0.822	44.7	80	0,2,3	CE		

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
75 X 75 X 30	AD7512LB	BALL	12	0.11	1.32	2200	6.9	0.190	29.0	80	0	CE		
75 X 75 X 30	AD7512MB	BALL	12	0.15	1.80	2600	7.8	0.228	34.9	80	0,3	UL,CUL,CE		
75 X 75 X 30	AD7512HB	BALL	12	0.24	2.88	3000	10.3	0.350	38.5	80	0,2,3	UL,CUL,CE		
75 X 75 X 30	AD7512UB	BALL	12	0.52	6.24	4200	13.1	0.822	44.7	80	0,2,3	CE		
75 X 75 X 30	AD7512MS	S	12	0.20	2.40	2600	7.8	0.228	34.9	80	0	UL,CUL,CE		
75 X 75 X 30	AD7512HS	S	12	0.30	3.60	3000	10.3	0.350	38.5	80	0,2	UL,CUL,CE		
75 X 75 X 30	AD7524MX	HYPRO	24	0.14	3.36	2600	7.8	0.228	34.9	80	0	CE		
75 X 75 X 30	AD7524HX	HYPRO	24	0.20	4.80	3000	10.3	0.350	38.5	80	0	CE		
75 X 75 X 30	AD7524UX	HYPRO	24	0.27	6.48	4200	13.1	0.822	44.7	80	0	CE		
75 X 75 X 30	AD7524MB	BALL	24	0.14	3.36	2600	7.8	0.228	34.9	80	0	UL,CUL,CE		
75 X 75 X 30	AD7524HB	BALL	24	0.16	3.84	3000	10.3	0.350	38.5	80	0	UL,CUL,CE		
75 X 75 X 30	AD7524UB	BALL	24	0.27	6.48	4200	13.1	0.822	44.7	80	0	CE		
75 X 75 X 30	AD7524LS	S	24	0.12	2.88	2200	6.9	0.190	29.0	80	0	CE		
75 X 75 X 30	AD7524MS	S	24	0.14	3.36	2600	7.8	0.228	34.9	80	0	UL,CUL,CE		
75 X 75 X 30	AD7524HS	S	24	0.16	3.84	3000	10.3	0.350	38.5	80	0	UL,CUL,CE		
75 X 75 X 30	AD7524US	S	24	0.27	6.48	4200	13.1	0.822	44.7	80	0	CE		
80 X 80 X 15	AD0805MX-D71	HYPRO	5	0.24	1.20	2440	22.4	0.083	26.0	63	1	UL,CUL,CE	200	32.34
80 X 80 X 15	AD0805HX-D71	HYPRO	5	0.43	2.15	3200	29.9	0.129	31.4	63	1	UL,CUL,CE	200	32.34
80 X 80 X 15	AD0805MB-D71	BALL	5	0.24	1.20	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.24
80 X 80 X 15	AD0805HB-D70	BALL	5	0.40	2.00	3200	29.9	0.129	33.4	63	0	CE	200	32.34
80 X 80 X 15	AD0805HB-D71	BALL	5	0.43	2.15	3200	29.9	0.129	31.4	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0805MS-D71	S	5	0.24	1.20	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0805HS-D70	S	5	0.40	2.00	3200	29.9	0.129	33.4	63	0	CE	200	32.34
80 X 80 X 15	AD0805HS-D71	S	5	0.43	2.15	3200	29.9	0.129	31.4	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812LX-D70	HYPRO	12	0.09	1.08	2000	20.0	0.050	19.6	63	0	UL,CUL,TUV,CE	200	32.24
80 X 80 X 15	AD0812MX-D70	HYPRO	12	0.12	1.44	2440	22.4	0.083	26.0	63	0,6	UL,CUL,TUV,CE		
80 X 80 X 15	AD0812MX-D71	HYPRO	12	0.15	1.80	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MX-D73	HYPRO	12	0.15	1.80	2440	22.4	0.083	26.0	63	3	CE		
80 X 80 X 15	AD0812HX-D70	HYPRO	12	0.18	2.16	3200	29.9	0.129	33.4	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HX-D71	HYPRO	12	0.19	2.28	3200	28.0	0.107	28.1	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HX-D73	HYPRO	12	0.19	2.28	3200	28.0	0.107	28.1	63	3	CE	200	32.34
80 X 80 X 15	AD0812LB-D70	BALL	12	0.09	1.08	2000	20.0	0.050	19.6	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812LB-D73	BALL	12	0.09	1.08	2000	20.0	0.050	19.6	63	3	CE	200	32.34
80 X 80 X 15	AD0812MB-D70	BALL	12	0.12	1.44	2440	22.4	0.083	26.0	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MB-D71	BALL	12	0.15	1.80	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MB-D73	BALL	12	0.15	1.80	2440	22.4	0.083	26.0	63	3	CE	200	32.34
80 X 80 X 15	AD0812MB-D74	BALL	12	0.08	0.96	2440	22.1	0.087	25.4	63	4	UL,CUL,CE	200	32.34
80 X 80 X 15	AD0812HB-D70	BALL	12	0.18	2.16	3200	29.9	0.129	33.4	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HB-D71	BALL	12	0.19	2.16	3200	29.9	0.129	33.4	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HB-D72	BALL	12	0.19	2.16	3200	29.9	0.129	33.4	63	2	CE	200	32.34
80 X 80 X 15	AD0812HB-D73	BALL	12	0.19	2.16	3200	29.9	0.129	33.4	63	3	TUV,CE	200	32.34
80 X 80 X 15	AD0812HB-D74	BALL	12	0.17	2.16	3200	29.9	0.129	33.4	63	4	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812LS-D70	S	12	0.09	1.08	2000	20.0	0.050	19.6	63	0,6	UL,CUL,TUV,CE	200	32.34

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED



**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
80 X 80 X 15	AD0812MS-D70	S	12	0.12	1.44	2440	22.4	0.083	26.0	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MS-D71	S	12	0.15	1.80	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MS-D73	S	12	0.15	1.80	2440	22.4	0.083	26.0	63	3	CE	200	32.34
80 X 80 X 15	AD0812HS-D70	S	12	0.18	2.16	3200	29.9	0.129	33.4	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HS-D71	S	12	0.19	2.28	3200	29.9	0.129	33.4	63	1	UL,CUL,CE	200	32.34
80 X 80 X 15	AD0812HS-D73	S	12	0.18	2.16	3200	29.9	0.129	33.4	63	3	CE	200	32.34
80 X 80 X 15	AD0824MX-D71	HYPRO	24	0.10	2.40	2440	21.0	0.070	27.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0824HX-D71	HYPRO	24	0.13	3.12	3200	29.0	0.116	33.5	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0824MB-D71	BALL	24	0.10	2.40	2440	21.0	0.070	27.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0824HB-D70	BALL	24	0.13	3.12	3200	32.0	0.131	33.6	63	0	CE	200	32.34
80 X 80 X 15	AD0824HB-D71	BALL	24	0.13	3.12	3200	32.0	0.131	33.6	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0824MS-D70	S	24	0.08	1.92	2440	22.4	0.083	26.0	63	0	CE	200	32.34
80 X 80 X 15	AD0824MS-D71	S	24	0.10	2.40	2440	21.0	0.070	27.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0824HS-D71	S	24	0.13	3.12	3200	29.0	0.116	33.5	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 20	AD0805HX-C72	HYPRO	5	0.32	3.84	3010	27.3	0.128	31.4	70	2	CE	200	35.20
80 X 80 X 20	AD0805HB-C70	BALL	5	0.43	5.16	3010	27.3	0.128	31.4	70	0	CE	200	35.20
80 X 80 X 20	AD0805HB-C71	BALL	5	0.32	3.84	3010	27.3	0.128	31.4	70	1,2	CE	200	35.20
80 X 80 X 20	AD0812LX-C70	HYPRO	12	0.10	1.20	2000	18.9	0.059	17.7	70	0	CE	200	35.20
80 X 80 X 20	AD0812MX-C70	HYPRO	12	0.16	1.92	2440	22.1	0.087	25.4	70	0	UL,CUL,CSA,CE	200	35.20
80 X 80 X 20	AD0812MX-C76	HYPRO	12	0.16	1.92	2440	21.8	0.085	25.0	70	6	CE	200	35.20
80 X 80 X 20	AD0812HX-C70	HYPRO	12	0.24	2.88	3010	27.3	0.128	31.4	70	0	UL,CUL,CSA,CE	200	35.20
80 X 80 X 20	AD0812HX-C72	HYPRO	12	0.24	2.88	3010	27.3	0.128	31.4	70	2,3	CE	200	35.20
80 X 80 X 20	AD0812UX-C72	HYPRO	12	0.29	3.48	4200	38.9	0.234	40.7	70	2	CE	200	35.20
80 X 80 X 20	AD0812LB-C70	BALL	12	0.10	1.20	2100	19.3	0.067	22.4	70	0	CE	200	35.20
80 X 80 X 20	AD0812LB-C76	BALL	12	0.10	1.20	2100	27.3	0.128	31.4	70	6	CE	200	35.20
80 X 80 X 20	AD0812MB-C70	BALL	12	0.16	1.92	2440	22.1	0.087	25.4	70	0,6	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 20	AD0812MB-C71	BALL	12	0.16	1.92	2440	22.1	0.087	25.4	70	1	UL,CSA,CE	200	35.20
80 X 80 X 20	AD0812MB-C72	BALL	12	0.16	1.92	2440	22.1	0.087	25.4	70	2,3	CE	200	35.20
80 X 80 X 20	AD0812HB-C70	BALL	12	0.24	2.88	3100	28.8	0.138	32.4	70	0,6	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 20	AD0812HB-C71	BALL	12	0.24	2.88	3010	27.3	0.128	31.4	70	1	UL,TUV,CSA,CE	200	35.20
80 X 80 X 20	AD0812HB-C72	BALL	12	0.24	2.88	3010	27.3	0.128	31.4	70	2,3	CE	200	35.20
80 X 80 X 20	AD0812UB-C72	BALL	12	0.29	3.48	4200	38.9	0.234	40.7	70	2	CE	200	35.20
80 X 80 X 20	AD0812LS-C70	S	12	0.24	2.88	2040	27.3	0.128	31.4	70	0	UL,CE	200	35.20
80 X 80 X 20	AD0812LS-C76	S	12	0.10	1.20	2040	27.3	0.128	31.4	70	6	CE	200	35.20
80 X 80 X 20	AD0812MS-C70	S	12	0.16	1.92	2440	22.1	0.087	25.4	70	0	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 20	AD0812MS-C71	S	12	0.16	1.92	2440	22.1	0.087	25.4	70	1	UL,CSA,CE	200	35.20
80 X 80 X 20	AD0812MS-C72	S	12	0.16	1.92	2440	22.1	0.087	25.4	70	2	CE	200	35.20
80 X 80 X 20	AD0812MS-C76	S	12	0.16	1.92	2400	21.8	0.085	25.0	70	6	CE	200	35.20
80 X 80 X 20	AD0812HS-C70	S	12	0.24	2.88	3010	27.3	0.128	31.4	70	0,6	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 20	AD0812HS-C70(UT)	S	12	0.24	2.88	3750	33.5	0.194	34.0	70	0,6	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 20	AD0812HS-C71	S	12	0.24	2.88	3010	27.3	0.128	31.4	70	1	UL,CSA,CE	200	35.20
80 X 80 X 20	AD0812HS-C72	S	12	0.24	2.88	3010	27.3	0.128	31.4	70	2	CE	200	35.20
80 X 80 X 20	AD0824MX-C70	HYPRO	24	0.13	3.12	2440	22.1	2.210	25.4	66	0,1,2,3	UL,CUL,TUV,CSA,CE	200	35.20

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
80 X 80 X 20	AD0824HX-C70	HYPRO	24	0.15	3.60	3010	27.3	0.128	31.4	70	0	UL,CUL,CSA,CE	200	35.20
80 X 80 X 20	AD0824MB-C70	BALL	24	0.13	3.12	2440	22.1	0.087	25.4	70	0	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 20	AD0824MB-C71	BALL	24	0.13	3.12	2440	22.1	0.087	25.4	70	1	UL,CSA,CE	200	35.20
80 X 80 X 20	AD0824HB-C70	BALL	24	0.15	3.60	3010	27.3	0.128	31.4	70	0	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 20	AD0824HB-C71	BALL	24	0.15	3.60	3010	27.3	0.128	31.4	70	1	UL,TUV,CSA,CE	200	35.20
80 X 80 X 20	AD0824HB-C72	BALL	24	0.15	3.60	3010	27.3	0.128	31.4	70	2	CE	200	35.20
80 X 80 X 20	AD0824MS-C70	S	24	0.13	3.12	2440	22.1	0.087	25.4	70	0	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 20	AD0824MS-C71	S	24	0.13	3.12	2440	22.1	0.087	25.4	70	1	UL,CSA,CE	200	35.20
80 X 80 X 20	AD0824HS-C70	S	24	0.15	3.60	3010	27.3	0.128	31.4	70	0	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 20	AD0824HS-C71	S	24	0.15	3.60	3010	27.3	0.128	31.4	70	1	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812DX-A70GL	HYPRO	12	0.08	0.96	1600	20.5	0.051	14.0	86	0,1,2	CE	200	35.20
80 X 80 X 25	AD0812LX-A70GL	HYPRO	12	0.12	1.44	2030	25.0	0.090	22.0	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812LX-A72GL	HYPRO	12	0.12	1.44	2030	25.0	0.090	22.0	86	2	UL,CE	200	35.20
80 X 80 X 25	AD0812LX-A73GL	HYPRO	12	0.12	1.44	2030	26.2	0.078	22.5	86	3	UL,TUV,CE	200	35.20
80 X 80 X 25	AD0812LX-A76GL	HYPRO	12	0.12	1.44	2030	25.0	0.090	22.0	86	6	UL,CUL,TUV,CE	200	35.20
80 X 80 X 25	AD0812MX-A70GL	HYPRO	12	0.15	1.80	2440	31.4	0.114	28.3	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812MX-A71GL	HYPRO	12	0.15	1.80	2450	31.5	0.115	27.6	86	1	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0812MX-A76GL	HYPRO	12	0.15	1.80	2440	31.4	0.114	28.3	86	6	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812HX-A70GL	HYPRO	12	0.25	3.00	3010	38.6	0.160	34.4	86	0,6	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812HX-A71GL	HYPRO	12	0.25	3.00	3010	38.6	0.160	34.4	86	1	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0812HX-A72GL	HYPRO	12	0.25	3.00	3010	38.6	0.160	34.4	86	2,3	UL,CE	200	35.20
80 X 80 X 25	AD0812UX-A70GL	HYPRO	12	0.50	6.00	3700	48.3	0.268	40.0	86	0	UL,CUL,TUV,CE	200	35.20
80 X 80 X 25	AD0812UX-A71GL	HYPRO	12	0.45	5.40	3900	50.0	0.279	41.0	86	1	TUV,CE	200	35.20
80 X 80 X 25	AD0812UX-A72GL	HYPRO	12	0.45	5.40	3900	50.0	0.279	41.0	86	2,3	CE	200	35.20
80 X 80 X 25	AD0812DB-A70GL	BALL	12	0.08	0.96	1600	20.5	0.050	15.0	86	0,1,3	CE	200	35.20
80 X 80 X 25	AD0812LB-A70GL	BALL	12	0.12	1.44	2030	26.2	0.078	22.5	86	0,6	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812LB-A71GL	BALL	12	0.12	1.44	2030	26.2	0.078	22.5	86	1	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0812LB-A72GL	BALL	12	0.12	1.44	2030	26.2	0.078	22.5	86	2,3	UL,TUV,CE	200	35.20
80 X 80 X 25	AD0812MB-A70GL	BALL	12	0.15	1.80	2440	31.4	0.114	28.3	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812MB-A70TS	BALL	12	0.15	1.80	2700	33.0	0.130	29.0	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812MB-A71GL	BALL	12	0.15	1.80	2440	31.4	0.114	28.3	86	1,2	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0812MB-A73GL	BALL	12	0.15	1.80	2440	31.4	0.114	28.3	86	3	UL,CE	200	35.20
80 X 80 X 25	AD0812MB-A76GL	BALL	12	0.15	1.80	2440	31.4	0.114	28.3	86	6	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812HB-A70GL	BALL	12	0.25	3.00	3010	38.6	0.160	34.4	86	0,1	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812HB-A72GL	BALL	12	0.25	3.00	3010	38.6	0.160	34.4	86	2,3	UL,TUV,CE	200	35.20
80 X 80 X 25	AD0812HB-A74GL	BALL	12	0.29	3.48	3010	38.6	0.160	34.4	86	4	TUV,CE	200	35.20
80 X 80 X 25	AD0812HB-A76GL	BALL	12	0.25	3.00	3010	38.6	0.160	34.4	86	6	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812UB-A70GL	BALL	12	0.30	3.60	3400	43.8	0.190	40.0	86	0	UL,CUL,TUV,CE	200	35.20
80 X 80 X 25	AD0812UB-A71GL	BALL	12	0.45	5.40	3900	50.0	0.279	41.0	86	1	UL,CUL,TUV,CE	200	35.20
80 X 80 X 25	AD0812UB-A72GL	BALL	12	0.45	5.40	3900	50.0	0.279	41.0	86	2	UL,CUL,CE	200	35.20
80 X 80 X 25	AD0812UB-A73GL	BALL	12	0.45	5.40	3900	50.0	0.279	41.0	86	3	UL,CUL,CE	200	35.20
80 X 80 X 25	AD0812DS-A70GL	S	12	0.08	0.96	1600	20.5	0.050	15.0	86	0,6	CE	200	35.20
80 X 80 X 25	AD0812LS-A70GL	S	12	0.12	1.44	2030	26.2	0.078	22.5	86	0	UL,TUV,CSA,CE	200	35.20

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
80 X 80 X 25	AD0812LS-A71GL	S	12	0.12	1.44	2030	26.2	0.078	22.5	86	1	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0812LS-A73GL	S	12	0.12	1.44	2030	26.2	0.078	22.5	86	3	UL,TUL,CE	200	35.20
80 X 80 X 25	AD0812LS-A76GL	S	12	0.12	1.44	2030	26.2	0.078	22.5	86	6	UL,CUL,TUV,CE	200	35.20
80 X 80 X 25	AD0812MS-A70GL	S	12	0.15	1.80	2440	31.4	0.114	28.3	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812MS-A71GL	S	12	0.15	1.80	2440	31.4	0.114	28.3	86	1,2	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0812MS-A73GL	S	12	0.15	1.80	2440	31.4	0.114	28.3	86	3	UL,CE	200	35.20
80 X 80 X 25	AD0812MS-A76GL	S	12	0.15	1.80	2440	31.4	0.114	28.3	86	6	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812HS-A70GL	S	12	0.25	3.00	3010	38.6	0.160	34.4	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0812HS-A71GL	S	12	0.25	3.00	3010	38.6	0.160	34.4	86	1	UL,TUL,CE	200	35.20
80 X 80 X 25	AD0812HS-A72GL	S	12	0.25	3.00	3010	38.6	0.160	34.4	86	2,3	UL,CE	200	35.20
80 X 80 X 25	AD0812HS-A76GL	S	12	0.25	3.00	3010	38.6	0.160	34.4	86	6	UL,CUL,TUV,CE	200	35.20
80 X 80 X 25	AD0812US-A70GL	S	12	0.38	4.56	3700	46.7	0.226	38.5	86	0	CE	200	35.20
80 X 80 X 25	AD0812US-A71GL	S	12	0.45	5.40	3900	50.0	0.279	41.0	86	1	TUV,CE	200	35.20
80 X 80 X 25	AD0812US-A73GL	S	12	0.45	5.40	3900	50.0	0.279	41.0	86	3	CE	200	35.20
80 X 80 X 25	AD0812US-A76GL	S	12	0.38	4.56	3700	46.7	0.226	38.5	86	6	UL,CUL,TUV,CE	200	35.20
80 X 80 X 25	AD0824LX-A70GL	HYPRO	24	0.09	2.16	2030	26.2	0.078	22.5	86	0	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0824MX-A70GL	HYPRO	24	0.10	2.40	2440	31.4	0.114	28.3	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0824MX-A72GL	HYPRO	24	0.09	2.16	2440	31.4	0.114	28.3	86	2	UL,CE	200	35.20
80 X 80 X 25	AD0824HX-A70GL	HYPRO	24	0.16	3.84	3010	38.6	0.166	34.0	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0824HX-A71GL	HYPRO	24	0.16	3.84	3010	38.6	0.166	34.0	86	1	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0824HX-A72GL	HYPRO	24	0.16	3.84	3010	38.6	0.166	34.0	86	2	UL,CE	200	35.20
80 X 80 X 25	AD0824UX-A71GL	HYPRO	24	0.26	6.24	3900	50.0	0.279	41.0	86	0,1,2,3	CE	200	35.20
80 X 80 X 25	AD0824LB-A70GL	BALL	24	0.09	2.16	2030	26.2	0.078	22.5	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0824LB-A71GL	BALL	24	0.09	2.16	2030	26.2	0.078	22.5	86	1	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0824LB-A73GL	BALL	24	0.09	2.16	2030	26.2	0.078	22.5	86	3	UL,CE	200	35.20
80 X 80 X 25	AD0824MB-A70GL	BALL	24	0.10	2.40	2440	31.4	0.114	28.3	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0824MB-A71GL	BALL	24	0.10	2.40	2440	31.4	0.114	28.3	86	1	UL,CUL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0824MB-A73GL	BALL	24	0.10	2.40	2440	31.4	0.114	28.3	86	3	UL,CE	200	35.20
80 X 80 X 25	AD0824HB-A70GL	BALL	24	0.16	3.84	3010	38.6	0.160	34.4	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0824HB-A71GL	BALL	24	0.16	3.84	3010	38.6	0.160	34.4	86	1	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0824HB-A72GL	BALL	24	0.16	3.84	3010	38.6	0.160	34.4	86	2	UL,TUV,CE	200	35.20
80 X 80 X 25	AD0824HB-A73GL	BALL	24	0.16	3.84	3010	38.6	0.160	34.4	86	3	UL,CE	200	35.20
80 X 80 X 25	AD0824HB-A76GL	BALL	24	0.16	3.84	3200	40.0	0.171	35.0	86	6	UL,CE	200	35.20
80 X 80 X 25	AD0824UB-A71GL	BALL	24	0.26	6.24	3900	50.0	0.279	41.0	86	1	UL,CUL,TUV,CE	200	35.20
80 X 80 X 25	AD0824UB-A72GL	BALL	24	0.26	6.24	3900	50.0	0.279	41.0	86	2	UL,CUL,CE	200	35.20
80 X 80 X 25	AD0824UB-A73GL	BALL	24	0.26	6.24	3900	50.0	0.279	41.0	86	3	CE	200	35.20
80 X 80 X 25	AD0824LS-A70GL	S	24	0.09	2.16	2030	26.2	0.078	22.5	86	0,1	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0824LS-A76GL	S	24	0.09	2.16	2030	26.2	0.078	22.5	86	6	UL,CE	200	35.20
80 X 80 X 25	AD0824MS-A70GL	S	24	0.10	2.40	2440	31.4	0.114	28.3	86	0	UL,TUV,CSA,CE	200	35.20
80 X 80 X 25	AD0824MS-A71GL	S	24	0.10	2.40	2440	31.4	0.114	28.3	86	1	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0824MS-A72GL	S	24	0.10	2.40	2440	31.4	0.114	28.3	86	2	UL,CE	200	35.20
80 X 80 X 25	AD0824MS-A76GL	S	24	0.10	2.40	2400	30.0	0.100	27.0	86	6	UL,CE	200	35.20
80 X 80 X 25	AD0824HS-A70GL	S	24	0.16	3.84	3010	38.6	0.160	34.4	86	0	UL,TUV,CSA,CE	200	35.20

NOTE B=Ball S=Sleeve X=Hypro AT=Terminals AW=Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
80 X 80 X 25	AD0824HS-A71GL	S	24	0.16	3.84	3010	38.6	0.160	34.4	86	1,2	UL,CSA,CE	200	35.20
80 X 80 X 25	AD0824US-A70GL	S	24	0.29	6.96	4100	52.5	0.253	42.0	86	0	CE	200	35.20
80 X 80 X 25	AD0824US-A71GL	S	24	0.26	6.24	3900	50.0	0.279	41.0	86	1	CE	200	35.20
80 X 80 X 25	AD0848HB-A71GL	BALL	48	0.11	5.28	3010	38.6	0.160	34.4	86	1	UL,CUL,TUV,CE	200	35.20
80 X 80 X 25	AD0848HB-A73GL	BALL	48	0.11	5.28	3010	38.6	0.160	34.4	86	3,6	CE	200	35.20
80 X 80 X 25	AD0848XB-A76GL	BALL	48	0.13	6.24	4500	55.2	0.302	44.8	86	6	CE	200	35.20
80 X 80 X 25	AD0848HS-A71GL	S	48	0.11	5.28	3010	38.6	0.160	34.4	86	1	UL,CUL,TUV,CE	200	35.20
80 X 80 X 25	AD0848HS-A73GL	S	48	0.08	3.84	3010	38.6	0.160	34.4	86	3,6	CE	200	35.20
92 X 92 X 20	AD0912MX-C70	HYPRO	12	0.16	1.92	2430	29.0	0.083	28.9	85	0	TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0912HX-C70	HYPRO	12	0.25	3.00	2740	32.8	0.106	32.8	85	0	UL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0912HX-C7	HYPRO	12	0.25	3.00	2740	32.8	0.106	32.8	85	6	CE	200	41.30
92 X 92 X 20	AD0912MB-C70	BALL	12	0.16	1.92	2430	29.0	0.083	28.9	85	0	UL,CUL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0912MB-C71	BALL	12	0.16	1.92	2430	29.0	0.083	28.9	85	1	UL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0912MB-C72	BALL	12	0.16	1.92	2430	29.0	0.083	28.9	85	2	TUV,CE	200	41.30
92 X 92 X 20	AD0912MB-C76	BALL	12	0.16	1.92	2430	29.0	0.083	28.9	85	6	CE	200	41.30
92 X 92 X 20	AD0912HB-C70	BALL	12	0.25	3.00	2740	32.8	0.106	32.8	85	0,6	UL,CUL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0912HB-C71	BALL	12	0.25	3.00	2740	32.8	0.106	32.8	85	1	UL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0912HB-C72	BALL	12	0.25	3.00	2740	32.8	0.106	32.8	85	2,3	TUV,CE	200	41.30
92 X 92 X 20	AD0912MS-C70	S	12	0.16	1.92	2430	29.0	0.083	28.9	85	0	UL,CUL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0912MS-C71	S	12	0.16	1.92	2430	29.0	0.083	28.9	85	1	UL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0912HS-C70	S	12	0.25	3.00	2740	32.8	0.106	32.8	85	0	UL,CUL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0912HS-C71	S	12	0.25	3.00	2740	32.8	0.106	32.8	85	1	UL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0912HS-C76	S	12	0.25	3.00	2740	32.8	0.106	32.8	85	6	CE	200	41.30
92 X 92 X 20	AD0924MX-C70	HYPRO	24	0.10	2.40	2430	29.0	2.110	28.9	78	0,1,2,3	UL,CUL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0924HX-C70	HYPRO	24	0.14	3.36	2740	32.8	0.106	32.8	85	0	TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0924MB-C70	BALL	24	0.10	2.40	2430	29.0	0.083	28.9	85	0	UL,CUL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0924MB-C71	BALL	24	0.10	2.40	2430	29.0	0.083	28.9	85	1	UL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0924HB-C70	BALL	24	0.14	3.36	2740	32.8	0.106	32.8	85	0	UL,CUL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0924HB-C71	BALL	24	0.14	3.36	2740	32.8	0.106	32.8	85	1	UL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0924HB-C73	BALL	24	0.14	3.36	2740	32.8	0.106	32.8	85	3	UL,CSA,CE	200	41.30
92 X 92 X 20	AD0924MS-C70	S	24	0.10	2.40	2430	29.0	0.083	28.9	85	0	UL,CUL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0924MS-C71	S	24	0.10	2.40	2430	29.0	0.083	28.9	85	1	UL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0924HS-C70	S	24	0.14	3.36	2740	32.8	0.106	32.8	85	0	UL,CUL,TUV,CSA,CE	200	41.30
92 X 92 X 20	AD0924HS-C71	S	24	0.14	3.36	2740	32.8	0.106	32.8	85	1	UL,TUV,CSA,CE	200	41.30
92 X 92 X 25	AD0912DX-A70GL	HYPRO	12	0.09	1.08	1600	28.0	0.060	22.0	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912DX-A71GL	HYPRO	12	0.07	0.84	1600	28.0	0.060	22.0	101	1	CE	200	52.36
92 X 92 X 25	AD0912LX-A70GL	HYPRO	12	0.12	1.44	2100	37.9	0.073	26.5	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912LX-A72GL	HYPRO	12	0.13	1.56	2200	35.9	0.097	29.3	101	2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912LX-A76GL	HYPRO	12	0.13	1.56	2000	32.4	0.054	23.5	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912MX-A70GL	HYPRO	12	0.17	2.04	2400	43.5	0.094	31.3	101	0,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912HX-A70GL	HYPRO	12	0.25	3.00	2700	50.0	0.117	33.7	101	0,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912HX-A76GL	HYPRO	12	0.25	3.00	2700	50.0	0.117	33.7	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912UX-A71GL	HYPRO	12	0.39	4.68	3200	57.8	0.158	38.6	101	1,2	UL,CUL,TUV,CE	200	52.36

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
92 X 92 X 25	AD0912UX-A76GL	HYPRO	12	0.30	3.60	3300	60.0	0.166	39.4	101	6	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912DB-A71GL	BALL	12	0.07	0.84	1600	28.0	0.060	22.0	101	1	CE	200	52.36
92 X 92 X 25	AD0912LB-A70GL	BALL	12	0.13	1.56	2050	36.0	0.063	25.0	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912LB-A702GL	BALL	12	0.12	1.44	2300	41.6	0.087	29.8	101	2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912LB-A76GL	BALL	12	0.12	1.44	2300	41.6	0.087	29.8	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912MB-A70GL	BALL	12	0.17	2.04	2600	47.2	0.108	32.7	101	0,1,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912MB-A76GL	BALL	12	0.17	2.04	2600	47.2	0.108	32.7	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912HB-A70GL	BALL	12	0.25	3.00	2900	52.5	0.133	35.0	101	0,1,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912HB-A76GL	BALL	12	0.25	3.00	2900	52.5	0.133	35.0	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912UB-A71GL	BALL	12	0.39	4.68	3300	60.0	0.166	39.4	101	1,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912UB-A76GL	BALL	12	0.39	4.68	3300	60.0	0.166	39.4	101	6	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912XB-A71GL	BALL	12	0.55	6.60	3800	67.0	0.198	43.9	101	1	CE	200	52.36
92 X 92 X 25	AD0912DS-A70GL	S	12	0.09	1.08	1600	28.0	0.060	22.0	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912DS-A71GL	S	12	0.07	1.08	1600	28.0	0.060	22.0	101	1	CE	200	52.36
92 X 92 X 25	AD0912LS-A70GL	S	12	0.13	1.56	2000	32.4	0.054	23.5	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912LS-A73GL	S	12	0.13	1.56	2100	37.9	0.073	26.5	101	3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912LS-A76GL	S	12	0.13	1.56	2000	32.4	0.054	23.5	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912MS-A70GL	S	12	0.17	2.04	2350	43.0	0.087	31.0	101	0,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912MS-A76GL	S	12	0.17	2.04	2350	43.0	0.087	31.0	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912HS-A70GL	S	12	0.25	3.00	2700	50.0	0.117	33.7	101	0,1,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912HS-A76GL	S	12	0.25	3.00	2700	50.0	0.117	33.7	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912US-A70GL	S	12	0.39	4.68	3200	57.8	0.156	39.4	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912US-A71GL	S	12	0.39	4.68	3300	60.0	0.198	39.1	101	1,2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912US-A76GL	S	12	0.30	3.60	3300	60.0	0.166	39.4	101	6	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924LX-A70GL	HYPRO	24	0.08	1.92	2100	37.9	0.073	26.5	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924MX-A70GL	HYPRO	24	0.12	2.88	2400	43.5	0.094	31.3	101	0,2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924MX-A71GL	HYPRO	24	0.17	2.04	2700	43.2	0.140	35.0	101	1	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924HX-A70GL	HYPRO	24	0.15	3.60	2700	50.0	0.115	33.7	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924UX-A71GL	HYPRO	24	0.21	5.04	3200	57.8	0.156	38.6	101	1,2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924UX-A73GL	HYPRO	24	0.21	5.04	3200	57.8	0.156	38.6	101	3	CE	200	52.36
92 X 92 X 25	AD0924LB-A70GL	BALL	24	0.08	1.92	2100	37.9	0.074	26.5	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924LB-A72GL	BALL	24	0.08	1.92	2300	41.6	0.086	29.8	101	2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924LB-A76GL	BALL	24	0.08	1.92	2300	41.6	0.086	29.8	101	6	CE	200	52.36
92 X 92 X 25	AD0924MB-A70GL	BALL	24	0.12	2.88	2600	47.2	0.106	32.7	101	0,2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924HB-A70GL	BALL	24	0.15	3.60	2900	52.5	0.131	35.0	101	0,1,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924HB-A76GL	BALL	24	0.15	3.60	2900	52.5	0.131	35.0	101	6	CE	200	52.36
92 X 92 X 25	AD0924UB-A72GL	BALL	24	0.21	5.04	3300	60.0	0.166	39.4	101	2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924XB-A71GL	BALL	24	0.25	6.00	3800	66.9	0.186	42.6	101	1,2	CE	200	25.36
92 X 92 X 25	AD0924LS-A70GL	S	24	0.08	1.92	2100	37.9	0.073	26.5	101	0,2	CE	200	52.36
92 X 92 X 25	AD0924MS-A70GL	S	24	0.12	2.88	2400	43.5	0.094	31.3	101	0,2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924HS-A70GL	S	24	0.15	3.60	2700	48.0	0.115	33.7	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924HS-A72GL	S	24	0.20	4.80	3000	48.4	0.169	38.0	101	2	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0924HS-A73GL	S	24	0.20	4.80	3000	48.4	0.169	38.0	101	3	UL,CUL,TUV,CE	200	52.36

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
92 X 92 X 25	AD0924US-A70GL	S	24	0.21	5.04	3300	60.0	0.166	39.4	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924US-A71GL	S	24	0.21	5.04	3200	57.8	0.158	38.6	101	1	UL,CE	200	52.36
92 X 92 X 25	AD0924US-A72GL	S	24	0.21	5.04	3200	57.8	0.158	38.6	101	2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0948HB-A71GL	BALL	48	0.13	6.24	2900	52.5	0.133	35.0	101	1	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0948UB-A71GL	BALL	48	0.16	7.68	3300	60.0	0.163	39.4	101	1	CE	200	52.36
92 X 92 X 25	AD0948HS-A72GL	S	48	0.07	3.36	2900	52.0	0.177	34.0	101	2	CE	200	52.36
120 X 120 X 25	AD1212LX-A71GL	HYPRO	12	0.24	2.88	1800	72.0	0.095	34.4	156	1	UL,CUL,CE	90	30.80
120 X 120 X 25	AD1212LX-A72GL	HYPRO	12	0.24	2.88	1800	72.0	0.095	34.4	156	2	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1212MX-A71GL	HYPRO	12	0.34	4.08	2050	80.5	0.117	38.0	156	1	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1212MX-A73GL	HYPRO	12	0.34	4.08	2050	80.5	0.117	38.0	156	3	CE	90	30.80
120 X 120 X 25	AD1212HX-A71GL	HYPRO	12	0.44	5.28	2200	85.2	0.136	39.1	156	1	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1212HX-A73GL	HYPRO	12	0.44	5.28	2200	85.2	0.136	39.1	156	3	CE	90	30.80
120 X 120 X 25	AD1212UX-A71GL	HYPRO	12	0.50	6.00	2500	98.6	0.179	43.3	156	1	CE	90	30.80
120 X 120 X 25	AD1212LB-A71GL	BALL	12	0.24	2.88	1800	72.0	0.095	34.4	156	1,2	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1212LB-A73GL	BALL	12	0.24	2.88	1800	72.0	0.095	34.4	156	3	CE	90	30.80
120 X 120 X 25	AD1212MB-A71GL	BALL	12	0.33	3.96	2050	80.5	0.117	38.0	156	1	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1212MB-A72GL	BALL	12	0.33	3.96	2050	80.5	0.117	38.0	156	2	UL,CUL,CE	90	30.80
120 X 120 X 25	AD1212MB-A73GL	BALL	12	0.33	3.96	2050	80.5	0.117	38.0	156	3	CE	90	30.80
120 X 120 X 25	AD1212HB-A71GL	BALL	12	0.37	4.44	2200	85.2	0.136	39.1	156	1	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1212HB-A72GL	BALL	12	0.37	4.44	2200	85.2	0.136	39.1	156	2	UL,CUL,CE	90	30.80
120 X 120 X 25	AD1212HB-A73GL	BALL	12	0.37	4.44	2200	85.2	0.136	39.1	156	3	CE	90	30.80
120 X 120 X 25	AD1212UB-A71GL	BALL	12	0.50	6.00	2500	98.6	0.179	43.3	156	1	TUV,CE	90	30.80
120 X 120 X 25	AD1212UB-A72GL	BALL	12	0.50	6.00	2500	98.6	0.179	43.3	156	2,3	CE	90	30.80
120 X 120 X 25	AD1212LS-A71GL	S	12	0.24	2.88	1800	72.0	0.095	34.4	156	1,3	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1212MS-A71GL	S	12	0.34	4.08	2050	80.5	0.117	38.0	156	1,3	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1212MS-A72GL	S	12	0.34	4.08	2050	80.5	0.117	38.0	156	2	UL,CUL,CE	90	30.80
120 X 120 X 25	AD1212HS-A71GL	S	12	0.44	5.28	220	85.2	0.136	39.1	158	1	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1212HS-A72GL	S	12	0.44	5.28	220	85.2	0.136	39.1	158	2	UL,CUL,CE	90	30.80
120 X 120 X 25	AD1212HS-A73GL	S	12	0.44	5.28	220	85.2	0.136	39.1	158	3	CE	90	30.80
120 X 120 X 25	AD1212HS-A74GL	S	12	0.40	4.80	2200	85.2	0.134	39.1	156	4	TUV,CE	90	30.80
120 X 120 X 25	AD1212US-A71GL	S	12	0.50	6.00	2500	98.6	0.179	43.3	156	1,2,3	CE	90	30.80
120 X 120 X 25	AD1224LX-A71GL	HYPRO	24	0.14	3.36	1800	72.0	0.095	34.4	156	1	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1224MX-A71GL	HYPRO	24	0.20	4.80	2050	80.5	0.117	38.0	156	1	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1224HX-A71GL	HYPRO	24	0.24	5.76	2200	85.2	0.136	39.1	156	1,2	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1224HX-A73GL	HYPRO	24	0.24	5.76	2200	85.2	0.136	39.1	156	3	CE	90	30.80
120 X 120 X 25	AD1224UX-A72GL	HYPRO	24	0.25	6.00	2500	98.6	0.176	43.3	156	2	CE	90	30.80
120 X 120 X 25	AD1224LB-A71GL	BALL	24	0.14	3.36	1800	72.0	0.095	34.3	156	1,2	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1224MB-A71GL	BALL	24	0.17	4.08	2050	80.5	0.117	38.0	156	1	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1224HB-A71GL	BALL	24	0.19	4.56	2200	85.2	0.136	39.1	156	1,2,3	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1224UB-A71GL	BALL	24	0.25	6.00	2500	98.6	0.176	43.3	156	1	TUV,CE	90	30.80
120 X 120 X 25	AD1224UB-A72GL	BALL	24	0.25	6.00	2500	98.6	0.176	43.3	156	2,3	CE	90	30.80
120 X 120 X 25	AD1224LS-A71GL	S	24	0.14	3.36	1800	72.0	0.095	34.4	156	1	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1224MS-A71GL	S	24	0.20	4.80	2050	80.5	0.117	38.0	156	1	UL,CUL,TUV,CE	90	30.80

NOTE B=Ball S=Sleeve X=Hypro AT=Terminals AW=Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
120 X 120 X 25	AD1224HS-A71GL	S	24	0.24	5.76	2200	85.2	0.136	39.1	156	1	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1224HS-A73GL	S	24	0.24	5.76	2200	85.2	0.136	39.1	156	3	CE	90	30.80
120 X 120 X 25	AD1224US-A71GL	S	24	0.25	6.00	2500	98.6	0.176	43.3	156	1	CE	90	30.80
120 X 120 X 25	AD1248HB-A71GL	BALL	48	0.25	9.60	2200	85.2	0.136	39.1	156	1	CE	90	30.80
120 X 120 X 32	AD2512LX	HYPRO	12	0.15	1.80	1200	12.0	0.109	34.3	276	0	TUV,CE		
120 X 120 X 32	AD2512MX	HYPRO	12	0.60	7.20	2300	23.7	0.621	51.1	276	0	UL,CUL,CE		
120 X 120 X 32	AD2512LB	BALL	12	0.15	1.80	1200	12.0	0.109	34.3	276	0,3	TUV,CE		
120 X 120 X 32	AD2512MB	BALL	12	0.60	7.20	2300	23.7	0.621	51.1	276	0	UL,CUL,TUV,CE		
120 X 120 X 32	AD2512MB	BALL	12	0.60	7.20	2300	23.7	0.621	51.1	276	2	TUV,CE		
120 X 120 X 32	AD2512MB	BALL	12	0.60	7.20	2300	23.7	0.621	51.1	276	3	CE		
120 X 120 X 32	AD2512HB	BALL	12	0.65	7.80	2500	25.2	0.640	51.0	276	0,3	CE		
120 X 120 X 32	AD2512UB	BALL	12	1.00	8.00	3200	33.1	1.121	55.8	276	0,2,3	CE		
120 X 120 X 32	AD2512LS	S	12	0.15	1.80	1200	12.0	0.109	34.3	276	0	TUV,CE		
120 X 120 X 32	AD2512MS	S	12	0.60	7.20	2300	23.7	0.621	51.1	276	0	TUV,CE		
120 X 120 X 32	AD2512HS	S	12	0.65	7.80	2500	25.2	0.640	51.0	276	0	CE		
120 X 120 X 32	AD2512US	S	12	1.00	8.00	3200	33.1	1.121	55.8	276	0	CE		
120 X 120 X 32	AD2524MX	HYPRO	24	0.40	9.60	2300	23.7	0.621	51.1	276	0	UL,TUV,CE		
120 X 120 X 32	AD2524MB	BALL	24	0.40	9.60	2300	23.7	0.621	51.1	276	0	UL,CUL,CSA,TUV,CE		
120 X 120 X 32	AD2524HB	BALL	24	0.43	9.80	2500	25.2	0.640	51.0	276	0	CE		
120 X 120 X 32	AD2524UB	BALL	24	0.50	9.80	2800	29.4	0.800	52.5	276	0	CE		
120 X 120 X 32	AD2524MS	S	24	0.40	9.60	2300	23.7	0.621	51.1	276	0	UL,CSA,TUV,CE		
120 X 120 X 32	AD2524US	S	24	0.50	9.80	2800	29.4	0.800	52.5	276	0	CE		
120 X 120 X 38	AD1212LX-F51	HYPRO	12	0.24	2.88	1950	72.3	0.135	32.9	297	1	UL,CUL,TUV,CE	40	33.66
120 X 120 X 38	AD1212LX-F53	HYPRO	12	0.24	2.88	1950	72.3	0.135	32.9	297	3	CE	40	33.66
120 X 120 X 38	AD1212MX-F51	HYPRO	12	0.35	4.20	2540	94.0	0.244	41.0	297	1	UL,CUL,CSA,CE	40	33.66
120 X 120 X 38	AD1212MX-F53	HYPRO	12	0.35	4.20	2540	94.0	0.244	41.0	297	3	CSA,CE	40	33.66
120 X 120 X 38	AD1212HX-F51	HYPRO	12	0.50	6.00	2800	104.8	0.270	42.8	297	1,4	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212HX-F52	HYPRO	12	0.50	6.00	2800	104.8	0.270	42.8	297	2	CSA,CE	40	33.66
120 X 120 X 38	AD1212HX-Y51	HYPRO	12	0.40	4.80	2750	108.0	0.215	43.3	213	1	CE	40	33.66
120 X 120 X 38	AD1212LB-F51	BALL	12	0.24	2.88	1950	72.3	0.135	32.9	297	1,3	UL,CUL,TUV,CE	40	33.66
120 X 120 X 38	AD1212LB-F52	BALL	12	0.24	2.88	1950	72.3	0.135	32.9	297	2	UL,CE	40	33.66
120 X 120 X 38	AD1212MB-F51	BALL	12	0.35	4.20	2540	94.0	0.244	41.0	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212MB-F52	BALL	12	0.35	4.20	2540	94.0	0.244	41.0	297	2,3,4,7	CSA,CE	40	33.66
120 X 120 X 38	AD1212HB-F51	BALL	12	0.50	6.00	2800	104.8	0.270	42.8	297	1,3	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212HB-F52	BALL	12	0.50	6.00	2800	104.8	0.270	42.8	297	2,4	UL,CUL,TUV,CE	40	33.66
120 X 120 X 38	AD1212HB-F57	BALL	12	0.50	6.00	2800	104.8	0.270	42.8	297	7	CSA,CE	40	33.66
120 X 120 X 38	AD1212HB-Y51	BALL	12	0.40	4.80	2750	108.0	0.215	43.3	213	1,3	CE	40	33.66
120 X 120 X 38	AD1212UB-F51	BALL	12	0.07	0.84	3200	122.0	0.394	48.0	297	1,2,4	CE	40	33.66
120 X 120 X 38	AD1212UB-F53	BALL	12	0.07	0.84	3200	122.0	0.394	48.0	297	3	UL,CUL,CE	40	33.66
120 X 120 X 38	AD1212LS-F51	S	12	0.24	2.88	1950	72.3	0.135	32.9	297	1	UL,CUL,TUV,CE	40	33.66
120 X 120 X 38	AD1212MS-F51	S	12	0.35	4.20	2540	94.0	0.244	41.0	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212MS-F52	S	12	0.35	4.20	2540	94.0	0.244	41.0	297	2,3,4,7	CSA,CE	40	33.66
120 X 120 X 38	AD1212HS-F51	S	12	0.50	6.00	2800	104.8	0.270	42.8	297	1,4	UL,CUL,TUV,CSA,CE	40	33.66

NOTE B=Ball S=Sleeve X=Hypro AT=Terminals AW=Wires

ALL RIGHTS RESERVED

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
120 X 120 X 38	AD1212HS-F52	S	12	0.50	6.00	2800	104.8	0.270	42.8	297	2,3,7	CSA,CE	40	33.66
120 X 120 X 38	AD1212US-F51	S	12	0.70	8.40	3200	122.0	0.394	48.0	297	1	CE	40	33.66
120 X 120 X 38	AD1224MX-F51	HYPRO	24	0.23	5.52	2540	94.0	0.244	41.0	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224HX-F51	HYPRO	24	0.32	7.68	2800	104.8	0.270	42.8	297	1,2	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224UX-F51	HYPRO	24	0.40	9.60	3200	122.0	0.394	48.0	297	1	UL,CUL,CE	40	33.66
120 X 120 X 38	AD1224UX-F52F	HYPRO	24	0.40	9.60	3200	122.0	0.394	48.0	297	2	CE	40	33.66
120 X 120 X 38	AD1224LB-F51	BALL	24	0.14	3.36	1950	72.3	0.135	32.9	297	1	UL,CUL,TUV,CE	40	33.66
120 X 120 X 38	AD1224MB-F51	BALL	24	0.23	5.52	2540	94.0	0.244	41.0	297	1,3	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224MB-F52	BALL	24	0.23	5.52	2540	94.0	0.244	41.0	297	2	UL,CSA,CE	40	33.66
120 X 120 X 38	AD1224MB-F54	BALL	24	0.23	5.52	2540	94.0	0.244	41.0	297	4	CSA,CE	40	33.66
120 X 120 X 38	AD1224HB-F51	BALL	24	0.32	7.68	2800	104.8	0.270	42.8	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224HB-F52	BALL	24	0.32	7.68	2800	104.8	0.270	42.8	297	2,3	UL,CSA,TUV,CE	40	33.66
120 X 120 X 38	AD1224HB-F54	BALL	24	0.32	7.68	2800	104.8	0.270	42.8	297	4,7	CSA,CE	40	33.66
120 X 120 X 38	AD1224UB-F51	BALL	24	0.40	9.60	3200	122.0	0.394	48.0	297	1,2,3	UL,CUL,CE	40	33.66
120 X 120 X 38	AD1224LS-F51	S	24	0.14	3.36	1950	72.3	0.135	32.9	297	1	UL,CUL,TUV,CE	40	33.66
120 X 120 X 38	AD1224MS-F51	S	24	0.23	5.52	2540	94.0	0.244	41.0	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224MS-F52	S	24	0.23	5.52	2540	94.0	0.244	41.0	297	2,3,4	CSA,CE	40	33.66
120 X 120 X 38	AD1224HS-F51	S	24	0.32	7.68	2800	104.8	0.270	42.8	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224HS-F52	S	24	0.32	7.68	2800	104.8	0.270	42.8	297	2,3,4	CSA,CE	40	33.66
120 X 120 X 38	AD1224US-F51	S	24	0.40	9.60	3200	122.0	0.394	48.0	297	1	UL,CUL,CE	40	33.66
120 X 120 X 38	AD1248MX-F52	HYPRO	48	0.14	6.72	2540	94.0	0.244	41.0	297	2	UL,CE	40	33.66
120 X 120 X 38	AD1248HX-F51	HYPRO	48	0.20	9.60	2800	104.8	0.270	42.8	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248HX-F52	HYPRO	48	0.20	9.60	2800	104.8	0.270	42.8	297	2	UL,CUL,CSA,CE	40	33.66
120 X 120 X 38	AD1248LS-F51	S	48	0.10	4.80	1950	72.3	0.135	32.9	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248MS-F51	S	48	0.14	6.72	2540	94.0	0.244	41.0	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248MS-F52	S	48	0.14	6.72	2540	94.0	0.244	41.0	297	2	UL,CE	40	33.66
120 X 120 X 38	AD1248LB-F51	BALL	48	0.10	4.80	1950	72.3	0.135	32.9	297	1,3	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248MB-F51	BALL	48	0.14	6.72	2540	94.0	0.244	41.0	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248MB-F52	BALL	48	0.14	6.72	2540	94.0	0.244	41.0	297	2,3	CE	40	33.66
120 X 120 X 38	AD1248HB-F51	BALL	48	0.20	9.60	2800	104.8	0.270	42.8	297	1,2	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248HB-F53	BALL	48	0.20	9.60	2800	104.8	0.270	42.8	297	3	UL,CE	40	33.66
120 X 120 X 38	AD1248HB-F54	BALL	48	0.20	9.60	2800	104.8	0.270	42.8	297	4	CE	40	33.66
120 X 120 X 38	AD1248HB-Y56	BALL	48	0.13	6.24	2750	108.0	0.215	43.3	213	6	CE	40	33.66
120 X 120 X 38	AD1248UB-F51	BALL	48	0.23	9.80	3200	122.0	0.394	48.0	297	1,3	CE	40	33.66
120 X 120 X 38	AD1248HS-F51	S	48	0.20	9.60	2800	104.8	0.270	42.8	297	1,2	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248HS-F53	S	48	0.20	9.60	2800	104.8	0.270	42.8	297	3	CE	40	33.66

NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires

**ALL RIGHTS RESERVED**