



The IDXPERT™ printer has been discontinued, but Brady continues to manufacture and stock labels and accessories for the printer!

Catalog #	Description
LABXPERT-SER-USB	Serial-to-USB adapter for PC cable
PCK-6	Cleaning Kit

## General ID, 5S Lean, Facility and Safety ID (B-422, B-428, B-483, B-499 and B-595)

- B-422 Polyester Material:** Permanent adhesive, good for powder-coated and textured surfaces. Best on flat surfaces. Temp. range: -40°F to 212°F (-40°C to 100°C). UL recognized.
- B-428 Metallized Polyester Material:** Permanent adhesive, silver finish. Temp. range: -40°F to 176°F (-40°C to 80°C). UL recognized.
- B-483 Polyester Material:** Permanent adhesive for powder-coated and textured surfaces. Best on flat surfaces. Temp. range: -40°F to 248°F (-40°C to 120°C). UL recognized.
- B-499 Nylon Cloth Material:** Permanent adhesive. Pliable for rough or smooth surfaces. Temp. range: -94°F to 194°F (-70°C to 90°C). UL recognized.
- B-595 Indoor / Outdoor Vinyl Material:** Permanent adhesive, very pliable, good for rough surfaces and outdoor use. Temp. range: -40°F to 180°F (-40°C to 82°C). UL recognized.




Figure 29



Figure 33




Figure 46  
(Includes black border)

Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Roll
<b>B-422 Polyester Labels</b>							
Fig. 29	X-7-422	B-422	Polyester	Black on White	0.500 (12.7)	0.500 (12.7)	350
Fig. 29	X-19-422	B-422	Polyester	Black on White	1.000 (25.4)	1.000 (25.4)	250
Fig. 29	X-132-422	B-422	Polyester	Black on White	1.500 (38.1)	1.250 (13.8)	250
Fig. 29	X-30-422	B-422	Polyester	Black on White	1.500 (38.1)	0.750 (19.1)	250
<b>B-428 Metallized Polyester Labels</b>							
Fig. 29	X-17-428-SV-BK	B-428	Polyester	Light Gray	1.000 (25.4)	0.500 (12.7)	500
Fig. 46	X-24-428-SVBB-BK	B-428	Polyester	Light Gray	1.130 (28.7)	0.500 (12.7)	500
Fig. 29	X-29-428-SV-BK	B-428	Polyester	Light Gray	1.500 (38.1)	0.500 (12.7)	500
Fig. 29	X-30-428-SV-BK	B-428	Polyester	Light Gray	1.500 (38.1)	0.750 (19.1)	325
Fig. 29	X-20-428-SV-BK	B-428	Polyester	Light Gray	2.000 (50.8)	1.000 (25.4)	100
<b>B-483 Polyester Labels</b>							
Fig. 29	X-17-483	B-483	Polyester	Black on White	1.000 (25.4)	0.500 (12.7)	500
Fig. 29	X-20-483	B-483	Polyester	Black on White	2.000 (50.8)	1.000 (25.4)	100
Fig. 29	X-61-483	B-483	Polyester	Black on White	2.000 (50.8)	0.500 (12.7)	100
<b>B-499 Nylon Cloth Labels</b>							
Fig. 29	X-130-499	B-499	Nylon Cloth	Black on White	0.375 (9.5)	0.750 (19.1)	300
Fig. 33	XC-375-499	B-499	Nylon Cloth	Black on White	0.375 (9.5)	20 ft. (6.1 m)	1 roll (cont.)
Fig. 33	XC-500-499	B-499	Nylon Cloth	Black on White	0.500 (12.7)	20 ft. (6.1 m)	1 roll (cont.)
Fig. 29	X-11-499	B-499	Nylon Cloth	Black on White	0.750 (19.1)	0.500 (12.7)	275
Fig. 33	XC-750-499	B-499	Nylon Cloth	Black on White	0.750 (19.1)	20 ft. (6.1 m)	1 roll (cont.)
Fig. 29	X-84-499	B-499	Nylon Cloth	Black on White	0.900 (22.9)	0.500 (12.7)	250
Fig. 33	XC-1000-499	B-499	Nylon Cloth	Black on White	1.000 (25.4)	20 ft. (6.1 m)	1 roll (cont.)
Fig. 29	X-162-499	B-499	Nylon Cloth	Black on White	1.500 (38.1)	0.500 (12.7)	165

General ID labels continued on next page.

## General ID, 5S Lean, Facility and Safety ID

(Continued from previous page.)




Figure 33



Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels Per Roll
<b>B-595 Indoor / Outdoor Vinyl Film</b>							
Fig. 33	XC-500-595-CL-BK	B-595	Vinyl	Black on Clear	0.500 (12.7)	25 ft. (7.6 m)	1 roll (cont.)
Fig. 33	XC-750-595-CL-BK	B-595	Vinyl	Black on Clear	0.750 (19.1)	25 ft. (7.6 m)	1 roll (cont.)
Fig. 33	XC-1000-595-CL-BK	B-595	Vinyl	Black on Clear	1.000 (25.4)	25 ft. (7.6 m)	1 roll (cont.)
Fig. 33	XC-1500-595-CL-BK	B-595	Vinyl	Black on Clear	1.500 (38.1)	25 ft. (7.6 m)	1 roll (cont.)
Fig. 33	XC-500-595-OR-BK	B-595	Vinyl	Black on Orange	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-OR-BK	B-595	Vinyl	Black on Orange	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-OR-BK	B-595	Vinyl	Black on Orange	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-OR-BK	B-595	Vinyl	Black on Orange	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-WT-BK	B-595	Vinyl	Black on White	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-WT-BK	B-595	Vinyl	Black on White	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-WT-BK	B-595	Vinyl	Black on White	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-WT-BK	B-595	Vinyl	Black on White	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-YL-BK	B-595	Vinyl	Black on Yellow	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-YL-BK	B-595	Vinyl	Black on Yellow	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-YL-BK	B-595	Vinyl	Black on Yellow	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-YL-BK	B-595	Vinyl	Black on Yellow	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-WT-RD	B-595	Vinyl	Red on White	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-WT-RD	B-595	Vinyl	Red on White	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-WT-RD	B-595	Vinyl	Red on White	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-WT-RD	B-595	Vinyl	Red on White	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-BL-WT	B-595	Vinyl	White on Blue	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-BL-WT	B-595	Vinyl	White on Blue	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-BL-WT	B-595	Vinyl	White on Blue	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-BL-WT	B-595	Vinyl	White on Blue	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-GN-WT	B-595	Vinyl	White on Green	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-GN-WT	B-595	Vinyl	White on Green	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-GN-WT	B-595	Vinyl	White on Green	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-GN-WT	B-595	Vinyl	White on Green	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-RD-WT	B-595	Vinyl	White on Red	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-RD-WT	B-595	Vinyl	White on Red	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-RD-WT	B-595	Vinyl	White on Red	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-RD-WT	B-595	Vinyl	White on Red	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)

## PermaSleeve® PS Polyolefin Wire Marking Sleeves (B-342)

3:1 heat-shrinkable sleeves fit snugly around wire for identification and protection. Fade resistant and flame retardant. Meets the following material and physical property specifications.

- SAE-AMS-DTL-23053/5 (Class 1)
  - SAE-AS-81531
  - MIL-STD-202
  - RoHS compliant
  - UL recognized
- **Tested per:**  
ASTM E162 and  
ASTM E662




Figure 44




Figure 58



Diagram	Catalog #	B#	Color	Approx. Wire Gauge	Range of Wire Dia. Inch (mm)	Sleeve Width A Inch (mm)	Supplied Diameter B Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeves Per Roll
<b>B-342 Die Cut Sleeves</b>										
Fig. 44	* XPS-125-1	B-342	Black on White	22 to 16	0.046 (1.2) - 0.110 (2.8)	1.015 (25.8)	0.125 (3.2)	0.047 (1.2)	.020 (0.5) ± .003 (0.07)	100
Fig. 44	* XPS-187-1	B-342	Black on White	20 to 10	0.062 (1.6) - 0.150 (3.8)	1.015 (25.8)	0.187 (4.7)	0.062 (1.6)	.020 (0.5) ± .003 (0.07)	100
Fig. 44	* XPS-250-1	B-342	Black on White	16 to 8	0.094 (2.4) - 0.215 (5.5)	1.015 (25.8)	0.250 (6.4)	0.093 (2.4)	.025 (0.6) ± .003 (0.07)	100
Fig. 44	* XPS-375-1	B-342	Black on White	12 to 4	0.125 (3.2) - 0.320 (8.13)	1.015 (25.8)	0.375 (9.5)	0.125 (3.1)	.025 (0.6) ± .003 (0.07)	100
<b>B-342 Continuous Sleeve Tubing</b>										
Fig. 58	* XPS-125-CONT	B-342	Black on White	22 to 16	0.046 (1.2) - 0.110 (2.8)	8 ft (2.45m)	0.125 (3.2)	0.047 (1.2)	.020 (0.5) ± .003 (0.07)	1 roll (cont.)
Fig. 58	* XPS-187-CONT	B-342	Black on White	20 to 10	0.062 (1.6) - 0.150 (3.8)	8 ft (2.45m)	0.187 (4.7)	0.062 (1.6)	.020 (0.5) ± .003 (0.07)	1 roll (cont.)
Fig. 58	* XPS-250-CONT	B-342	Black on White	16 to 8	0.094 (2.4) - 0.215 (5.5)	8 ft (2.45m)	0.250 (6.4)	0.093 (2.4)	.025 (0.6) ± .003 (0.07)	1 roll (cont.)
Fig. 58	* XPS-375-CONT	B-342	Black on White	12 to 4	0.125 (3.2) - 0.320 (8.13)	8 ft (2.45m)	0.375 (9.5)	0.125 (3.1)	.025 (0.6) ± .003 (0.07)	1 roll (cont.)
Fig. 58	* XPS-125-CONT-YL-BK	B-342	Black on Yellow	22 to 16	0.046 (1.2) - 0.110 (2.8)	8 ft (2.45m)	0.125 (3.2)	0.047 (1.2)	.020 (0.5) ± .003 (0.07)	1 roll (cont.)
Fig. 58	* XPS-187-CONT-YL-BK	B-342	Black on Yellow	20 to 10	0.062 (1.6) - 0.150 (3.8)	8 ft (2.45m)	0.187 (4.7)	0.062 (1.6)	.020 (0.5) ± .003 (0.07)	1 roll (cont.)
Fig. 58	* XPS-250-CONT-YL-BK	B-342	Black on Yellow	16 to 8	0.094 (2.4) - 0.215 (5.5)	8 ft (2.45m)	0.250 (6.4)	0.093 (2.4)	.025 (0.6) ± .003 (0.07)	1 roll (cont.)

\* ⚠ **WARNING:** Cancer www.P65Warnings.ca.gov