



Find your ideal combination

Philips Fortimo and Lexel modules, drivers and cables

December 2011

PHILIPS
sense and simplicity

Content

Fortimo LED decorative modules

Fortimo LED disk modules

Fortimo LED downlight module (DLM)

Fortimo LED downlight module (DLM) Food

Fortimo LED downlight module Twistable (TDLM)

Fortimo LED integrated spot module

Fortimo LED high brightness module (HBM)

Fortimo LED linear light module (LLM)

Fortimo LED linear light module Solar (LLM)

Fortimo LED spotlight module (SLM) Gen1

Fortimo LED spotlight module (SLM) Gen2

Lexel LED downlight module (DLM)

Lexel LED spotlight module (SLM)

Fortimo LED strip system

Module type			Suitable driver and cable combination					
	Logistic code	European code	Driver	Logistic code	European code	Cable	Logistic code	European code
	12NC	EOC		12NC	EOC		12NC	EOC

Fortimo LED decorative modules

300 lumen								
Fortimo deco mini spot 300 827 10V	929000663008	871829115835600	Xitanium LED driver 10W/0.70A-14V DIM	913710053666	871016306416130	None (cables connected to modules)		
Fortimo deco mini spot 300 840 10V	929000662908	871829115837000	Xitanium LED driver 30W/0.70A-42V DIM	913710053866	871016306418530			
Fortimo deco mini downlight 300 827 10V	929000663108	871829115839400	Xitanium LED dimmable driver 20/30W 42V	913713220162	871016384331600			
Fortimo deco mini downlight 300 840 10V	929000663208	871829115841700	(independent)					
Fortimo deco mini strip 300 40D 827 10V	929000663408	871829115843100						
Fortimo deco mini strip 300 40D 840 10V	929000669908	871829115845500						
Fortimo deco mini strip 300 100D 827 10V	929000663308	871829115847900						
Fortimo deco mini strip 300 100D 840 10V	929000670008	871829115849300						

Module type			Suitable driver and cable combination					
	Logistic code	European code	Driver	Logistic code	European code	Cable	Logistic code	European code
	12NC	EOC		12NC	EOC		12NC	EOC

Fortimo LED disk modules

300 lumen								
Fortimo LED disk module 300/827 230V	929000662803	871829116719800	None, integrated system			None, integrated system		
800 lumen								
Fortimo LED disk module 800/840 230V	929000664608	871829115277400	None, integrated system			None, integrated system		
Fortimo LED disk module 800/927 230V W	929000303501	871829111500700						

Module type			Suitable driver and cable combination					
	Logistic code	European code	Driver	Logistic code	European code	Cable	Logistic code	European code
	12NC	EOC		12NC	EOC		12NC	EOC
Fortimo LED downlight module (DLM)								
1100 lumen								
Fortimo LED DLM 1100 10W/850 Gen3	929000660703	871829114388800	Fortimo LED driver 1100-3000 (new) (successor of Fortimo LED driver 1100-2000)	929000614403	872790092085700	Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
Fortimo LED DLM 1100 11W/835 Gen3	929000660503	871829114386400				LED DLM cable 60 cm	929000484803	872790087989600
Fortimo LED DLM 1100 11W/840 Gen3	929000660603	871829114387100	Xitanium 45W 200-700mA 80V I 230V (successor of Fortimo driver 1100-2000/I)	929000614503	872790092083300	LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire	929000615203	872790093129700
Fortimo LED DLM 1100 12W/830 Gen3	929000660403	871829114385700	Fortimo LED driver 1100-3000/TD	929000465003	872790084297500	Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
						LED DLM cable 60 cm	929000484803	872790087989600
			Fortimo LED driver 1100-3000 TD/I	929000465203	872790086270600	LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire	929000615203	872790093129700
			Xitanium 25W 0.3-0.7A 36V I 230V	929000600203	872790090096500	Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
						LED DLM cable 60 cm	929000484803	872790087989600
			Xitanium 25W 0.3-1A 36V TD/I 230V	929000600403	872790091434400	Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
						LED DLM cable 60 cm	929000484803	872790087989600
			Xitanium 25W/0.3-1A 36V TD/Is 230V	929000485803	872790091435100	Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
			LED DLM cable 60 cm	929000484803	872790087989600			
			Xitanium 25W 0.3-0.7A 36V TE/I 230V	929000600303	872790090730800	Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
						LED DLM cable 60 cm	929000484803	872790087989600
2000 lumen								
Fortimo LED DLM 2000 20W/850 Gen3	929000661103	871829114392500	Fortimo LED driver 1100-3000 (new)	929000614403	872790092085700	Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
Fortimo LED DLM 2000 22W/840 Gen3	929000661003	871829114391800	(successor of Fortimo LED driver 1100-2000)			LED DLM cable 60 cm	929000484803	872790087989600
Fortimo LED DLM 2000 23W/835 Gen3	929000660903	871829114390100	Xitanium 45W 200-700mA 80V I 230V (successor of Fortimo driver 1100-2000/I)	929000614503	872790092083300	LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire	929000615203	872790093129700
Fortimo LED DLM 2000 24W/830 Gen3	929000660803	871829114389500	Fortimo LED driver 1100-3000/TD	929000465003	872790084297500	Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
						LED DLM cable 60 cm	929000484803	872790087989600
			Fortimo LED driver 1100-3000 TD/I	929000465203	872790086270600	LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire	929000615203	872790093129700
						LED DLM cable 60 cm	929000484803	872790087989600
			Xitanium 50W 0.3-1A 62V 230V	929000636303	871829113782500	Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
						LED DLM cable 60 cm	929000484803	872790087989600
			Xitanium 50W SH 0.3-1A 62V I 230V	929000617403	871829113780100	LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire	929000615203	872790093129700
						Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
			Xitanium 50W SH 0.3-1A 62V TD/TE/I 230V	929000617203	871829111948700	LED DLM cable 60 cm /I 12V / 60 cm cable with earth wire	929000615203	872790093129700
						LED DLM cable 60 cm	929000484803	872790087989600

3000 lumen								
Fortimo LED DLM 3000 38W/850 Gen3	929000619103	871829114396300	Fortimo LED driver 1100-3000 (new) (successor of Fortimo LED driver 1100-2000)	929000614403	872790092085700	Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
Fortimo LED DLM 3000 41W/840 Gen3	929000660303	871829114395600				LED DLM cable 60 cm	929000484803	872790087989600
Fortimo LED DLM 3000 44W/830 Gen3	929000618903	871829114393200	Xitanium 45W 200-700mA 80V I 230V (successor of Fortimo LED driver 1100-2000/I)	929000614503	872790092083300	LED DLM cable 60 cm / I 12V / 60 cm cable with earth wire	929000615203	872790093129700
Fortimo LED DLM 3000 44W/835 Gen3	929000619003	871829114394900	FortimoLEDdriver1100-3000/TD	929000465003	872790084297500	Fortimo LED DLM cable 1100-2000 / 25 cm	929000463103	872790080709700
						LED DLM cable 60 cm	929000484803	872790087989600
			Fortimo LED driver 1100-3000 TD/I	929000465203	872790086270600	LED DLM cable 60 cm / I 12V / 60 cm cable with earth wire	929000615203	872790093129700

Module type	Suitable driver and cable combination									
	Logistic code	European code	Driver	Logistic code	European code	Cable	Logistic code	European code		
	12NC	EOC		12NC	EOC		12NC	EOC		
Fortimo LED downlight module (DLM) Food										
2000 lumen										
Fortimo LED DLM 2000 50W/Food30	929000478003	872790086576900	Fortimo LED DLM driver 2000 50W/Food 120-277V	929000478103	872790086578300	Fortimo LED DLM cable Food / 25 cm	929000478203	872790086580600		
Fortimo LED DLM 2000 50W/Food40	929000478703	872790086575200				LED DLM cable 25 cm	929000666103			
						LED DLM cable 60 cm	929000484803	872790087989600		
Fortimo LED downlight module Twistable										
1100 lumen										
Fortimo TDLM 1100 18W/840 230V	929000499103	872790090534200	Not applicable, power on board			Fortimo TDLM LH 1100 230V	929000499503	872790092368100		
Fortimo TDLM 1100 20W/827 230V	929000498903	872790090536600								
Fortimo TDLM 1100 20W/830 230V	929000499003	872790090535900								
2000 lumen										
Fortimo TDLM 2000 32W/830 230V	929000638003	871829114933000	Not applicable, power on board			On request				
Fortimo TDLM 2000 32W/840 230V	929000638103	871829114934700								

Module type			Suitable driver and cable combination					
	Logistic code 12NC	European code EOC	Driver	Logistic code 12NC	European code EOC	Cable	Logistic code 12NC	European code EOC
Fortimo LED high brightness module (HBM)								
4000/6000 lumen, one module on one driver								
Fortimo LED HBM 4000 35W/757	929000636603	871829114379600	Xitanium 75W 0.35-0.7A GL Prog sXt	929000702302	871829111887900	Fortimo HBM cable 60 cm	929000659803	871829114382600
Fortimo LED HBM 4000 40W/641	929000636503	871829114378900						
Fortimo LED HBM 4000 45W/740	929000665003	871829116117200						
Fortimo LED HBM 6000 52W/757	929000636803	871829114381900						
Fortimo LED HBM 6000 59W/641	929000636703	871829114380200						
Fortimo LED HBM 6000 68W/740	929000665103	871829116119600						
4000/6000 lumen, two modules on one driver								
Fortimo LED HBM 4000 35W/757 x2	929000636603	871829114379600	Xitanium 150W 0.35-0.7A GL Prog sXt	929000702202	872790078351300	Fortimo HBM Cable 60 cm, x2	929000659803	871829114382600
Fortimo LED HBM 4000 40W/641 x2	929000636503	871829114378900						
Fortimo LED HBM 4000 45W/740 x2	929000665003	871829116117200						
Fortimo LED HBM 6000 52W/757 x2	929000636803	871829114381900						
Fortimo LED HBM 6000 59W/641 x2	929000636703	871829114380200						
Fortimo LED HBM 6000 68W/740 x2	929000665103	871829116119600						
Fortimo LED integrated spot module								
600 lumen								
Fortimo integrated spot 600 827 15D 230V	9290 006 94508	8718291 199564 00	Non, integrated system					
Fortimo integrated spot 600 827 24D 230V	9290 006 94608	8718291 199588 00						
Fortimo integrated spot 600 827 36D 230V	9290 006 94708	8718291 199601 00						
Fortimo integrated spot 600 830 15D 230V	9290 006 94808	8718291 199625 00						
Fortimo integrated spot 600 830 24D 230V	9290 006 94908	8718291 199649 00						
Fortimo integrated spot 600 830 36D 230V	9290 006 95008	8718291 199663 00						
Fortimo integrated spot 600 840 15D 230V	9290 006 95108	8718291 199687 00						
Fortimo integrated spot 600 840 24D 230V	9290 006 95208	8718291 199700 00						
Fortimo integrated spot 600 840 36D 230V	9290 006 95308	8718291 199724 00						

Module type			Suitable driver and cable combination					
	Logistic code 12NC	European code EOC	Driver	Logistic code 12NC	European code EOC	Cable	Logistic code 12NC	European code EOC
Fortimo LED linear light module (LLM)								
1100 lumen								
Fortimo LED LLM 1100 13W/730	929000634903	871829111532800	Xitanium 35W 0.20-0.70A 230V Otd	929000634003	871829112003200	Fortimo LLM cable 25 cm	929000483303	872790086714500
			Xitanium 35W 0.20-0.70A LS6 230V Otd	929000634103	871829112004900	Fortimo LLM cable 25 cm	929000483303	872790086714500
			Xitanium 35W 0.20-0.70A LS8 230V Otd	929000634203	8718291 120056 00	Fortimo LLM cable 25 cm	929000483303	872790086714500
Fortimo LED LLM 1100 11W/740	929000616103	871829112218000	Xitanium 35W 0.20-0.70A 230V Otd	929000634003	871829112003200	Fortimo LLM cable 25 cm	929000483303	872790086714500
			Xitanium 35W 0.20-0.70A LS6 230V Otd	929000634103	871829112004900	Fortimo LLM cable 25 cm	929000483303	872790086714500
			Xitanium 35W 0.20-0.70A LS8 230V Otd	929000634203	8718291 120056 00	Fortimo LLM cable 25 cm	929000483303	872790086714500
Fortimo LED LLM 1100 12W/840	929000615703	871829111533500	on request					
1800 lumen								
Fortimo LED LLM 1800 20W/730	929000635003	871829111534200	Xitanium 35W 0.20-0.70A 230V Otd	929000634003	871829112003200	Fortimo LLM cable 25 cm	929000483303	872790086714500
			Xitanium 35W 0.20-0.70A LS6 230V Otd	929000634103	871829112004900	Fortimo LLM cable 25 cm	929000483303	872790086714500
			Xitanium 35W 0.20-0.70A LS8 230V Otd	929000634203	871829112005600	Fortimo LLM cable 25 cm	929000483303	872790086714500
Fortimo LED LLM 1800 18W/740	929000615903	871829112217300	Xitanium 35W 0.20-0.70A 230V Otd	929000634003	871829112003200	Fortimo LLM cable 25 cm	929000483303	872790086714500
			Xitanium 35W 0.20-0.70A LS6 230V Otd	929000634103	871829112004900	Fortimo LLM cable 25 cm	929000483303	872790086714500
			Xitanium 35W 0.20-0.70A LS8 230V Otd	929000634203	8718291 120056 00	Fortimo LLM cable 25 cm	929000483303	872790086714500
Fortimo LED LLM 1800 20W/840	929000616003	871829112001800	on request					
3000 lumen								
Fortimo LED LLM 3000 34W/730	929000611303	872790090365200	Xitanium 75W 0.35-0.70A 1-10V 230V sXt + integrated cable	913701217502	872790092567800	No separate cable needed		
Fortimo LED LLM 3000 33W/740	929000611403	872790090366900	Xitanium 75W 0.35-0.7A GL Prog sXt	929000702302	871829111887900	No cable released; need 6 pins to flying leads		
			Xitanium 75W 0.35-0.70A 1-10V 230V sXt +	913701217502	872790092567800	No separate cable needed		
4500 lumen								
Fortimo LED LLM 4500 53W/730	929000611103	872790090363800	Xitanium 75W 0.35-0.70A 1-10V 230V sXt + integrated	913701217502	872790092567800	No separate cable needed		
			Xitanium 75W 0.35-0.7A GL Prog sXt	929000702302	871829111887900	No cable released; need 6 pins to flying leads		
Fortimo LED LLM 4500 50W/740	929000611203	872790090364500	Xitanium 75W 0.35-0.70A 1-10V 230V sXt + integrated	913701217502	872790092567800	No separate cable needed		
			Xitanium 75W 0.35-0.7A GL Prog sXt	929000702302	871829111887900	No cable released; need 6 pins to flying leads		
1800 lumen (two modules on one driver)								
Fortimo LED LLM 1800 20W/730 (2x)	929000635003	871829111534200	Xitanium 75W 0.35-0.7A GL Prog sXt	929000702302	871829111887900	No cable released; need 5 pins to flying leads x2		
Fortimo LED LLM 1800 18W/740 (2x)	929000615903	871829112217300	Xitanium 75W 0.35-0.7A GL Prog sXt	929000702302	871829111887900	No cable released; need 5 pins to flying leads x2		
3000 lumen (two modules on one driver)								
Fortimo LED LLM 3000 34W/730 (2x)	929000611303	872790090365200	Xitanium 150W 0.35-0.7A GL Prog sXt	929000702202	8727900783513 00	No cable released; need 6 pins to flying leads x2		
Fortimo LED LLM 3000 33W/740 (2x)	929000611403	872790090366900	Xitanium 150W 0.35-0.7A GL Prog sXt	929000702202	8727900783513 00	No cable released; need 6 pins to flying leads x2		
4500 lumen (two modules on one driver)								
Fortimo LED LLM 4500 53W/730 (2x)	929000611103	872790090363800	Xitanium 150W 0.35-0.7A GL Prog sXt	929000702202	8727900783513 00	No cable released; need 6 pins to flying leads x2		
Fortimo LED LLM 4500 50W/740 (2x)	929000611203	872790090364500	Xitanium 150W 0.35-0.7A GL Prog sXt	929000702202	8727900783513 00	No cable released; need 6 pins to flying leads x2		

Module type			Suitable driver and cable combination					
	Logistic code	European code	Driver	Logistic code	European code	Cable	Logistic code	European code
	12NC	EOC		12NC	EOC		12NC	EOC
Fortimo LED linear light module (LLM) Solar								
1800 lumen								
Fortimo LED LLM 1800 20W/730	929000635003	871829111534200	Xitanium 40W 0.2-0.7A LS 12-24VDC (Solar driver)	929000611903	872790092559300	50cm	929000615103	872790093033700
Fortimo LED LLM 1800 18W/740	929000615903	871829112217300						
Fortimo LED LLM 1800 20W/840	929000616003	871829112001800						
3000 lumen								
Fortimo LED LLM 3000 34W/730	929000611303	872790090365200	Xitanium 40W 0.2-0.7A LS 12-24VDC (Solar driver)	929000611903	872790092559300	50cm	929000614903	872790093031300
Fortimo LED LLM 3000 33W/740	929000611403	872790090366900						
4500 lumen								
Fortimo LED LLM 4500 53W/730 DS	929000612103	872790092032100	Xitanium 70W 0.2-0.7A LS 12-24VDC (Solar driver)	929000612003	872790092560900	Cable Fortimo Solar LLM driver 4500lm	50929000615003	872790093032000
Fortimo LED LLM 4500 48W/740 DS	929000612203	872790092033800						

Module type	Suitable driver and cable combination							
	Logistic code	European code	Driver	Logistic code	European code	Cable	Logistic code	European code
	12NC	EOC		12NC	EOC		12NC	EOC
Fortimo LED spotlight module (SLM) - Gen1								
800/1100 lumen - Gen1								
Fortimo LED SLM 800 10W/835	929000621503	871829111866400	Xitanium 25W 0.3-0.7A 36V I 230V	929000600203	872790090096500	Fortimo LED SLM cable 25 cm	929000614703	872790092152600
Fortimo LED SLM 800 10W/840	929000621603	871829111867100	Xitanium 25W 0.3-0.7A 36V TE/I 230V	929000600303	872790090730800	Fortimo LD SLM cable 60 cm	929000619203	872790095423400
Fortimo LED SLM 800 11W/830	929000621403	871829111865700	Xitanium 25W 0.3-1A 36V TD/I 230V	929000600403	872790091434400	Fortimo LED SLM cable 60 cm, 12V	929000632903	872790095424100
Fortimo LED SLM 1100 15W/840	929000612903	872790091410800	Xitanium 25W 0.3-1A 36V TD/Is 230V	929000485803	872790091435100			
Fortimo LED SLM 1100 17W/830	929000611503	872790091406100	Fortimo LED Driver 1100-3000	929000614403	872790092085700			
Fortimo LED SLM 1100 17W/835	929000612703	872790091408500	Fortimo LED Driver 1100-3000/TD	929000465003	872790084297500			
			Fortimo LED Driver 1100-3000/I	929000465103	872790082522000			
			Fortimo LED Driver 1100-3000/TDI	929000465203	872790086270600			
			Xitanium 45W 200-700mA 80V I 230V	929000614503	872790092083300			
1500/2000 lumen - Gen1								
Fortimo LED SLM 1500 19W/840	929000621903	871829111864000	Xitanium 50W/s 0.3-1A 62V 230V	929000636403	871829113781800	Fortimo LED SLM cable 25 cm	929000614703	872790092152600
Fortimo LED SLM 1500 20W/830	929000621703	871829111862600	Xitanium 50W 0.3-1A 62V 230V	929000636303	871829113782500	Fortimo LED SLM cable 60 cm	929000619203	872790095423400
Fortimo LED SLM 1500 20W/835	929000621803	871829111863300	Xitanium 50W 0.3-1A 62V TD/TE 230V	929000661203	871829115712000	Fortimo LED SLM cable 60 cm, 12 V	929000632903	872790095424100
Fortimo LED SLM 2000 29W/840	929000613003	872790091411500	Xitanium 50W SH 0.3-1A 62V I 230V	929000617403	871829113780100			
Fortimo LED SLM 2000 32W/830	929000611603	872790091407800	Xitanium 50W LH 0.3-1A 62V TD/TE/I 230V	929000617103	871829111947000			
Fortimo LED SLM 2000 32W/835	929000612803	872790091409200	Xitanium 50W SH 0.3-1A 62V TD/TE/I 230V	929000617203	871829111948700			
			Fortimo LED Driver 1100-3000	929000614403	872790092085700			
			Fortimo LED Driver 1100-3000/TD	929000465003	872790084297500			
			Fortimo LED Driver 1100-3000/I	929000465103	872790082522000			
			Fortimo LED Driver 1100-3000/TDI	929000465203	872790086270600			
			Xitanium 45W 200-700mA 80V I 230V	929000614503	872790092083300			
3000 lumen - Gen1								
Fortimo LED SLM 3000 38W/840	929000635903	871829111861900	Xitanium 50W/s 0.3-1A 62V 230V	929000636403	871829113781800	Fortimo LED SLM cable 25 cm	929000614703	872790092152600
Fortimo LED SLM 3000 43W/830	929000635703	871829111859600	Xitanium 50W 0.3-1A 62V 230V	929000636303	871829113782500	Fortimo LED SLM cable 60 cm	929000619203	872790095423400
Fortimo LED SLM 3000 41W/835	929000635803	871829111860200	Xitanium 50W 0.3-1A 62V TD/TE 230V	929000661203	871829115712000	Fortimo LED SLM cable 60 cm, 12 V	929000632903	872790095424100
			Xitanium 50W SH 0.3-1A 62V I 230V	929000617403	871829113780100			
			Xitanium 50W LH 0.3-1A 62V TD/TE/I 230V	929000617103	871829111947000			
			Xitanium 50W SH 0.3-1A 62V TD/TE/I 230V	929000617203	871829111948700			

Module type	Suitable driver and cable combination							
	Logistic code	European code	Driver	Logistic code	European code	Cable	Logistic code	European code
	12NC	EOC		12NC	EOC		12NC	EOC
Fortimo LED spotlight module (SLM) - Gen2								
2000 lumen - Gen2								
Fortimo LED SLM 2000 25W/827 L19 G2	9290 006 75403	871829118627400	Xitanium 50W/s 0.3-1A 62V 230V	929000636403	871829113781800	Fortimo LED SLM cable 25 cm	929000614703	872790092152600
Fortimo LED SLM 2000 23W/830 L19 G2	9290 006 75803	871829118631100	Xitanium 50W 0.3-1A 62V 230V	929000636303	871829113782500	Fortimo LED SLM cable 60 cm	929000619203	872790095423400
Fortimo LED SLM 2000 22W/835 L19 G2	9290 006 76203	871829118638000	Xitanium 50W 0.3-1A 62V TD/TE 230V	929000661203	871829115712000	Fortimo LED SLM cable 60 cm, 12 V	929000632903	872790095424100
Fortimo LED SLM 2000 20W/840 L19 G2	9290 006 76403	871829118678600	Xitanium 50W SH 0.3-1A 62V I 230V	929000617403	871829113780100			
			Xitanium 50W LH 0.3-1A 62V TD/TE/I 230V	929000617103	871829111947000			
			Xitanium 50W SH 0.3-1A 62V TD/TE/I 230V	929000617203	871829111948700			
			Fortimo LED Driver 1100-3000	929000614403	872790092085700			
			Fortimo LED Driver 1100-3000/TD	929000465003	872790084297500			
			Fortimo LED Driver 1100-3000/I	929000465103	872790082522000			
			Fortimo LED Driver 1100-3000/TDI	929000465203	872790086270600			
			Xitanium 45W 200-700mA 80V I 230V	929000614503	872790092083300			
2000/3000 lumen - Gen2								
Fortimo LED SLM 2000 34W/927 L19 G2	9290 006 75603	87182911 8629800	Xitanium 50W/s 0.3-1A 62V 230V	929000636403	871829113781800	Fortimo LED SLM cable 25 cm	929000614703	872790092152600
Fortimo LED SLM 2000 31W/930 L19 G2	9290 006 76003	87182911 8636600	Xitanium 50W 0.3-1A 62V 230V	929000636303	871829113782500	Fortimo LED SLM cable 60 cm	929000619203	872790095423400
Fortimo LED SLM 3000 42W/827 L19 G2	9290 006 76503	87182911 8680900	Xitanium 50W 0.3-1A 62V TD/TE 230V	929000661203	871829115712000	Fortimo LED SLM cable 60 cm, 12 V	929000632903	872790095424100
Fortimo LED SLM 3000 39W/830 L19 G2	9290 006 76903	87182911 8684700	Xitanium 50W SH 0.3-1A 62V I 230V	929000617403	871829113780100			
Fortimo LED SLM 3000 40W/835 L19 G2	9290 006 77303	87182911 8682300	Xitanium 50W LH 0.3-1A 62V TD/TE/I 230V	929000617103	871829111947000			
Fortimo LED SLM 3000 36W/840 L19 G2	9290 006 77503	87182911 8686100	Xitanium 50W SH 0.3-1A 62V TD/TE/I 230V	929000617203	871829111948700			

Module type			Suitable driver and cable combination					
	Logistic code	European code	Driver	Logistic code	European code	Cable	Logistic code	European code
	12NC	EOC		12NC	EOC		12NC	EOC
Lexel LED downlight module (DLM)								
1100 lumen								
Lexel LED DLM module 1100 2700-6500	929000463203	872790081322700	Lexel LED DLM driver 1100 DALI/DMX	929000484203	872790088575000	Lexel LED DLM cable 1100	929000463503	872790081324100
						LED DLM cable 60 cm	929000484803	872790087989600
						LED DLM cable 60cm // 12V	929000615203	872790093129700
2000 lumen								
Lexel LED DLM module 2000 2700-6500	929000659903	871829113935500	Lexel LED DLM driver 1100 DALI/DMX	929000484203	872790088575000	Lexel LED DLM cable 1100	929000463503	872790081324100
						LED DLM cable 60 cm	929000484803	872790087989600
						LED DLM cable 60cm // 12V	929000615203	872790093129700
Lexel LED spotlight module (SLM)								
800 lumen								
Lexel LED SLM module 800 25W/RGB	929000620303	872790095416600	Lexel LED driver 25W - DMX	929000632703	871829112509900	Lexel LED SLM cable 25 cm or	929000620403	872790095417300
						Lexel LED SLM cable 60 cm and	929000633203	872790095420300
						Lexel LED SLM DMX/4B cable 60 cm FL	929000661303	871829113937900
			Lexel LED driver 25W - DALI	929000620503	871829112508200	Lexel LED SLM cable 25 cm or	929000620403	872790095417300
						Lexel LED SLM cable 60 cm and	929000633203	872790095420300
			Lexel LED driver 25W - 4B	929000632803	871829112510500	Lexel LED SLM cable 25 cm or	929000620403	872790095417300
						Lexel LED SLM cable 60 cm and	929000633203	872790095420300
						Lexel LED SLM DMX/4B cable 60 cm FL	929000661303	871829113937900
1100 lumen								
Lexel LED SLM module 1100 22W/8TV	929000620203	872790095415900	Lexel LED driver 25W - DMX TW	929000659703	871829114017700	Lexel LED SLM cable 25 cm or	929000620403	872790095417300
						Lexel LED SLM cable 60 cm and	929000633203	872790095420300
						Lexel LED SLM DMX/4B cable 60 cm FL	929000661303	871829113937900
			Lexel LED driver 25W - DALI	929000620503	871829112508200	Lexel LED SLM cable 25 cm or	929000620403	872790095417300
						Lexel LED SLM cable 60 cm	929000633203	872790095420300
			Lexel LED driver 25W - 4B	929000632803	871829112510500	Lexel LED SLM cable 25 cm or	929000620403	872790095417300
						Lexel LED SLM cable 60 cm and	929000633203	872790095420300
						Lexel LED SLM DMX/4B cable 60 cm FL	929000661303	871829113937900

Module type				Suitable driver and cable combination					
	Logistic	European	Nr. of strips	Driver	Logistic	European	Cable driver to module	Logistic	European
	code	code			code	code		code	code
	12NC	EOC			12NC	EOC		12NC	EOC

Fortimo LED strip system

630 lumen									
Fortimo LED Strip 280mm 630lm 830	9290 006 68803	8718291161738 00	5	Xitanium 75W 200mA 200V TD 230V	929000661803	871829115255200	Fortimo LED strip cable 60cm	9290 006 37703	87182911 51456 00
			6	Xitanium 75W 240mA 200V TD 230V	929000661903	871829115256900			
			7	Xitanium 75W 280mA 200V TD 230V	929000662003	871829115257600			
			8	Xitanium 75W 320mA 200V TD 230V	929000662103	871829115258300			
			9	Xitanium 75W 360mA 200V TD 230V	929000662203	871829115259000			
			10	Xitanium 75W 0.15-0.4A 200V TD 230V	9290 006 70403	87182911 68188 00			
Fortimo LED Strip 280mm 630lm 840	9290 006 37603	87182911 50008 00	5	Xitanium 75W 200mA 200V TD 230V	929000661803	871829115255200	Fortimo LED strip cable 60cm	9290 006 37703	87182911 51456 00
			6	Xitanium 75W 240mA 200V TD 230V	929000661903	871829115256900			
			7	Xitanium 75W 280mA 200V TD 230V	929000662003	871829115257600			
			8	Xitanium 75W 320mA 200V TD 230V	929000662103	871829115258300			
			9	Xitanium 75W 360mA 200V TD 230V	929000662203	871829115259000			
			10	Xitanium 75W 0.15-0.4A 200V TD 230V	9290 006 70403	87182911 68188 00			
Fortimo LED Strip 280mm 630lm 865	9290 006 69003	8718291161783 00	5	Xitanium 75W 200mA 200V TD 230V	929000661803	871829115255200	Fortimo LED strip cable 60cm	9290 006 37703	87182911 51456 00
			6	Xitanium 75W 240mA 200V TD 230V	929000661903	871829115256900			
			7	Xitanium 75W 280mA 200V TD 230V	929000662003	871829115257600			
			8	Xitanium 75W 320mA 200V TD 230V	929000662103	871829115258300			
			9	Xitanium 75W 360mA 200V TD 230V	929000662203	871829115259000			
			10	Xitanium 75W 0.15-0.4A 200V TD 230V	9290 006 70403	87182911 68188 00			



©2011 Koninklijke Philips Electronics N.V.
All rights reserved. Data subject to change.

www.philips.com/fortimo
www.philips.com/oem