



Connectors > Connector Accessories > Connector Adapters & Connector Savers



Connector Interface Adapter Type: **Between Series Adapter**
Body Orientation: **Straight**
Side A Interface: **SMB**
Side A Gender: **Plug**
Side B Interface: **FAKRA**

Features

Product Type Features

Connector Interface Adapter Type	Between Series Adapter
Side A Interface	SMB
Side A Gender	Plug
Side B Interface	FAKRA
Side B Gender	Receptacle
Connector System	Cable-to-Cable
Sealable	Yes

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Plating Material	Nickel
Body Material	Zinc Alloy



Contact Features

Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Body Orientation	Straight
------------------	----------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series

FAKRA

Connector Adapters & Connector Savers(6)

Infotainment & Multimedia Cable Assemblies(31)

Other Automotive Connector Accessories(39)

SMB RF Connectors(2)

Customers Also Bought

TE Part #2326896-1
COAX,SOC HSG TRMNL BLOCK, UNSLD,180DEG

TE Part #2326910-3
FAKRA AUT,SOC HSG,UNSLD, 180DEG,COD C

TE Part #2333210-1
1POS,FAKRA AUT,HDR ASSY,180DEG, COD A

TE Part #2-2333210-1
1POS,FAKRA AUT,HDR ASSY,180DEG, COD A

TE Part #2338810-1
FLOATING HD CAMERA,SOCKET, ASSEMBLY

TE Part #2380000-1
SMB HEADER, ASSEMBLY

TE Part #2380551-3
FAKRA AUT,SOC HSG ,SLD,180DEG, COD C

TE Part #2390730-3
ADAPTOR SMB TO FAKRA,ASSY, 180DEG,COD C

TE Part #2338810-3
FLOATING HD CAMERA,SOCKET, ASSEMBLY

TE Part #2419600-3
Camera FAKRA Floating Adaptor, Assy, C

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_2390730-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2390730-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2390730-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English