

Wieland Electric



Datasheet

Item No. 70.300.1640.0

Female insert BAS BUS 16 2,5 50

revos BASIC 500V 16 pole + ground, female insert 500V/16A with wire protection, Sn screw connection



Item No.	70.300.1640.0
EAN	4015573219625
order unit	10 Piece(s)













Technical data

General		
Model	Female insert	
Inflammability class of insulation material acc. with UL94	Vo	
Colour	Grey	
Mating cycles	200	
Pollution degree	3	
Modular version	No	
Operating temperature range min.	-40 °C	
Operating temperature range max.	120 °C	
Connection Data		
Connection type	Screw connection	
Number of poles	16	
Plus switching contacts	0	
Number of pole for rated current 2	0	
Number of pole for rated current 3	0	
Total number of poles (without ground contact)	16	
With wire protection	Yes	
Conductor cross section rigid (solid, stranded)	2.5	
Protective contact	Yes	
Technical Data UL/CSA		
Rated voltage according to UL/CSA	600	
Rated current according UL	16	
Rated current according CSA	16	



Min. conductor cross section flexible wire	0.5	
Max. conductor cross section flexible wire	2.5	
Conductor cross section flexible AWG wire	22-14 AWG	
Model		
With housing	No	
Contacts		
Contact material	Copper alloy	
Surface	Tin-plated	
Contact resistance	1.5 mOhm	
Wire strip length	7 mm	
Screws head design/recomm. Torque		
Mounting screws	H1/0.5-0.7 Nm	
Clamping screws	H1/0.5-0.7 Nm	
Ground conductor screws	H2/1.2-1.6 Nm	
Technical Data DIN EN 61984		
Nominal voltage	500	
Rated voltage face/ground	500	
Nominal current	16	
Rated impulse voltage	6	
	·	





Drawings

