

SCC 1500™

Sizes on Page 2

Static Shielding Bag ~ Metal-Out


SCC 1500 metal-out static shielding bags are approved by major computer, electronics, and disk drive manufacturers for use worldwide. Our transparent, metalized static shield bag structure provides a static safe environment for sensitive electronic devices. Provides low charge retention and rapid static decay. Bags are lot coded for QC traceability.

Standards

Meets the requirements of MIL-PRF-81705 Type III, EIA 541, EIA 625, MIL-HDBK-263, MIL-STD-1686, EOS/ESD Standards, and charge retention standards.

Specifications


Electrical Properties:		Typical Values	
Surface Resistivity / Resistance	ASTM D257	or	ANSI/ESD STM11.11
Interior	>10 ⁵ <10 ¹² ohms/square	or	>10 ⁴ <10 ¹¹ ohms
Exterior	<10 ⁵ ohms/square	or	< 10 ⁴ ohms
Metal	100 ohms		
Static Shielding	< 30 volts		MIL-PRF-81705, EIA 541
Static Shielding	< 10 nJ		EOS/ESD S11.31
Static Decay	< 0.05 seconds		MIL-PRF-81705, FTMS 101 MTH 4046
Charge Retention	< 100 volts		
Physical Properties:			
Tensile Strength	>20 lbs		ASTM D 882
Seam Strength	Pass		MIL-PRF-81705
Light Transmission	40 %		Tobias
Heat Sealing Conditions			
Temperature	250 F - 375 F		
Time	0.5 - 3.5 seconds		
Pressure	30 - 70 PSI		
Thickness	3.1 mils		SCC 008
Outgassing	Pass		ASTM E595
Non-corrosive	Pass		FTMS 101 MTH 3005



SCC 1500 with Open Top

Material Structure

SCC 1500 flat and ZipTop static shielding bags are manufactured using a proprietary top coating. The top coating and metal layer provide low charge retention and Faraday Effect shielding of an Electrostatic Discharge (ESD) with the associated electrostatic fields. Polyester dielectric stops the current from ESD. Tribocharging is minimized by the specially processed polyethylene.



See SCC Data Sheets for these related items:

- Static Warning Labels
- Heat Sealer

P R O D U C T D A T A S H E E T

SCC 1500 Static Shielding Bag METAL-OUT

PRODUCT	ITEM NUMBER	DATASHEET
STATIC SHIELDING BAG, OPEN TOP AND ZIPTOP	150(W")(L")	1101-B




US and Canada: 866-722-3736
 Fax: 866-722-3735
 Intl: 919-774-3808
 Fax: 919-774-1287
 3010 Lee Avenue Sanford, NC 27330
 email: info@staticcontrol.com
 www.**StaticControl.com** ©

SCC 1500™

Open Top Static Shielding Bag ~ Metal-Out

W"x L"	P/N	W"x L"	P/N	W"x L"	P/N
3 x 5	15035	8 x 10	150810	12 x 16	1501216
4 x 6	15046	8 x 12	150812	12 x 18	1501218
5 x 8	15058	9 x 12	150912	14 x 18	1501418
6 x 8	15068	10 x 12	1501012	15 x 18	1501518
6 x 10	150610	10 x 14	1501014	16 x 24	1501624
6 x 30	150630	10 x 24	1501024	18 x 18	1501818
7 x 15	150715	11 x 15	1501115	18 x 24	1501824



SCC 1500 ZipTop™

Recloseable Static Shielding Bag ~ Metal-Out

W"x L"	P/N	W" x L"	P/N	W" x L"	P/N
3 x 5	150Z35	5 x 8	150Z58	8 x 10	150Z810
4 x 4	150Z44	6 x 8	150Z68	10 x 12	150Z1012
4 x 6	150Z46	6 x 10	150Z610	12 x 18	150Z1218

- All standard sizes in-stock/same day shipment.
- Width is measured from inside seam to inside seam.
- Length is measured from the top edge to the bottom fold.
- Opening is in the "width" dimension.
- Custom bag sizes, custom printing, and custom hot stamping are available.
- Most sizes are packed 100 per case.
Small sizes are packed 1000 or 500 per case.

P R O D U C T D A T A S H E E T

SCC 1500 Static Shielding Bag METAL-OUT

PRODUCT
STATIC SHIELDING BAG, OPEN TOP AND ZIPTOP

ITEM NUMBER
150(W")(L")

DATASHEET
1101-B



STATIC CONTROL COMPONENTS, Inc.
ESD PRODUCTS DIVISION

US and Canada: **866-722-3736**
 Fax: 866-722-3735
 Intl: 919-774-3808
 Fax: 919-774-1287
 3010 Lee Avenue Sanford, NC 27330
 email: info@staticcontrol.com
 www.**StaticControl.com** ©