Rev	AWO #	Description	Date	Appr
-		RELEASED	5/12/06	

APPROVED: _____

DATE: _____ TITLE: _____









SPECIFICATIONS:
Material:
Insulator: LCP, glass reinforced, rated UL 94V-0
Insulator color: Natural
Contacts: Phosphor Bronze
Plating:
Tin over Copper underplate overall
Electrical:
Operating voltage: 250 VAC max
Current rating: 1 Amp max
Contact resistance: 30 mohms max
Insulation resistance: 1000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1500 VAC for 1 minute
Operating temperature: −40˚C to +100˚C
Environmental:
Lead free, RoHS compliant.
Recommended soldering temp: 260 for 5 sec.

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	SS	5/12/06
CHECKED		
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
SIMM Socket, Vertical Mount, Single Row, 30 Pos, Metal Latch , Thumb Lever

SIZE	PART NO.	REV.
X	**SIMM - 130 - VTL**	-

REF: | SCALE: NTS | SHEET 1 OF 1