

3M™ Vinyl Table Mat

Premium Vinyl Table Mat

A long time industry favorite, this three layer vinyl material provides excellent electrical properties. The top layer is tough, easy to clean, dissipative vinyl. The center layer, a highly conductive metal scrim, moves the charge from the surface to ground quickly. The bottom layer is a durable, non-skid, cushion of dissipative foam. Compatible with Constant Monitors. Available in rolls, mats, and mats with ground cord.

Standards

Meets the requirements of ESD Standard 4.1, ESD Standard 20.20, EIA 625, MILI-HDBK-263, and MIL-STD-1686.

Specifications

Resistance to Ground point (RTG) 10^7 ohms
 Resistance Top to Top (RTT) 10^7 ohms
 Thickness: 0.125 inches
 Colors: Blue and Gray

Part Numbers

Mats	Includes mat, two snaps, installed.	
SIZE	BLUE P/N	GRAY P/N
24x36 inches	TM2436L3BL	TM2436L3GR
24x48 inches	TM2448L3BL	TM2448L3GR



Call for custom sizes.

Mat Kits	Includes mat, two snaps, installed, and a 15 foot ground cord.	
SIZE	BLUE P/N	GRAY P/N
24x36 inches	TM2436L3BL-L	TM2436L3GR-L
24x48 inches	TM2448L3BL-L	TM2448L3GR-L

Call for custom sizes.

Rolls	Includes roll of matting material.	
SIZE	BLUE P/N	GRAY P/N
2x100 feet	TM241200L3BL	TM241200L3GR
3x100 feet	TM361200L3BL	TM361200L3GR
30"x100 feet	TM301200L3BL	TM301200L3GR
4x100 feet	TM481200L3BL	TM481200L3GR

See 3M Data Sheets for these related items:
 3M™ Ground Cords
 3M™ Snaps
 3M™ Snap Tool



R - T - G?

RTG is the resistance from one point on the mat's surface to the mat's ground point, and is the fundamental electrical test for a mat. A proper RTG insures that a mat can conduct charge from a point on the surface to the mat ground point. The guideline in ESD STM-4.1 for RTG is 1×10^6 to 1×10^9 ohms. ANSI/ESD S-20.20 has an upper limit of $< 1 \times 10^9$ ohms.

RTT is the resistance from one point on the mat's surface to another point. A proper RTT insures the consistency of the mat's resistance properties. The ESD STM-4.1 guideline for RTT is $> 1 \times 10^6$ ohms.

P R O D U C T D A T A S H E E T

Mat - Premium Vinyl- THREE LAYER

PRODUCT	ITEM NUMBER	DATASHEET
THREE LAYER VINYL MAT	SEE ABOVE	1133-A

3M Electronic Solutions Division
 6801 River Place Blvd.
 Austin, TX 78726-9000
 US and Canada: 866-722-3736
 Fax: 866-722-3735
 Intl: 919-718-0000; Fax: 919-774-8174
 email: 3Mstaticinfo@mmm.com; www.3M.com/static

3M is a trademark of 3M Company.
 All other trademarks herein are the property of their respective owners.



© 2008