

COUNTRY/LANGUAGE English

WHAT'S NEW

PRODUCTS

INDUSTRY SOLUTIONS

SUPPORT &amp; SERVICES


REGULATIONS/  
COMPLIANCEVISUAL WORKPLACE /  
LEAN

PRODUCT REGISTRATION

DISTRIBUTOR ONLY

Home &gt; Products By Category &gt; Labels &gt; General Labelling &amp; Equipment Identification &gt; Rating Plates &gt; Thermal Transfer Printable Labels

## Thermal Transfer Printable Labels



Brady's line of metallic, non metal labels exceed expectations in most industrial environments. Design to work with our easy-to-use software and our full line of Thermal Transfer Printers, these materials will allow you to create the sharp, professional rating plates and other labels you need.

These labels coupled with Brady's IP™ Thermal Transfer Printing System, are the only metallic product available for hassle-free printing. Supplied with our industrial-strength adhesive, as well as our Mondo Bondo™ adhesive, you can trust our labels in dirty, oily environments, and you can easily wipe clean the label front. Print on-demand labels, faster, easier and with more efficiency than other systems by using Brady's metallic, non-metal labels and IP Printer combination

[Overview](#)   [Specifications](#)

**Article Number:** 104192

**Order Reference:** THT-18-480-3

**Size - Width (mm):** 76.2

**Size - Height (mm):** 25.4

**Material Type:** Metallic, Non-Metal Polyester

**Brady Material Number:** [B-480](#)

**Approval/Compliance:** This material is CSA approved at UL with its respective ribbon

**Max. Service Temp. °C:** 145

**Special Properties:** Designed for powder coated surfaces, Ultra-aggressive adhesive

**Vertical Repeat (mm):** 28.58

**Web Width (mm):** 81.28

**QTY. per Row:** 1

**Printer Compatibility:** 300XPlusII, 360XPlusII, 600XPlusII, BP1244, BP1344, BP2461, BP3481, BP6441, IP300, IP600, MVP200, MVP300, PR200, PR300, PR600, Thermal Transfer Printers

**Industry:** Manufacturing

**Application(s):** General & Industrial Identification

**Format:** IP™ Enabled

[Contact Us](#)

[Quote Request](#)

[Print Page](#)

[Email This Page](#)

For further information on this product or for details of a local Brady Authorised Distributor, please use the "Contact Us" button

**For Distributors:** [dis only login](#) | [www.bradyserve.com](http://www.bradyserve.com)

**Additional Information:** [Privacy](#) | [Copyright](#) | [Site Map](#)

Copyright 2012 Brady Worldwide, Inc.