



Part Number	Pieces Per Package	Material	Color	Labels Per Row	Label Width Inch (mm) A	Label Height Inch (mm) B	Horizontal Repeat Inch (mm) C	Top Margin Inch (mm) D	Left Margin Inch (mm) E	Labels Per Sheet
0.800" Label Width										
LAT-4-410-10	10,000	Polyolefin	White	8	0.800 (20.32)	0.250 (6.35)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	304
LAT-4-652-10	10,000	Polyimide	Amber	8	0.800 (20.32)	0.250 (6.35)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	304
LAT-4-737-10	10,000	Tedlar	White	8	0.800 (20.32)	0.250 (6.35)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	304
LAT-4-747-10	10,000	Polyester	White	8	0.800 (20.32)	0.250 (6.35)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	304
LAT-4-747-10-YL	10,000	Polyester	Yellow	8	0.800 (20.32)	0.250 (6.35)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	304
LAT-5-652-10	10,000	Polyimide	Amber	8	0.800 (20.32)	0.500 (12.70)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	152
LAT-5-747-10	10,000	Polyester	White	8	0.800 (20.32)	0.500 (12.70)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	152
LAT-5-747-10-YL	10,000	Polyester	Yellow	8	0.800 (20.32)	0.500 (12.70)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	152
LAT-5-759-10	10,000	Paper	White	8	0.800 (20.32)	0.500 (12.70)	1.000 (25.40)	0.875 (22.23)	0.350 (8.89)	152
LAT-37-799-1,-2.5	1,000/2,500	Nylon Cloth	White	9	0.800 (20.32)	1.437 (36.50)	0.900 (22.86)	0.875 (22.23)	0.300 (7.62)	54
1.000" Label Width										
LAT-6-652-10	10,000	Polyimide	Amber	7	1.000 (25.40)	0.250 (6.35)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	266
LAT-6-747-10	10,000	Polyester	White	7	1.000 (25.40)	0.250 (6.35)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	266
LAT-6-747-10-YL	10,000	Polyester	Yellow	7	1.000 (25.40)	0.250 (6.35)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	266
LAT-8-409-10	10,000	Polyolefin	White	7	1.000 (25.40)	0.375 (9.53)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	175
LAT-8-652-10	10,000	Polyimide	Amber	7	1.000 (25.40)	0.375 (9.53)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	175
LAT-8-707-10	10,000	Polyester	White	7	1.000 (25.40)	0.375 (9.53)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	175
LAT-8-712-10	10,000	Polyester	Clear	7	1.000 (25.40)	0.375 (9.53)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	175
LAT-8-747-10	10,000	Polyester	White	7	1.000 (25.40)	0.375 (9.53)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	175
LAT-8-747-10-YL	10,000	Polyester	Yellow	7	1.000 (25.40)	0.375 (9.53)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	175
LAT-8-799-10	10,000	Nylon Cloth	White	7	1.000 (25.40)	0.375 (9.53)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	175
LAT-7-410-10	10,000	Polyolefin	White	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-7-652-10	10,000	Polyimide	Amber	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-7-707-10	10,000	Polyester	White	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-7-709-10	10,000	Removable Polyester	White	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-7-712-10	10,000	Polyester	Clear	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-7-722-10	10,000	Polyester	Clear	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-7-737-10	10,000	Tedlar®	White	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-7-737Y-10	10,000	Tedlar	Yellow	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-7-747-10	10,000	Polyester	White	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-7-747-10-YL	10,000	Polyester	Yellow	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-7-773-10	10,000	Metallized Polyester	Silver	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-7-799-10	10,000	Nylon Cloth	White	7	1.000 (25.40)	0.500 (12.70)	1.100 (27.94)	0.875 (22.23)	0.450 (11.43)	133
LAT-60-799-2.5	2,500	Nylon Cloth	White	15	1.000 (25.40)	1.000 (25.40)	0.500 (12.70)	0.875 (22.23)	0.550 (13.97)	285
LAT-39-799-1,-2.5	1,000/2,500	Nylon Cloth	White	7	1.000 (25.40)	1.437 (36.50)	1.100 (27.94)	0.875 (22.23)	0.300 (7.62)	42
1.250" Label Width										
LAT-30-737-10-WT	10,000	Tedlar	White	5	1.250 (31.75)	0.375 (9.53)	1.600 (40.64)	0.875 (22.23)	0.450 (11.43)	125
LAT-30-737-10-YL	10,000	Tedlar	Yellow	5	1.250 (31.75)	0.375 (9.53)	1.600 (40.64)	0.875 (22.23)	0.450 (11.43)	125
1.500" Label Width										
LAT-9-409-10	10,000	Polyolefin	White	5	1.500 (38.10)	0.250 (6.35)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	190
LAT-9-652-10	10,000	Polyimide	Amber	5	1.500 (38.10)	0.250 (6.35)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	190
LAT-9-709-10	10,000	Removable Polyester	White	5	1.500 (38.10)	0.250 (6.35)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	190
LAT-9-747-10	10,000	Polyester	White	5	1.500 (38.10)	0.250 (6.35)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	190
LAT-9-747-10-YL	10,000	Polyester	Yellow	5	1.500 (38.10)	0.250 (6.35)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	190
LAT-9-799-10	10,000	Nylon Cloth	White	5	1.500 (38.10)	0.250 (6.35)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	190
LAT-41-707-10	10,000	Polyester	White	5	1.500 (38.10)	0.375 (9.525)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	125
LAT-41-712-10	10,000	Polyester	Clear	5	1.500 (38.10)	0.375 (9.525)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	125
LAT-47-707-10	10,000	Polyester	White	5	1.500 (38.10)	0.500 (12.70)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	100
LAT-47-712-10	10,000	Polyester	Clear	5	1.500 (38.10)	0.500 (12.70)	1.600 (40.64)	0.875 (22.23)	0.300 (7.62)	100
LAT-20-773-2.5	2,500	Metallized Polyester	Silver	5	1.500 (38.10)	0.750 (19.05)	1.600 (40.64)	0.875 (22.23)	0.250 (6.35)	60

Tedlar® is a registered trademark of DuPont.

Note: Labels in chart are sorted in order by width, height, 3 digit material number (within part number), then die number (within part number).