

Wire Marker Cards




PART NUMBER EXPLANATION:


Most Brady part numbers in this section follow the same two-part format:

The first code indicates the Brady product being referenced, the second code indicates the marker legend.

Numbers




Higher Numbers



Mounted in groups of five identical groups per card.


| LEGEND | | B-500 Vinyl Cloth | B-702 Vinyl Film | B-605 Over-Laminated | B-184 Aluminum Foil | B-12 Acetate Cloth | Markers per Card | |
|--------|----------------|-------------------|------------------|----------------------|---------------------|--------------------|-------------------|-------------------|
| | | | | | | | 1.500" (38.10 mm) | 0.750" (19.05 mm) |
| | 0 | WM-0 | TWM-0 | OLWM-0 | AF-0 | HH-0 | 36 | 72 |
| | 1 | WM-1 | TWM-1 | OLWM-1 | AF-1 | HH-1 | 36 | 72 |
| | 2 | WM-2 | TWM-2 | OLWM-2 | AF-2 | HH-2 | 36 | 72 |
| | and so on thru | and so on thru | and so on thru | and so on thru | and so on thru | and so on thru | | |
| | 25 | WM-25 | TWM-25 | OLWM-25 | AF-25 | HH-25 | 36 | 72 |
| | 26 | WM-26 | TWM-26 | OLWM-26 | AF-26 | | 36 | 72 |
| | and so on thru | and so on thru | and so on thru | and so on thru | and so on thru | | 36 | 72 |
| | WM-99 | TWM-99 | OLWM-99 | AF-50 | | | 25 | 50 |
| | 601 - 605 | WM-601-605 | | | | | 25 | 50 |
| | 606 - 610 | WM-606-610 | | | | | 25 | 50 |
| | 611 - 615 | WM-611-615 | | | | | 25 | 50 |
| | and so on thru | and so on thru | | | | | | |
| | 921 - 925 | WM-921-925 | | | | | | |

Consecutive Numbers



| LEGEND | | B-500 Vinyl Cloth | B-702 Vinyl Film | B-605 Over-Laminated | B-184 Aluminum Foil | B-12 Acetate Cloth | Quantity Each Number Per Card | | Markers per Card | |
|--------|----------------|-------------------|------------------|----------------------|---------------------|--------------------|-------------------------------|-------------------|-------------------|-------------------|
| | | | | | | | 1.500" (38.10 mm) | 0.750" (19.05 mm) | 1.500" (38.10 mm) | 0.750" (19.05 mm) |
| | 1-33 | WM-1-33 | TWM-1-33 | OLWM-1-33 | AF-1-33 | HH-1-33 | 1 | 2 | 33 | 66 |
| | 34-66 | WM-34-66 | TWM-34-66 | OLWM-34-66 | AF-34-66 | HH-34-66 | 1 | 2 | 33 | 66 |
| | 67-99 | WM-67-99 | TWM-67-99 | OLWM-67-99 | AF-67-99 | HH-67-99 | 1 | 2 | 33 | 66 |
| | 100-124 | WM-100-124 | TWM-100-124 | OLWM-100-124 | AF-100-124 | | 1 | 2 | 25 | 50 |
| | 125-149 | WM-125-149 | TWM-125-149 | OLWM-125-149 | AF-125-149 | | 1 | 2 | 25 | 50 |
| | and so on thru | and so on thru | and so on thru | and so on thru | and so on thru | | | | | |
| | WM-1775-1799 | TWM-375-399 | OLWM-250-274 | AF-250-274 | | | 1 | 2 | 25 | 50 |

Consecutive Numbers Repeated



| LEGEND | | B-500 Vinyl Cloth | B-702 Vinyl Film | B-605 Over-Laminated | B-184 Aluminum Foil | Sequences per Card | | Markers per Card | |
|--------|-------|-------------------|------------------|----------------------|---------------------|--------------------|-------------------|-------------------|-------------------|
| | | | | | | 1.500" (38.10 mm) | 0.750" (19.05 mm) | 1.500" (38.10 mm) | 0.750" (19.05 mm) |
| | 1-3 | WM-1-3 | TWM-1-3 | | AF-1-3 | 12 | 24 | 36 | 72 |
| | 1-4 | WM-1-4 | | | AF-1-4 | 9 | 18 | 36 | 72 |
| | 1-5 | WM-1-5 | | | | 7 | 14 | 35 | 70 |
| | 1-6 | WM-1-6 | | | | 6 | 12 | 36 | 72 |
| | 1-8 | WM-1-8 | | | | 4 | 8 | 32 | 64 |
| | 1-9 | WM-1-9 | | | AF-1-9 | 4 | 8 | 36 | 72 |
| | 0-9 | WM-0-9 | TWM-0-9 | | | 3 | 6 | 30 | 60 |
| | 0-10 | WM-0-10 | | | | 3 | 6 | 33 | 66 |
| | 1-10 | WM-1-10 | TWM-1-10 | OLWM-1-10 | AF-1-10 | 3 | 6 | 30 | 60 |
| | 1-12 | WM-1-12 | TWM-1-12 | OLWM-1-12 | AF-1-12 | 3 | 6 | 36 | 72 |
| | 1-16 | WM-1-16 | TWM-1-16 | OLWM-1-16 | AF-1-16 | 2 | 4 | 32 | 64 |
| | 1-18 | WM-1-18 | TWM-1-18 | OLWM-1-18 | AF-1-18 | 2 | 4 | 36 | 64 |
| | 19-36 | WM-19-36 | TWM-19-36 | | | 2 | 4 | 36 | 72 |