

Fox Electronics Headquarters  
 5570 Enterprise Parkway  
 Fort Myers, FL 33905 USA  
 Tel: 888-GET-2-FOX  
 Outside US: +1.239.693.0099  
 Fax: +1.239.693.1554

Fox Electronics EMEA  
 9 Alderson Drive  
 Stretton  
 Burton upon Trent  
 Staffordshire  
 DE13 0QZ  
 Tel: +44 1283 568153

Fox Electronics Asia  
 21/F, Cheong Sun Tower  
 118 Wing Lok Street  
 Sheung Wan, Hong Kong  
 Tel: +852.2854.4285  
 Fax: +852.2854.4282

Fox Electronics Singapore  
 81 Kaki Bukit Ave 1 #04-38  
 Shun Li Industrial Park  
 417943  
 Tel: +65.6844798

Fox Electronics Japan  
 3-28-6-1A Yoyogi  
 Shibuya-ku, Tokyo 151  
 Japan  
 Tel: +81.3.3374.2079  
 Fax: +81.3.3377.5221

Quote Number	Rev	Create Date	Fox CSR/E-Mail	Reference	Expiration Date
200000		07/09/2007	LESLIE HUTTO Leslie.Hutto@foxonline.com		11/07/2010

**Quote To Customer (47)**
**FUTURE ELECTRONICS**

Contact: NICHOLAS TRISTRAM  
 E-Mail: nicholas.tristram@future.ca  
 Phone: 514- 694-7710 2697

**Sales Office**
**WEISS CO**

Contact:  
 E-Mail:  
 Phone:

**Payment Terms: NET 30 DAYS**
**All prices are in U.S. Dollars.**

Line	Del/Lead Time	Quantity	Unit Price
1			

**Quote Type: BUY**

Fox Part #: 793-12.288-10  
 Fox Description: FVXO-HC53BR-12.288

Cust Part#: 793-12.288-10

Product Family: FVXO-HC5  
 Frequency: 0012.288000  
 Technology: XpressO Voltage Controlled Oscillator  
 Logic: HCMOS  
 Package: Ceramic  
 Model: 5 x 3.2 mm  
 Voltage: 3.3V+-5%  
 Input Current 1: 32mA  
 Operating Temperature: -40 To +85 C  
 Storage Temperature: -55 To +125 C  
 Symmetry: 45-55%  
 Rise Time (0.1Vdd~0.9Vdd): 3nS Max  
 Fall Time (0.9Vdd~0.1Vdd): 3nS Max  
 Output Load: 15pF  
 Control Voltage: 0V~3.3V  
 Absolute Pull Range (APR): 50.0 ppm  
 Linearity: 10%  
 Modulation Bandwidth: 10kHz Min  
 Start-up Time: 10mS  
 Enable Time: 100nS  
 Disable Time: 100nS  
 Noise Optimization: D  
 LEAD-FREE: YES  
 RoHS Compliance Status: YES  
 Termination Finish: Category = (e4)  
 Termination Material: Au  
 Moisture Sensitivity Level: 1  
 Reflow Soldering: 260C 10 Seconds

1-50 1 to 2 Days,  
 51 to 2K 1 Week,  
 2K+ to 20K 2 to 3 Weeks  
 20K+ Will Advise

**EAU: 0**
**NCNR**
**XpressO®**

Covered by one or more of listed U.S. Patents:

5,960,405 5,952,890 6,188,290 6,664,860 B2

**Foreign Patents:**

R.S.A. 98/0866, ROC 120851, Singapore 67081; 67082, Philippines 1-1998-0245

EP 0958652, China ZL 98802217.6, Malaysia MY-118540-A,

Hong Kong HK1026079, Mexico 232179, India 212435,

US and Foreign Patents Pending

XpressO ® is a Registered Trademark of Fox Electronics

**\$100 minimum order for established customer accounts in good standing.**
**Visa, MasterCard and American Express accepted With 3 % Handling charges.**
**QUOTE NUMBER MUST BE REFERENCED ON PO WHEN PLACING ORDERS**