



Accessories

Primary adapters

The MPP/GPP line is available with country-specific mains plugs. The products are therefore universally applicable. Not only do the plugs enhance mobility and reliability of the corresponding product, they even facilitate the management of the country versions of power supplies and chargers.

In countries with other mains plug types, the IEC adapter with the 2-pin IEC 320 C8 socket provides a standardized alternative.

Secondary adapters


All standard units come with a round lead of 1.83 m length and our approved secondary adapter system. Depending on the required output voltage, the wire diameter is between 0.25 mm² (AWG30) and 1,31 mm² (AWG16). FRIWO also offers a broad range of secondary output plugs, including coaxial plugs (acc. to DIN 45323) and jack plugs (acc. to DIN 45318). Polarity is adjustable by reversing connector.

Customer-specific leads are also an option. If necessary, customer-specific flat or round leads can be fitted. Special versions as well as types and dimensions of low voltage plugs are available too.


Power cords

Power cords with 2 contact IEC 320 C7 mains plug provide a specific solution for each country. All power cords are 2 m of length and can be used with our IEC 320 CB socket for the MPP/GPP and DT lines.

Primary adapters GPP system



Primary adapters MPP system



Secondary adapters



Straight coaxial connectors				Angled coaxial connectors			
Ø out.	Ø in.	Length mm	Order No.	Ø out.	Ø in.	Length mm	Order No.
3.5	1.3	9.5	1807699	3.5	1.3	9.5	1822478
4.0	1.7	9.5	1822557	4.0	1.7	9.5	1822558
4.0	1.7	11.0	1811994	4.0	1.7	11.0	1822482
4.8	1.7	9.5	1822559	4.8	1.7	9.5	1822560
5.5	2.1	9.5	1807700	5.5	2.1	9.5	1822479
5.5	2.1	11.5	1807701	5.5	2.1	11.5	1822480
5.5	2.1	14.0	1807697	5.5	2.1	14.0	1822476
5.5	2.5	9.5	1807698	5.5	2.5	9.5	1822477
5.5	2.5	11.5	1807702	5.5	2.5	11.5	1822481
5.5	3.3	9.5	1822561	5.5	3.3	9.5	1822562
DIN 45323			1807703	DIN 45323			1822483

Power cords



Primary adapter	GPP
Country	Order No.
EURO	1827417
UK	1827420
USA/Japan	1827422
Australia	1827425
IEC	1827428
Korea	1835619
Argentina	1831610
India	1831323
China	1835620
Brazil	1835621
South Africa	1838236

Primary adapter	MPP
Country	Order No.
EURO	1717707
UK	1717618
USA/Japan	1717715
Australia MPP 15	1800496
Australia MPP 6/30	1804237
IEC	1809281
Korea	1832029
Brazil	1843164
China	1840406

Straight jack connectors			Connectors/sockets	
Ø out.	Length mm	Order No.	Description	Order No.
2.5	13	1807704	Texas connector	
3.5	14	1807705	Straight Texas connector	1807706
			Angled Texas connector	1822486
Angled jack connectors				
2.5	13	1822484	Texas sockets 2-pin	
3.5	14	1822485	Snap in type	1323938
			PCB type	1321609
			Texas sockets 3-pin	
			Snap in type	1327259
			PCB type	1363506

Power cords	
Country	Order No.
EURO	1812274
UK	1812275
USA/Japan	1812276
Australia	1812277
China	1843276