

BNC Adapters

PLATING SPECIFICATIONS

BODY: G - GOLD N - NICKEL S - SILVER

PIN/CONTACT: G - GOLD N - NICKEL S - SILVER T - TIN

DIELECTRIC: D - DELRIN PE - POLYETHYLENE T - TEFLON



FIG. 1
RFB-1130, -1



FIG. 2
RFB-1130-2



FIG. 3
RFB-1130-3



FIG. 4
RFB-1130-5




FIG. 5
RFB-1131



FIG. 6
RFB-1132



FIG. 7
RFB-1133



FIG. 8
RFB-1134



FIG. 9
RFB-1135, -, -T



FIG. 10
RFB-1136



FIG. 11
RFB-1137



FIG. 12
RFB-1138

BNC

PHOTOS FOR REFERENCE ONLY, SHOWN AT 100% ACTUAL SIZE.

PART #	FIG	DESCRIPTION	NOTES	REPLACES OR EQUIVALENT TO	PLATING		
					BDY	P/C	DIE
RFB-1130	1	T-ADAPTER	BNC MALE TO DOUBLE BNC FEMALE	UG-274B/U, C/U	N	G	T
RFB-1130-1	1	T-ADAPTER	BNC MALE TO DOUBLE BNC FEMALE, DIECAST	UG-274B/U, C/U	N	G	D
RFB-1130-2	2	T-ADAPTER	BNC MALE TO DOUBLE BNC FEMALE, MOLDED PLASTIC JACKET	FOR LAN USE	N	G	D
RFB-1130-3	3	F-ADAPTER	BNC MALE TO DOUBLE BNC FEMALE	FOR LAN USE	N	G	D
RFB-1130-5	4	GOALPOST ADAPTER	BNC MALE TO DOUBLE BNC FEMALE	FOR LAN USE	N	G	D
RFB-1131	5	T-ADAPTER	TRIPLE BNC FEMALE		N	S	T
RFB-1132	6	RIGHT ANGLE ADAPTER	BNC MALE TO BNC FEMALE	UG-306/U, A/U, B/U	N	S	T
RFB-1133	7	BARREL ADAPTER	BNC MALE TO BNC MALE	MS39012/3992-15-00491 UG-491/U, A/U, B/U	N	G	T
RFB-1134	8	BARREL ADAPTER	BNC FEMALE TO BNC FEMALE	UG-914/U	N	G	P
RFB-1135	9	FEMALE BULKHEAD ADAPTER	DOUBLE BNC FEMALE WITH D-FLAT & O-RING	UG-492/U	N	G	D
RFB-1135-I	9	FEMALE BULKHEAD ADAPTER	DOUBLE BNC FEMALE WITH D-FLAT, INSULATED		S	G	D
RFB-1135-T	9	FEMALE BULKHEAD ADAPTER	DOUBLE BNC FEMALE WITH D-FLAT & O-RING	UG-492/U, D/U	N	G	T
RFB-1136	10	ADAPTER	BNC MALE TO UHF FEMALE	UG-255A/U	N	G	D
RFB-1137	11	ADAPTER	BNC FEMALE TO UHF MALE	UG-273/U	N	S	D
RFB-1138	12	ADAPTER	BNC FEM TO BNC MALE, CONNECTOR SAVER		N	G	D

BNC ADAPTERS — continued

BNC



FIG. 13
RFB-1139



FIG. 14
RFB-1140



FIG. 15
RFB-1141



FIG. 16
RFB-1142, -4, -5, -6



FIG. 17
RFB-1144



FIG. 18
RFB-1145,



FIG. 19
RFB-1151



FIG. 20
RFB-1152



FIG. 21
RFB-1153



FIG. 22
RFB-1155



FIG. 23
RFE-6101



FIG. 24
RFE-6102



FIG. 25
RFE-6103



FIG. 26
RFE-6150



FIG. 27
RFE-6151



FIG. 28
RFF-1479

PHOTOS FOR REFERENCE ONLY, SHOWN AT 100% ACTUAL SIZE.

PART #	FIG	DESCRIPTION	NOTES	REPLACES OR EQUIVALENT TO	PLATING		
					BDY	P/C	DIE
RFB-1139	13	ADAPTER	BNC MALE TO RCA PHONO JACK		N	G	D
RFB-1140	14	ADAPTER	BNC FEMALE TO RCA PHONO PLUG		N	S	D
RFB-1141	15	ADAPTER	BNC FEMALE TO PHONO PLUG (MOTOROLA) FOR GP 300, P110 & P120	HLN9756A	N	G	T
RFB-1142	16	ADAPTER	BNC FEMALE TO SMA FEMALE	UNIDEN / JOHNSON SMR	N	G	T
RFB-1142-4	16	ADAPTER	BNC FEMALE TO SMA (MOTOROLA) FEMALE	USE WITH MOTOROLA CELLULAR	N	G	T
RFB-1142-5	16	ADAPTER	BNC FEMALE TO SMA FEMALE (OKI 900)	USE WITH OKI 900 CELLULAR	N	G	T
RFB-1142-6	16	ADAPTER	BNC FEMALE TO SMA (MOTOROLA) FEMALE Q/D*	*1.5 TURNS	N	G	T
RFB-1144	17	ADAPTER	BNC FEMALE TO F MALE		N	G	D
RFB-1145	18	ADAPTER	BNC FEMALE TO 1/4 X 24 STUD	FOR KENWOOD PORTABLES TK240 & TK340	N	S	T
RFB-1151	19	BULKHEAD ADAPTER	BNC FEMALE TO RCA PHONO JACK WITH D-FLAT		N	G	D
RFB-1152	20	BULKHEAD ADAPTER	BNC FEMALE TO RCA MALE QUICK DISCONNECT		N	N	T
RFB-1153	21	BULKHEAD ADAPTER	BNC FEMALE TO F MALE QUICK DISCONNECT		N	N	T
RFB-1155	22	ADAPTER	BNC MALE TO F FEMALE		N	G	D
RFE-6101	23	ADAPTER	FME MALE TO BNC FEMALE		N	G	T
RFE-6102	24	ADAPTER	FME MALE TO BNC MALE		N	G	T
RFE-6103	25	RIGHT ANGLE ADAPTER	FME MALE TO BNC MALE		N	G	T
RFE-6150	26	ADAPTER	FME FEMALE TO BNC FEMALE		N	G	T
RFE-6151	27	ADAPTER	FME FEMALE TO BNC MALE		N	G	T
RFF-1479	28	ADAPTER	F MALE TO BNC FEMALE		N	T	PE



FIG. 29
RFN-1023-5



FIG. 30
RFN-1037-1



FIG. 31
RFN-1038-1



FIG. 32
RFN-1039-1



FIG. 33
RFN-1040-1



FIG. 34
RFT-1230



FIG. 35
RFT-1231



FIG. 36
RFT-1232



FIG. 37
RFU-545



FIG. 38
RFU-622



FIG. 39
RFU-627



FIG. 40
RSA-3413



FIG. 41
RSA-3413-3



FIG. 42
RSA-3458



FIG. 43
RSA-3459



FIG. 44
RSA-3476, -1

PHOTOS FOR REFERENCE ONLY, SHOWN AT 100% ACTUAL SIZE.

PART #	FIG	DESCRIPTION	NOTES	REPLACES OR EQUIVALENT TO	PLATING		
					BDY	P/C	DIE
RFN-1023-5	29	BULKHEAD ADAPTER	N FEMALE TO BNC FEMALE		N	G	T
RFN-1037-1	30	ADAPTER	N MALE TO BNC FEMALE	UG-201A/U	S	G	T
RFN-1038-1	31	ADAPTER	N FEMALE TO BNC MALE	UG-349B/U	S	G	T
RFN-1039-1	32	ADAPTER	N FEMALE TO BNC FEMALE		S	G	T
RFN-1040-1	33	ADAPTER	N MALE TO BNC MALE	UG-1034/U	S	G	T
RFT-1230	34	ADAPTER	TNC FEMALE TO BNC MALE		N	G	T
RFT-1231	35	ADAPTER	TNC MALE TO BNC FEMALE		N	G	T
RFT-1232	36	ADAPTER	TNC FEMALE TO BNC FEMALE		N	G	T
RFU-545	37	ADAPTER	UHF FEMALE TO BNC FEMALE		N	S	D
RFU-622	38	ADAPTER	MINI UHF MALE TO BNC FEMALE	MOTOROLA 5880367B23 (58C83488R01)	N	G	T
RFU-627	39	ADAPTER	MINI UHF FEMALE TO BNC MALE	MOTOROLA 5880367B28	N	G	T
RSA-3413	40	BULKHEAD ADAPTER	SMA FEMALE TO BNC FEMALE		N	G	T
RSA-3413-3	41	BULKHEAD ADAPTER	SMA FEMALE TO BNC FEMALE, W/ .375-32 UNEF THREADS		N	G	T
RSA-3458	42	ADAPTER	SMA MALE TO BNC FEMALE		N	G	T
RSA-3459	43	ADAPTER	SMA MALE TO BNC MALE		N	G	T
RSA-3476	44	ADAPTER	SMA FEMALE TO BNC MALE		N	G	T
RSA-3476-1	44	ADAPTER	SMA FEMALE TO BNC MALE		G	G	T