

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION .2001.
 © COPYRIGHT 2001 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
J	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		REVISED (FJ00-1882-01)	24AUG'01	C.J	H.M

AS SHOWN: -1(本図)

MOUNTING SURFACE

9.5 ϕ P.C.B

0.8

4.6

34.5 MAX

60.3

13.35 \pm 0.3

2.05 \pm 0.1

9.8

16.74

76.5 MIN

77 MIN

85.6 (PC CARD)

78

73.42

70.84

58.1

4

4

4

4

20

4

74.04

75.7

79.2

80.7

86.1

95.6

11.5

BUTTON STROKE

29.1

29.9

31.4

60.4

0.5

29.6

34.9

35.95 MAX

33.9 MAX

5.7

1.65 \pm 0.15

13.35 \pm 0.3

13.85

15.1 \pm 0.4

57.6

76

66.5

54.6 (Ins. sheet)

19.5

17.5

2.1

3.95

13.4

3.9 (Ins. sheet)

60.1 (Ins. sheet)

60.6

1.9 \pm 0.3

1.6 \pm 0.3

1.2 \pm 0.3

78

14

17.5

5

5

1.5

2.55

7.85

50

2.5

54.6 (Ins. sheet)

56.5 (Ins. sheet)

*2.3

*3.6

29.3

30.6

83.6 (BACKET)

83.1 (FRONT SURFACE OF SHUTTER)

82.1 (AXIS OF SHUTTER)

76.5 MIN

77 MIN

85.6 (PC CARD)

78

73.42

70.84

58.1

4

4

4

4

20

4

74.04

75.7

79.2

80.7

86.1

95.6

11.5

BUTTON STROKE

29.1

29.9

31.4

60.4

0.5

29.6

34.9

35.95 MAX

33.9 MAX

5.7

1.65 \pm 0.15

13.35 \pm 0.3

13.85

15.1 \pm 0.4

57.6

76

66.5

54.6 (Ins. sheet)

19.5

17.5

2.1

3.95

13.4

3.9 (Ins. sheet)

60.1 (Ins. sheet)

60.6

1.9 \pm 0.3

1.6 \pm 0.3

1.2 \pm 0.3

78

14

17.5

5

5

1.5

2.55

7.85

50

2.5

54.6 (Ins. sheet)

56.5 (Ins. sheet)

*2.3

*3.6

29.3

30.6

55.4 (SHUTTER WIDTH)

0.6

SHUTTER COLOR: SILVER GRAY

SECT A-A (SCALE 2:1)

BUTTON COLOR: SILVER GRAY

TABLE 1

POST LENGTH	5	3.5	4.25
回路番号 CIRCUIT NO.	1, 17, 34, 35, 51, 68	36, 67	その他 OTHERS

1	INSULATOR SHEET	⑥
2	SPRING PIN	⑤
4	NUT (M2)	④
1	SHUTTER SUB ASSEMBLY	③
1	EJECTOR SUB ASSEMBLY	②
1	HEADER MAIN ASSEMBLY	①
数量 QTY	名称 NAME	ITEM

注記

△ 本寸長は、表1を参照のこと。

2 推奨ネジ締め付けトルク: 0.15N・m(1.5kg・cm)から0.2N・m(2kg・cm)

3 適用PCカード: PCMCIA準拠のPCカード

4 推奨取り付け寸法: X-Y並目寸 M2 P=0.4, L=12mm

NOTE

△ REFER TO TABLE 1 FOR POST CONTACT LENGTH.

2 RECOMMENDED TIGHTENING TORQUE: FROM 0.15N・m(1.5kg・cm) TO 0.2N・m(2kg・cm)

3 APPLIED CARD: PCMCIA ATTRIBUTE PC CARD.

4 RECOMMENDED MACHINE SCREW: METRIC COARSE SCREW TREAD M2 P=0.4, L=12mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	K.YAMAGUCHI	2APR'01
CHK	S.WATANABE	9APR'01
APVD	H.MURAMATSU	10APR'01

NAME: CARD BUS CONNECTOR DOUBLE SLOT TOP MOUNT PUSH-PUSH TYPE

PRODUCT SPEC: 108-5590

APPLICATION SPEC: -

WEIGHT: 35gr

SIZE: A3 CAGE CODE: 00779 DRAWING NO: C-1473670

CUSTOMER DRAWING

SCALE: 1:1 SHEET: 1 OF 2 REV: A

AMP 1470-19 REV 31MAR2000 08AUG2001 11:22am FJ033475 S:\AMP-KawasakiEC\CC_CE\EN22_CadData\AutoCAD\fj033475 S-WATANABE\AR-1\C-1473670.dwg

