


Fortimo LED decorative modules

Fortimo deco mini strip 300 40D 827 10V



Fortimo LED Decorative module – Enhance your creativity. Featuring the newest energy-efficient LED technology, Fortimo LED Decorative modules offer high quality light with excellent color rendering and a long lifetime. Their small footprint and different shapes give luminaire makers maximum freedom of design. Fortimo LED Decorative modules are ideal for sleek designs of wall-mounted luminaires, pendant lighting, floor-standing luminaires and desk lamps for home applications requiring high-quality light, the ‘design’ factor and the perfect ambiance.

Product data

• General Characteristics

Number of LEDs	3 x
Ingress Protection	IP 20 [Ingress Protection 20]
Housing color	Transparent
Life to 70% lumen maintenance	20000 hr

• Light Technical Characteristics

Color Code	827
Color Designation (text)	Warm White
Beam Angle	120 D
Correlated Color Temperature	2700 K
Luminous Flux	250 (min), 300 (nom) Lm
Color rendering index	85
Color consistency initial	4

• Electrical Characteristics

Dimming range	100-25 %
Dimmable	Yes
Power module	6.5 W
Module input voltage	10 V

• Temperature Characteristics

T-case maximum	65 (max) C
T-case lifetime	65 (max) C

• Product Dimensions

Length A1	82.5 mm
-----------	---------

Fixing Hole Distance A2	75.5 mm
Length A3	68.5 mm
Width B1	12 mm
Height C1	10.2 mm
Height C2	4.7 mm
Fixing Hole Diameter D1	3.2 mm
Length Cable X1	300 mm

• Approval & Application Chars

VDE marking	No
VDE-EMC marking	No
CB compliance	Yes
CE marking	Yes
ENEC certificate	No
CCC certificate	No
UL certificate	No
CSA certificate	No
TISI marking	No
RCM compliance	No
RoHS compliance	Yes

• Product Data

Order code	929000663408
Full product code	929000663408
Full product name	Fortimo deco mini strip 300 40D 827 10V
Order product name	Fortimo deco mini strip 300 40D 827 10V
Pieces per pack	1
Packing configuration	50
Packs per outerbox	50
Bar code on pack - EAN1	8718291158431

PHILIPS


sense and simplicity

Fortimo LED decorative modules

Bar code on
outerbox - EAN3 8718291158448
Logistic code(s) -
12NC 929000663408

Net weight per piece 15.900 gr

Dimensional drawing



Fortimo deco mini strip 300 40D 827 10V

Product	A1 (Norm)	A2 (Norm)	A3 (Norm)	B1 (Norm)	C1 (Norm)	C2 (Norm)	D1 (Norm)	X1 (Norm)
Fortimo deco mini strip 300 40D 827 10V	82.5	75.5	68.5	12	10.2	4.7	3.2	300



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, December 1
data subject to change