

3M™ Anti-Fatigue Mats

Anti-fatigue Floor Mat

This 3/8 inch thick foamed vinyl mat provides relief and comfort for personnel that must stand or walk for long periods. Embossing improves traction. Suppresses voltage on personnel as they approach a work area.

Standards

Meets the requirements of EIA 625, MILI-HDBK-263, and MIL-STD-1686.

Specifications

Resistance to Ground point (RTG) 10⁹⁻¹⁰ ohms
 Resistance Top to Top (RTT) 10⁹⁻¹⁰ ohms
 Thickness: 0.375 inches
 Color: Gray or Brown

Part Numbers

Mats	Includes mat, two snaps, installed.	
SIZE	GRAY P/N	BROWN P/N
24x36 inches	AFM2436L1VGR	AFM2436L1VBR
36x60 inches	AFM3660L1VGR	AFM3660L1VBR

Call for custom sizes.



Mat Kits	Includes mat, two snaps, installed, and a 15 foot ground cord.	
SIZE	GRAY P/N	BROWN P/N
24x36 inches	AFM2436L1VGR-F	AFM2436L1VBR-F
36x60 inches	AFM3660L1VGR-F	AFM3660L1VBR-F

Call for custom sizes.

Rolls	Includes roll of matting material.	
SIZE	GRAY P/N	BROWN P/N
3x60 feet	AFM36720L1VGR	AFM36720L1VBR

See 3M Data Sheets for these related items:

- 3M™ Ground Cords
- 3M™ Snaps
- 3M™ Snap Tool



R - T - G?

RTG is the resistance from one point on the mat's surface to the mat's ground point, and is the fundamental electrical test for a mat. A proper RTG insures that a mat can conduct charge from a point on the surface to the mat ground point. The guideline in ESD STM-4.1 for RTG is 1x10⁶ to 1x10⁹ ohms. ANSI/ESD S-20.20 has an upper limit of <1 x10⁹ ohms.

RTT is the resistance from one point on the mat's surface to another point. A proper RTT insures the consistency of the mat's resistance properties. The ESD STM-4.1 guideline for RTT is >1x10⁶ ohms.

P R O D U C T D A T A S H E E T

Mat - Anti-Fatigue - FLOOR MAT

PRODUCT
ANTI-FATIGUE FLOOR MAT

ITEM NUMBER
SEE ABOVE

DATASHEET
1137-B

3M Electronic Solutions Division
 6801 River Place Blvd.
 Austin, TX 78726-9000
 US and Canada: **866-722-3736**
 Fax: 866-722-3735
 Intl: 919-718-0000; Fax: 919-774-8174
 email: 3Mstaticinfo@mmm.com; www.3M.com/static

3M is a trademark of 3M Company.
 All other trademarks herein are the property
 of their respective owners.



© 2008