



ROHS COMPLIANT
 PER AAVID SPEC: ROHS-9000

THIS DOCUMENT CONTAINS AAVID THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE AND WHICH MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED AND MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS

REVISIONS			
REV	DESCRIPTION	APPROVE	DATE
B	ECR#C060745: Add ROHS	<i>Leader</i>	Aug/12/06



- NOTES:
- ⚠ IN ORDER TO ACHIEVE FIN UNIFORMITY, VARIATION FORM MINIMUM FIN DIMENSION TO MAXIMUM FIN DIMENSION MUST BE 0.41(0.016) OR LESS
 - ⚠ PLUS OR MINUS TOLERANCE DOES NOT APPLY TO LAST ROW OF FINS, THIS IS INTENDED TO ALLOW FOR MANUFACTURING VARIANCES, BUT THAT ROW MUST MEET NOTE NUMBER ONE REQUIREMENTS.
 - ⚠ CUT OFF, BOTH ENDS, TO BE $\pm 1/2^\circ$ ANGULARITY IN RELATION TO EXTRUDED LENGTH.
 - 4. DIMENSIONS/TOLERANCES UNLESS SPECIFICALLY INDICATED OTHERWISE ARE TO BE CONSIDERED AT THE EXTRUDED BASE.
 - 5. COLOR: BLACK
 - 6. *DENOTES CRITICAL CHARACTERISTIC FOR LOT INSPECTION
- *表示重点尺寸和特征



FINISH: 黑色阳极

FINISH	Black anodize
REVISED	B
MATERIAL	AL6063-T5
TOLERANCE UNLESS NOTED	
.XX ± 0.25 ANGULAR $\pm 3^\circ$	

Item	Part Description	Part Number	Q'ty
AAVID CHINA INC.			
Heat Sink (Old P/N: 034268/1790-1)			
Customer P/N:		N/A	
Part Number		304429	
APPROVE	CHK'D	DRAW	DATE
<i>Leader</i>	TOMMY	JACKLI	Aug/12/06
UNITS	SCALE		
mm	1:1		