




# 61155

	Part Number	Thermal Resistance °C/W at 3in length	Width in	Height in	Surface Area in/in	Weight lb/ft
	61155	0.94	12.25	1.00	74.5	6.80




## Natural Convection

Heat Sink Temperature Rise Above Ambient





Power Dissipated (W)

Heat Sink Thermal Resistance



Power Dissipated (W)

## Forced Convection



## Building a Part Number

Full Bar Length = 8.20ft

Base Part #	Bar Length	Finish	Length (use zeros for full or half bars)
5 digit base part #	<u>1</u> Full (normally 8-ft)	<u>F</u> Unfinished	0 0 0 0 0
	<u>2</u> Half (small cut fee)	<u>F</u> Unfinished	0 0 0 0 0
	<u>3</u> Custom (cut to specified length)	<u>B</u> Black Anodized <u>C</u> Gold Chromate <u>U</u> Unfinished* <u>V</u> AavSHIELD <sup>3</sup>	<i>indicate length in inches to three decimal places;</i> If the part is less than 10 inches, the first of these 5 digits (digit 7 of the 12 digit series) would be a zero (0).

