





Back to search results

62200

<b>This part is in stock!</b>		
<b>Inventory Snapshot:</b>	237 feet*	
*Material in stock maybe allocated to other orders and is subject to prior sales		
<b>OEM Pricing*</b>		
<b>8 feet:</b> \$93.75 per foot	<b>16 feet:</b> \$46.88 per foot	<b>32 feet:</b> \$23.44 per foot
*For larger quantities, please contact our sales department		

	Part Number	Thermal Resistance °C/W at 3in length*	Width in	Height in	Surface Area in <sup>2</sup> /in	Weight lb/ft	Part Class
	62200	2.80	3.50	0.85	25.0	1.40	A

\*Based on a 75°C rise in natural convection





Thermal Curves  
based on 3.000 in length

New Length 3.000  in  mm


Change Length

**Natural Convection**




## Forced Convection

**Heat Sink Temperature Rise Above Ambient (10W Dissipated)**



**Heat Sink Thermal Resistance**



## Building a Part Number

Full Bar Length = 8.00ft

Base Part #	Bar Length	Finish	Length (use zeros for full or half bars)	RoHS	
5 digit base part #	<u>1</u> Full (normally 8-ft)	<u>E</u> Unfinished	0 0 0 0 0	Compliant NO "G" required	
	<u>2</u> Half (small cut fee)	<u>E</u> Unfinished	0 0 0 0 0		
	<u>3</u> Custom (cut to specified length)	<u>B</u> Black Anodized	<u>U</u> Unfinished* <u>V</u> AavSHIELD <sup>3</sup>	length in inches to three decimal places**	Compliant Add "G"
		<u>C</u> Gold Chromate			

62200      3      U      06500      G

\*For unfinished extrusions with cut lengths other than half bar, the finish designation is a U.

\*\*If the part is less than 10 inches, the first of these 5 digits (digit 7 of the 13 digit series) would be a zero (0).

### Examples:

If you wanted to simply order extrusion # 62200 in standard bar form, the part number would be: 622001F00000. The unit price would be sold by the foot.

If you wanted extrusion 62200 cut to a length of 6.500" and black anodized, the part number would be: 622003B06500G. The unit price would be by the piece.

If you wanted extrusion 62200 cut to a length of 14.725" and a wash finish, the part number would be: 622003U14725G. The unit price would be by the piece.

If you wanted extrusion 62200 cut to a length of 14.725" and Gold Chromate finish, the part number would be: 622003C14725. The unit price would be by the piece.

Standard Aavid Thermalloy parts require all 12-13 positions to be complete.

## Non-Standard Extrusions

Aavid Thermalloy has over 10,000 extrusion profile designs on file, most with the extrusion die already available. These parts have minimum order requirements and longer lead times, but may be cost effective compared to a new design.

## Customizing & Advanced Capabilities

We offer several options for those applications which require a more unique solution. Challenge us with your thermal requirements - we can design custom solutions.

©2012 Aavid Thermalloy, LLC