

Data Sheet

Momentum® 5400.6

Durable mobility anywhere, anytime

**500, 320, 250, 160 and 120 GB • 5400 RPM •
SATA 3Gb/s with NCQ • G-Force Protection™**

Key Advantages

- 8-MB cache delivers fast performance.
- Robust design and high shock tolerance enable mobility in rugged operating environments.
- 1000 Gs of nonoperating shock make the drive ideal for notebook PCs and industrial applications.
- G-Force Protection™ feature available for added robustness in mobile environments
- Green features:
 - Leverages Seagate laptop power management technology
 - Utilizes ramp load features that remove the head from the disk during idle periods, improving idle power consumption and adding to the durability of the drive
- QuietStep™ technology enables ultra-quiet load/unload acoustics
- SATA 3Gb/s interface with Native Command Queuing
- Perpendicular recording technology
- High instantaneous (burst) data transfer rates up to 3 Gb/s



Best-Fit Applications

- Mainstream laptops
- External storage solutions/boxes
- Whitebooks
- Industrial applications requiring a small form factor

Momentum® 5400.6

Durable mobility anywhere, anytime



With fourth-generation perpendicular magnetic recording technology and capacities up to 500 GB, the Seagate® Momentum® 5400.6 drive offers the best combination of performance, capacity, mobility and durability in a laptop hard drive. The Momentum 5400.6 drive offers a fast SATA 3Gb/s interface plus an 8-MB cache, making the drive ideal for mainstream laptops, workstations, gaming laptops and personal external storage.

G-Force Protection

When a laptop is dropped, the most catastrophic damage to the hard drive occurs when the head scrapes across the surface of the disk, causing potential data loss. The G-Force Protection feature, an optional drop sensor, protects the Momentum 5400.6 drive against shock by sensing when the system is in a free-fall state, moving the heads off the platter and locking them in place—all within three-tenths of a second.

Seagate Global Customer Support

- Get presales and technical support at support.seagate.com.
- Visit our knowledge base for answers to common support questions.
- Find documentation for current and legacy drives
- Utilize our online troubleshooting and diagnostic tools.
- Download DiscWizard™ help transfer data from an older drive.
- Seagate also offers multi-lingual phone, email and chat support.
- Seagate Design Service Centers help companies transform innovative ideas into viable products.

Specifications	500 GB ¹	320 GB ¹	250 GB ¹	160 GB ¹	120 GB ¹
Model Number	ST9500325AS ST9500325ASG ²	ST9320325AS ST9320325ASG ²	ST9250315AS ST9250315ASG ²	ST9160314AS ST9160314ASG ²	ST9120315AS
Interface Options	SATA 3Gb/s NCQ	SATA 3Gb/s NCQ	SATA 3Gb/s NCQ	SATA 3Gb/s NCQ	SATA 3Gb/s NCQ
Performance					
Transfer Rate					
Maximum Internal (Mb/s)	1175	1175	1175	1175	1175
Maximum External (MB/s)	300	300	300	300	300
Cache (MB)	8	8	8	8	8
Average Latency (ms)	5.6	5.6	5.6	5.6	5.6
Spindle Speed (RPM)	5400	5400	5400	5400	5400
Areal Density (Gb/in²)	394	394	394	394	394
Configuration/Organization					
Disks/Heads	2/4	2/3	1/2	1/2	1/1
Bytes per Sector	512	512	512	512	512
Reliability/Data Integrity					
G-Force Protection™	Available	Available	Available	Available	—
Head-Rest Method	QuietStep™ Ramp Load	QuietStep™ Ramp Load	QuietStep™ Ramp Load	QuietStep™ Ramp Load	QuietStep™ Ramp Load
Load/Unload Cycles	>600,000	>600,000	>600,000	>600,000	>600,000
Nonrecoverable Read Errors per Bits Read	1 per 10E14	1 per 10E14	1 per 10E14	1 per 10E14	1 per 10E14
Annualized Failure Rate (AFR)	0.48%	0.48%	0.48%	0.48%	0.48%
Power Management					
Startup Current 5V (amps max)	1.0	1.0	1.0	1.0	1.0
Power Management (W)					
Seek	1.54	1.54	1.54	1.54	1.54
Read/Write Avg	2.6/2.85	2.6/2.85	2.6/2.85	2.6/2.85	2.6/2.85
Idle/Standby Avg	0.81/0.22	0.81/0.22	0.81/0.22	0.81/0.22	0.81/0.22
Environmental					
Temperature (°C)					
Operating	0 to 60	0 to 60	0 to 60	0 to 60	0 to 60
Nonoperating	-40 to 70	-40 to 70	-40 to 70	-40 to 70	-40 to 70
Shock (Gs)					
Operating: 2 ms	350	350	350	350	350
Nonoperating: 1 ms	1000	1000	1000	1000	1000
Acoustics (bels—sound power)					
Idle	2.4	2.4	2.4	2.4	2.4
Seek	2.6	2.6	2.6	2.6	2.6
Physical					
Height (in/mm)	0.374/9.5	0.374/9.5	0.374/9.5	0.374/9.5	0.374/9.5
Width (in/mm)	2.75/69.85	2.75/69.85	2.75/69.85	2.75/69.85	2.75/69.85
Depth (in/mm)	3.957/100.5	3.957/100.5	3.957/100.5	3.957/100.5	3.957/100.5
Weight (lb/kg)	0.218/98.8	0.218/98.8	0.206/93.5	0.206/93.5	0.206/93.5

¹ One gigabyte, or GB, equals one billion bytes when referring to hard drive capacity.
² Drive with G-Force Protection™ feature

www.seagate.com
1-800-SEAGATE (1-800-732-4283)

AMERICAS Seagate Technology LLC 920 Disc Drive, Scotts Valley, California 95066, United States, 831-438-6550
 ASIA/PACIFIC Seagate Technology International Ltd. 7000 Ang Mo Kio Avenue 5, Singapore 569877, 65-6485-3888
 EUROPE, MIDDLE EAST AND AFRICA Seagate Technology SAS 130-136, rue de Silly, 92773, Boulogne-Billancourt Cedex, France 33 1-4186 10 00

Copyright © 2009 Seagate Technology LLC. All rights reserved. Printed in USA. Seagate, Seagate Technology and the Wave logo are registered trademarks of Seagate Technology LLC in the United States and/or other countries. DiscWizard, G-Force Protection, Momentum and QuietStep are either trademarks or registered trademarks of Seagate Technology LLC or one of its affiliated companies in the United States and/or other countries. All other trademarks or registered trademarks are the property of their respective owners. When referring to hard drive capacity, one gigabyte, or GB, equals one billion bytes and one terabyte, or TB, equals one trillion bytes. Your computer's operating system may use a different standard of measurement and report a lower capacity. In addition, some of the listed capacity is used for formatting and other functions, and thus will not be available for data storage. Seagate reserves the right to change, without notice, product offerings or specifications. DS1663.2-0903US, March 2008