





Part Number: 622001F00000

	Part Number	Thermal Resistance °C/W at 3in length	Width in	Height in	Surface Area in/in	Weight lb/ft
	62200	2.80	3.50	0.85	25.0	1.40




Thermal Curves

based on 3.000 in length


Natural Convection

Heat Sink Temperature Rise Above Ambient



Power Dissipated (W)


Heat Sink Thermal Resistance




Power Dissipated (W)

Forced Convection

Heat Sink Temperature Rise
Above Ambient (10W Dissipated)
Air Flow (m/s)



Heat Sink
Thermal Resistance
Air Flow (m/s)



Building a Part Number

Full Bar Length = 8.00ft

Base Part #	Bar Length	Finish	Length (use zeros for full or half bars)
62200	<u>1</u> Full	<u>E</u> Unfinished	0 0 0 0
	<u>2</u> Half	<u>E</u> Unfinished	0 0 0 0
	<u>3</u> Custom	<u>B</u> Black Anodized <u>C</u> Gold Chromate <u>U</u> Unfinished <u>V</u> AavSHIELD ³	<i>indicate length in inches to three decimal places;</i> 1 5 2 5 0 = 15.250 "

62200 — — — — — — —