





Rev	AWO #	Description	Date	Appr
-		RELEASED	7/31/09	

APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



RECOMMENDED PCB LAYOUT



Positions: 02 thru 20

A = .098 [2.50] x No. of Spaces  
 B = .098 [2.50] x No. of Spaces + .197 [5.00]

SPECIFICATIONS:

- Material: Nylon66, rated UL 94V-2
- Insulator color: Beige
- Contacts: Brass
- Plating: Tin over copper underplate overall.
- Electrical: Tin over copper underplate overall.
- Voltage Rating: 250V AC
- Current Rating: 3 Amps Max
- Dielectric Withstanding Voltage: 1000V AC for 1 minute.
- Insulation Resistance: 1000 Megohms Min
- Contact Resistance: 20 Milliohms Max
- Temperature Range: -40°C to 105°C
- Environmental: Lead free, RoHS compliant
- Recommended soldering temp: 235°C for 5 seconds

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .098 [2.50] PITCH WAFER, RIGHT ANGLE  
 PCB TYPE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]		TOLERANCES: EXCEPT AS NOTED	
INCHES		HOLE SIZES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XXX	± .015
.XXX	± .015	Ø.XXX	± .010
APPROVALS		DATE	
DRAWN	DY	7/31/09	
CHECKED			
APPROVED			
SIZE	PART NO.	SCALE	REV.
X	25SH-E-XX-TR	NTS	-
REF:	S00004T	SHEET	1 OF 1

