# AZ2900 \_\_\_\_

### **25 AMP POWER RELAY**

#### FEATURES

- Panel mount
- Universal mounting bracket with break-away tabs
- 25 Amp switching
- Quick-connect terminals
- UL, CUR file E44211

### CONTACTS

Arrangement	SPST (1 Form A) SPST (1 Form B) SPST (1 Form A and 1 Form B) SPDT (1 Form C)		
Ratings	Resistive load:		
	Max. switched power: 6925 VA Max. switched current: 25 A Max. switched voltage: 277 VAC		
UL, CUR	1 Form A 12 FLA, 60 LRA at 125 VAC, 30k cycles 8 FLA, 48 LRA at 250 VAC, 30k cycles 7 FLA, 42 LRA at 277 VAC, 30k cycles 25 A at 277 VAC, resistive, 50k cycles		
	1 Form C 14 FLA, 84 LRA at 125 VAC, 30k cycles 8 FLA, 48 LRA at 250 VAC, 30k cycles 7 FLA, 42 LRA at 277 VAC, 30k cycles 25 A at 277 VAC, resistive, 50k cycles		
	1 Form A & B 12 FLA, 60 LRA at 120 VAC, 30k cycles 8 FLA, 48 LRA at 250 VAC, 30k cycles 7 FLA, 42 LRA at 277 VAC, 30k cycles 18 A at 277 VAC, resistive, 100k cycles		
Material	Silver cadmium oxide		
Resistance	< 200 milliohms initially (24 V, 1 A voltage drop method)		

#### **GENERAL DATA**

Life Expectancy Mechanical Electrical	Minimum operations 1 x $10^6$ 1 x $10^5$ at 25 A 277 VAC Res.			
Operate Time (typical)	25 ms at nominal coil voltage			
Release Time (typical)	25 ms at nominal coil voltage			
Dielectric Strength (at sea level for 1 min.)	2500 Vrms coil to contact 1000 Vrms between open contacts			
Insulation Resistance	500 megohms min. at 500 VDC, 20°C 50% RH			
Dropout	Greater than 20% of nominal coil voltage			
Ambient Temperature Operating Storage	At nominal coil voltage -20°C (-4°F) to 40°C (104°F) -20°C (-4°F) to 105°C (221°F)			
Vibration	0.062" DA at 10–55 Hz			
Shock Operating	10 g, 11 ms <sup>1</sup> / <sub>2</sub> sine (no false operation)			
Enclosure	Phenolic			
Terminals	Quick-connect			
Weight	85 grams			

#### COIL

Power			
At Nominal Voltage (typical)	4.0 VA		
Temperature Rise	60°C (108°F) at nominal coil voltage		
Temperature	Max. 105°C (221°F)		

### NOTES

- 1. All values at 20°C (68°F).
- 2. Relay may pull in with less than "Must Operate" value.
- 3. Specifications subject to change without notice.



IERICAN ZETTLER, INC.

www.azettler.com


# AZ2900

### **RELAY ORDERING DATA**

	ORDER NUMBER*				
Nominal Coil VAC	Must Operate VAC	Max. Continuous VAC	Coil Resistance ±10%	Coil Current A	1 Form C**
24	20.4	31.2	77	0.167	AZ2900–1C–24A
120	102	132	2000	0.033	AZ2900–1C–120A
240	204	264	6000	0.017	AZ2900–1C–240A
277	235	305	7250	0.014	AZ2900–1C–277A

\*For 1 Form A, 1 Form B, or 1 Form A & B, substitute "-1A", "-1B" or "-1AB" in place of "-1C". Note: 1 Form B version not UL approved. For permanant plastic mounting tabs on 2.15" (hole diameter .150") centers add suffix "P" or for 2.62" centers (hole diameter .189") add "P1". \*\*There is no terminal "6" on 1 Form C relays.

#### **MECHANICAL DATA**



Dimensions in inches with metric equivalents in parentheses. Tolerance: ± .010"



 AMERICAN ZETTLER, INC.
 www.azettler.com

 75 COLUMBIA · ALISO VIEJO, CA 92656 · PHONE: (949) 831-5000 · FAX: (949) 831-8642 · E-MAIL: SALES @ AZETTLER.COM