



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/9/04	
A		UPDATED	12/04/07	



SPECIFICATIONS:

Material:
 Contact: Phosphor Bronze, 0.2mm thick
 Plating: Tin over Copper underplate

Electrical:
 Operating voltage: 250 VAC RMS max
 Current rating: 20 Awg: 5 Amps max
 22 Awg: 5 Amps max
 24 Awg: 4 Amps max
 26 Awg: 3 Amps max
 28 Awg: 2 Amps max
 30 Awg: 1 Amp max.

Mechanical:
 Contact resistance: 10 mohms max.
 Dielectric withstanding voltage: 1500 VAC for 1 minute
 Temperature rise: 30°C max.

Environmental:
 Wire size: 22 Awg thru 28 Awg
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED	
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010
APPROVALS	DATE
DRAWN	SS
CHECKED	
APPROVED	

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .118" [3.0mm] CRIMP, MULTI ROW HOUSINGS, TIN PLATED

SIZE	PART NO.	REV.
X	DMT-C-F-T-1	A
REF:	SCALE: NTS	SHEET 1 OF 1