



REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	12/08/08	L.CHAN




- MATERIALS:**  
 PLASTIC HOUSING: ENGINEERING THERMOPLASTIC  
 FLAMMABILITY RATING UL 94V-0  
 COLOR: PANTONE GREEN 362C  
 CONTACTS: PHOSPHOR BRONZE  
 PLATING: REFER TO PART NUMBER FOR GOLD THICKNESS ON MATING SURFACES.  
 50 μ" [1.27 MICRONS]  
 MIN. NICKEL UNDERPLATE  
 100 μ" [2.54 MICRONS]  
 MIN. MATTE TIN ON CONTACT TAILS.



- MECHANICAL:**  
 MATING FORCE: 6.0 LBS MAX.
- ELECTRICAL:**  
 CONTACT RESISTANCE: 40 MILLIOHMS MAXIMUM  
 INSULATION RESISTANCE: 500 MEGOHMS MINIMUM  
 CURRENT RATING: 1.5 AMPS  
 VOLTAGE RATING: 150 VOLTS AC
- ENVIRONMENTAL:**  
 STORAGE TEMPERATURE: -20°C to 85°C  
 PACKAGING METHOD: TRAY PACKAGING
- UL FILE NUMBER:** E136228

RECOMMENDED P.C.B. LAYOUT  
(COMPONENT SIDE OF BOARD)



RECOMMENDED PANEL CUTOUT

AMPHENOL PART NUMBER: RJE03-188-0X90

1 = 06 μ" GOLD  
 2 = 15 μ" GOLD  
 3 = 30 μ" GOLD  
 4 = 50 μ" GOLD

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

MATERIAL	DRAWN HUILAN	DATE 12/08/08	Amphenol Canada Corp.		
	DESIGNED				
FINISH	CHECKED MT CHEN	12/08/08	TITLE MODULAR JACK, 8 POSITION, 8 CONTACTS, WITHOUT SHIELD, GREEN COLOR (NO SIDE FLANGES, NO KEY) - RoHS COMPLIANT		
	I. E. APPRD.				
	Q. A. APPRD.		DWG	DRAWING NO.	REV.
	DWG. APPRD.		C	P-RJE03-188-0X90	A
	ENG. REL. NO.		DIMENSIONS ARE IN	CODE ID. NO.	
	REF. EAR 13431		INCHES [mm]	03554	
			SCALE 4/1	WT. -----	SURF. -----
					SHEET 1 OF 1