




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		Released	12/18/2003	
A		Redrawn	10/26/07	SS
B		REVISED DIM.	12/31/08	



SPECIFICATIONS:
 Material: Insulator: Thermoplastic, rated UL94V-0
 Insulator color: Green
 Metal cage: Phosphor Bronze, Nickel plated
 Screw: Steel, Zinc plated
 Electrical:
 Operating voltage: 250 VAC max.
 Current rating: 12 Amps max.
 Insulation resistance: 500 Mohms min.
 Dielectric withstanding voltage: 2,000 VAC for 1 minute
 Mechanical:
 Wire range: 12 to 16 AWG Stranded
 Temperature Rating:
 Operating temperature: -55°C to +105°C
 Environmental:
 Lead free, RoHS compliant.

ROHS COMPLIANT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM]	
TOLERANCES EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	ØXX ± .10
.XX ± .020	ØXXX ± .015
.XXX ± .015	ØXXXX ± .010
APPROVALS	DATE
DRAWN TD	12/18/2003
CHECKED	
APPROVED	

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE	TERMINAL BLOCK, 0.5mm, 02-24 POLE
SIZE	PART NO.
X	TSF-XX
REF: S00036T	SCALE: NTS
	SHEET 1 OF 1
	REV. B