

**ADDA USA  
DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow	Pressure (mmAg)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
15 X 15 X 6	AD1505MX-K90	HYPRO	5	0.08	0.36	17000	0.15	1.83	23	3	0,6	CE		
20 X 20 X 6	AD2005MX-K70	HYPRO	5	0.1	0.5	14000	1.12	4.54	27.1	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2005MB-K70	BALL	5	0.1	0.5	14000	1.12	4.54	27.1	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2005LX-K70	HYPRO	5	0.08	0.4	10500	1.04	3.9	17	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2005LB-K70	BALL	5	0.05	0.25	10500	1.04	3.9	17	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2005DX-K70	HYPRO	5	0.05	0.25	7000	1.01	3.59	10.1	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2012MB-K70	BALL	12	0.06	0.72	14000	1.12	4.54	27.1	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2012MX-K70	HYPRO	12	0.06	0.72	14000	1.12	4.54	27.1	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2012LB-K70	BALL	12	0.06	0.72	10500	1.04	3.9	17	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2012LX-K70	HYPRO	12	0.05	0.6	10500	1.04	3.9	17	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 10	AD2005MX-G70	HYPRO	5	0.09	0.45	11500	0.62	2.46	20	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2005MB-G70	BALL	5	0.07	0.35	11500	0.62	2.46	20	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2005LX-G70	HYPRO	5	0.08	0.4	9000	0.44	1.5	14.8	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2005LB-G70	BALL	5	0.06	0.3	9000	0.44	1.5	14.8	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2012MX-G70	HYPRO	12	0.05	0.61	11500	0.62	2.46	20	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2012MB-G70	BALL	12	0.05	0.6	11500	0.62	2.46	20	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2012LX-G70	HYPRO	12	0.06	0.72	9000	0.44	1.5	14.8	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2012LB-G70	BALL	12	0.06	0.7	9000	0.44	1.5	14.8	5	0,6	UL,CUL,TUV,CE	900	17.6
25 X 25 X 6	AD0205MX-K50	HYPRO	5	0.11	0.55	12000	2.62	5.87	27.5	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0205MB-K50	BALL	5	0.08	0.4	12000	2.62	5.87	27.5	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0205LX-K50	HYPRO	5	0.08	0.4	9000	1.92	3.13	17.6	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0205LB-K50	BALL	5	0.05	0.25	9000	1.92	3.13	17.6	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0212MX-K50	HYPRO	12	0.07	0.84	12000	2.62	5.87	27.5	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0212MB-K50	BALL	12	0.07	0.84	12000	2.62	5.87	27.5	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0212LX-K50	HYPRO	12	0.06	0.72	9000	1.92	3.13	17.6	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0212LB-K50	BALL	12	0.05	0.6	9000	1.92	3.13	17.6	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 10	AD2005HX-G50	HYPRO	5	0.08	0.65	12000	2.56	6.73	29	6	0,6	UL,CUL,TUV,CE	600	15
25 X 25 X 10	AD2005MX-G50	HYPRO	5	0.06	0.42	10000	2.14	4.93	26.9	6	0,6	UL,CUL,TUV,CE	600	15
25 X 25 X 10	AD2005LX-G50	HYPRO	5	0.05	0.25	8000	1.69	3.23	24.1	6	0,6	UL,CUL,TUV,CE	600	15
25 X 25 X 10	AD2012HX-G50	HYPRO	12	0.09	1.02	12000	2.56	6.73	29	6	0,6	UL,CUL,TUV,CE	600	15
25 X 25 X 10	AD2012MX-G50	HYPRO	12	0.06	0.68	10000	2.14	4.93	26.9	6	0,6	UL,CUL,TUV,CE	600	15
25 X 25 X 10	AD2012LX-G50	HYPRO	12	0.04	0.5	8000	1.69	3.23	24.1	6	0,6	UL,CUL,TUV,CE	600	15
30 X 30 X 6	AD0305MX-K70	HYPRO	5	0.11	0.55	9000	3.44	3.75	24.8	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0305MB-K70	BALL	5	0.08	0.4	9000	3.44	3.75	24.8	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0305LX-K70	HYPRO	5	0.09	0.45	7500	2.81	2.76	18.5	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0305LB-K70	BALL	5	0.07	0.35	7500	2.81	2.76	18.5	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0312MX-K70	HYPRO	12	0.06	0.72	9000	3.44	3.75	24.8	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0312MB-K70	BALL	12	0.06	0.72	9000	3.44	3.75	24.8	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0312LX-K70	HYPRO	12	0.05	0.65	7500	2.81	2.76	18.5	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0312LB-K70	BALL	12	0.05	0.65	7500	2.81	2.76	18.5	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 10	AD0305MX-G50	HYPRO	5	0.12	0.6	9000	4.52	4.51	28.2	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0305MB-G50	BALL	5	0.12	0.6	9000	4.52	4.51	28.2	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0305LX-G50	HYPRO	5	0.09	0.45	8000	4	3.81	23.8	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0305LB-G50	BALL	5	0.09	0.45	8000	4	3.81	23.8	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0305DX-G50	HYPRO	5	0.05	0.25	5500	2.46	1.97	14.6	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0305DB-G50	BALL	5	0.05	0.25	5500	2.46	1.97	14.6	8	0,6	UL,CUL,TUV,CE	400	14

B= Ball H= Hypro S= Sleeve

**ADDA USA CORP. ALL RIGHTS RESERVED**

All specifications subject to change without notice.

**ADDA USA  
DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow	Pressure (mmAg)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
30 X 30 X 10	AD0312MX-G50	HYPRO	12	0.09	1.08	9000	4.52	4.51	28.2	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0312MB-G50	BALL	12	0.09	1.08	9000	4.52	4.51	28.2	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0312LX-G50	HYPRO	12	0.07	0.84	8000	4	3.81	23.8	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0312LB-G50	BALL	12	0.07	0.84	8000	4	3.81	23.8	8	0,6	UL,CUL,TUV,CE	400	14
35 X 35 X 6	AD3505MX-K70	HYPRO	5	0.11	0.55	8000	5.37	3.5	25.9	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3505MB-K70	BALL	5	0.09	0.45	8000	5.37	3.5	25.9	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3505LX-K70	HYPRO	5	0.1	0.5	6500	4.3	2.45	19.7	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3505LB-K70	BALL	5	0.08	0.4	6500	4.3	2.45	19.7	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3512MX-K70	HYPRO	12	0.08	0.96	8000	5.37	3.5	25.9	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3512MB-K70	BALL	12	0.08	0.96	8000	5.37	3.5	25.9	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3512LX-K70	HYPRO	12	0.06	0.72	6500	4.3	2.45	19.7	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3512LB-K70	BALL	12	0.06	0.72	6500	4.3	2.45	19.7	7	0	UL,CUL,TUV,CE	400	13
40 X 40 X 6	AD0405HX-K90	HYPRO	5	0.12	0.6	6200	6.39	2.55	25.8	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0405HB-K90	BALL	5	0.12	0.6	6800	6.71	2.75	27.3	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0405MX-K90	HYPRO	5	0.09	0.45	5500	5.39	1.87	22.2	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0405MB-K90	BALL	5	0.09	0.45	5800	5.59	2.06	23.4	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0405LX-K90	HYPRO	5	0.07	0.35	4500	4.26	1.29	16.6	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0405LB-K90	BALL	5	0.07	0.35	4800	4.69	1.46	18.3	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412HX-K90	HYPRO	12	0.08	0.96	6200	6.39	2.55	25.8	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412HB-K90	BALL	12	0.08	0.96	6800	6.71	2.75	27.3	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412MX-K90	HYPRO	12	0.07	0.84	5500	5.39	1.87	22.2	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412MB-K90	BALL	12	0.07	0.84	5800	5.59	2.06	23.4	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412LX-K90	HYPRO	12	0.06	0.72	4500	4.26	1.29	16.6	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412LB-K90	BALL	12	0.06	0.72	4800	4.69	1.46	18.3	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 10	AD0405HX-G70	HYPRO	5	0.19	0.95	6000	7.11	3.89	27.5	14	0,6	UL,CUL,TUV,CE	560	32.12
40 X 40 X 10	AD0405MX-G70	HYPRO	5	0.11	0.55	4200	4.9	1.91	15.9	14	0,6	UL,CUL,TUV,CE	560	32.12
40 X 40 X 10	AD0412HX-G70	HYPRO	12	0.1	1.2	6000	7.11	3.89	27.5	14	0,6	UL,CUL,TUV,CE	560	32.12
40 X 40 X 10	AD0412MX-G70	HYPRO	12	0.08	1.08	4200	4.9	1.91	15.9	14	0,6	UL,CUL,TUV,CE	560	32.12
40 X 40 X 10	AD0412LX-G70	HYPRO	12	0.08	0.96	3300	3.43	0.36	14	14	0,6	UL,CUL,TUV,CE	560	32.12
40 X 40 X 15	AD0412HB-D50	BALL	12	0.09	0.99	8000	9.2	7.3	39.3	24	0,6	CE	500	44
40 X 40 X 15	AD0412MB-D50	BALL	12	0.08	0.88	7000	7.5	5.36	31.8	24	0,6	CE	500	44
40 X 40 X 15	AD0412LB-D50	BALL	12	0.07	0.84	6000	6.8	4.03	27.5	24	0,6	CE	500	44
40 X 40 X 20	AD0412HX-C50	H or S	12	0.11	1.32	7500	10	7.83	31.1	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HB-C50	BALL	12	0.1	1.2	7800	10.5	8.69	31.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MX-C50	H or S	12	0.08	0.96	6700	9	6.71	27.6	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MB-C50	BALL	12	0.08	0.96	6900	9.2	6.79	28.3	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412LX-C50	H or S	12	0.07	0.84	6000	7.9	5.14	24.2	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412LB-C50	BALL	12	0.07	0.84	6200	8.2	5.49	25.2	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HX-C50	H or S	24	0.09	2.16	7500	10	7.83	31.1	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HB-C50	BALL	24	0.09	2.16	7800	10.5	8.69	31.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MX-C50	H or S	24	0.07	1.68	6700	9	6.71	27.6	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MB-C50	BALL	24	0.07	1.68	6900	9.2	6.79	28.3	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LX-C50	H or S	24	0.06	1.44	6000	7.9	5.14	24.2	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LB-C50	BALL	24	0.06	1.44	6200	8.2	5.49	25.2	28	0,6	UL,CUL,TUV,CE	500	36.96
45 X 45 X 6	AD4505HX-K90	HYPRO	5	0.13	0.67	6300	9.09	2.78	27.6	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4505HB-K90	BALL	5	0.16	0.79	6600	9.5	3.02	29.2	10	0,6	Pending	560	19.3

B= Ball H= Hypro S= Sleeve

**ADDA USA CORP. ALL RIGHTS RESERVED**

All specifications subject to change without notice.

**ADDA USA  
DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow	Pressure (mmAg)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
45 X 45 X 6	AD4505MX-K90	HYPRO	5	0.09	0.44	5300	7.57	2.22	23.2	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4505MB-K90	BALL	5	0.1	0.5	5600	8.09	2.39	24.4	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4505LX-K90	HYPRO	5	0.06	0.28	4300	6.15	1.5	17.7	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4505LB-K90	BALL	5	0.06	0.31	4600	6.61	1.72	19.1	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512HX-K90	HYPRO	12	0.07	0.83	6300	9.09	2.78	27.6	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512HB-K90	BALL	12	0.07	0.8	6600	9.5	3.02	29.2	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512MX-K90	HYPRO	12	0.06	0.68	5300	7.57	2.22	23.2	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512MB-K90	BALL	12	0.05	0.64	5600	8.09	2.39	24.4	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512LX-K90	HYPRO	12	0.04	0.51	4300	6.15	1.5	17.7	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512LB-K90	BALL	12	0.04	0.5	4600	6.61	1.72	19.1	10	0,6	Pending	560	19.3
45 X 45 X 10	AD4505HX-G70	HYPRO	5	0.2	1	5000	8.95	3.08	26.8	16	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MX-G70	BALL	5	0.16	0.8	4200	7.25	2.56	20.2	16	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512HX-G70	HYPRO	12	0.09	1.08	5000	8.95	3.08	26.8	16	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MX-G70	BALL	12	0.07	0.84	4200	7.25	2.56	20.2	16	0,6	UL,CUL,TUV,CE	500	24.64
50 X 50 X 8	AD0505LX-J90	HYPRO	5							29		CE	480	31.9
50 X 50 X 8	AD0505MB-J90(S)	1B & 1S	5	0.1	0.5	5200	7.2	0.86	26.5	29		CE	480	31.9
50 X 50 X 10	AD0512MX-G70	HYPRO	12	0.07	0.84	4600	11.03	2.92	25.2	17	0,6	UL,CUL,TUV,CE	560	32.12
50 X 50 X 10	AD0512MB-G70	BALL	12	0.07	0.84	4600	11.03	2.92	25.2	17	0,6	UL,CUL,TUV,CE	560	32.12
50 X 50 X 10	AD0512LX-G70	HYPRO	12	0.06	0.72	3900	9.35	2.09	19.9	17	0,6	UL,CUL,TUV,CE	560	32.12
50 X 50 X 10	AD0512LB-G70	BALL	12	0.06	0.72	3900	9.35	2.09	19.9	17	0,6	UL,CUL,TUV,CE	560	32.12
52 X 52 X 15	AD0505HX-D70	HYPRO	5	0.26	1.3	4600	12	4.22	28.7	37	0,1,2,3,6	CUL,UL,CE	480	46.2
52 X 52 X 15	AD0505MX-D70	HYPRO	5	0.16	0.8	3700	9.7	2.69	22.6	37	0,1,2,3,6	CUL,UL,CE	480	46.2
52 X 52 X 15	AD0512HX-D70	HYPRO	12	0.1	1.2	4600	12	4.22	28.7	37	0,1,2,3,6	CUL,UL,CE	480	46.2
52 X 52 X 15	AD0512MX-D70	HYPRO	12	0.09	1.08	3700	9.7	2.69	22.6	37	0,1,2,3,6	CUL,UL,CE	480	46.2
60 X 60 X 10	AD0605HX-G90	H,S,or X	5	0.28	1.4	4200	16.6	2.88	32.8	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 10	AD0605MX-G90	H,S,or X	5	0.23	1.15	3600	14.1	2.16	28.5	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 10	AD0605LX-G90	H,S,or X	5	0.15	0.75	3000	11.9	1.49	23.1	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 10	AD0612HX-G90	H,S,or X	12	0.14	1.68	4200	16.6	2.88	32.8	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 10	AD0612MX-G90	H,S,or X	12	0.12	1.44	3600	14.1	2.16	28.5	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 10	AD0612LX-G90	H,S,or X	12	0.11	1.32	3000	11.9	1.49	23.1	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 15	AD0605HX-D71GL	H,S,or X	5	0.37	1.85	4500	16.6	3.86	32.4	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 15	AD0605MX-D71GL	H,S,or X	5	0.25	1.25	3900	14.2	3	28.8	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 15	AD0605LX-D71GL	H,S,or X	5	0.2	1	3500	13.5	2.3	27.6	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 15	AD0612HX-D71GL	H,S,or X	12	0.13	1.56	4500	16.6	3.86	32.4	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 15	AD0612MX-D71GL	H,S,or X	12	0.11	1.32	3900	14.2	3	28.8	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 15	AD0612LX-D71GL	H,S,or X	12	0.06	0.72	3500	13.5	2.3	27.6	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 20	AD0605HX-C70GL	H,S,or X	5	0.3	1.5	4500	16.4	3.53	29.7	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 20	AD0605MX-C70GL	H,S,or X	5	0.24	1.2	3900	14.5	2.82	25.7	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 20	AD0612HX-C70GL	H,S,or X	12	0.16	1.92	4500	16.4	3.53	29.7	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 20	AD0612HX-C70GL	H,S,or X	12	0.13	1.56	3900	14.5	2.82	25.7	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 20	AD0612MX-C70GL	H,S,or X	12	0.08	0.96	3500	13.3	2.44	21.6	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 20	AD0624HX-C70GL	H,S,or X	24	0.09	2.16	4500	16.4	3.53	29.7	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 25	AD0605MX-A70GL	H,S,or X	5	0.32	1.6	3500	18	3	24	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44
60 X 60 X 25	AD0605LX-A70GL	H,S,or X	5	0.22	1.1	2500	13.2	16	16.1	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44
60 X 60 X 25	AD0612UX-A70GL	H or S	12	0.25	3	5300	28.3	6.35	37	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44
60 X 60 X 25	AD0612UB-A70GL	BALL	12	0.22	2.64	5300	28.3	6.35	37	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44

B= Ball H= Hypro S= Sleeve

**ADDA USA CORP. ALL RIGHTS RESERVED**

All specifications subject to change without notice.

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow	Pressure (mmAg)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
60 X 60 X 25	AD0612HX-A70GL	H,S,or X	12	0.23	2.76	4500	23.2	4.78	32.3	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44
60 X 60 X 25	AD0612MX-A70GL	H,S,or X	12	0.14	1.68	3500	18	3	24	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44
60 X 60 X 25	AD0612LX-A70GL	H,S,or X	12	0.08	0.96	2500	13.2	1.6	16.1	58	0,1,2,3,4,6,7,9	CE	300	44
80 X 80 X 15	AD0805HX-D71	H,S,or X	5	0.43	2.15	3200	29.9	3.28	31.4	65	0,1,3,4,6,7,9,	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0805MX-D71	H,S,or X	5	0.24	1.2	2440	22.4	2.11	26	65	0,1,3,4,6,7,9,	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HX-D71	H,S,or X	12	0.19	2.28	3200	29.9	3.28	31.4	65	0,1,3,4,6,7,9,	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MX-D71	H,S,or X	12	0.15	1.8	2440	22.4	2.11	26	65	0,1,3,4,6,7,9,	UL,CUL,TUV,CE	200	32.34
80 X 80 X 20	AD0805HX-C70	H,S,or X	5	0.4	5.16	3010	27.3	3.25	31.4	66	0,1,2,3	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 20	AD0812HX-C70	H,S,or X	12	0.24	2.88	3010	27.3	3.25	31.4	66	0,1,2,3	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 20	AD0812MX-C70	H,S,or X	12	0.16	1.92	2440	22.1	2.21	25.4	66	0,1,2,3	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 20	AD0824HX-C70	H,S,or X	24	0.15	3.6	3010	27.3	3.25	31.4	66	0,1,2,3	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 20	AD0824MX-C70	H,S,or X	24	0.13	3.12	2440	22.1	2.21	25.4	66	0,1,2,3	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812UX-A71GL	H,S,or X	12	0.45	5.4	3900	50	6.81	40.6	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812HX-A70GL	H,S,or X	12	0.25	3	3010	38.6	4.06	34	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812MX-A70GL	H,S,or X	12	0.15	1.8	2440	31.4	2.9	28.3	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812LX-A70GL	H,S,or X	12	0.12	1.44	2030	26.2	1.98	22.5	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812DX-A70GL	H,S,or X	12	0.08	0.96	1600	20.5	1.27	15	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0824UX-A71GL	H,S,or X	24	0.26	6.24	3900	50	7.09	41	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812HX-A70GL	H,S,or X	24	0.16	3.84	3010	38.6	4.06	34.4	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0824MX-A70GL	H,S,or X	24	0.1	2.4	2440	31.4	2.9	28.3	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0824LX-A70GL	H,S,or X	24	0.09	2.16	2030	26.2	1.98	22.5	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
92 X 92 X 20	AD0912HX-C70	H,S,or X	12	0.25	3	2740	32.8	2.69	32.8	78	0,1,2,3	UL,CUL,TUV,CSA,CE	200	41.3
92 X 92 X 20	AD0912MX-C70	H,S,or X	12	0.16	1.92	2430	29	2.11	28.9	78	0,1,2,3	UL,CUL,TUV,CSA,CE	200	41.3
92 X 92 X 20	AD0924HX-C70	H,S,or X	24	0.14	3.36	2740	32.8	2.69	32.8	78	0,1,2,3	UL,CUL,TUV,CSA,CE	200	41.3
92 X 92 X 20	AD0924MX-C70	H,S,or X	24	0.1	2.4	2430	29	2.11	28.9	78	0,1,2,3	UL,CUL,TUV,CSA,CE	200	41.3
92 X 92 X 25	AD0912UX-A71GL	H or S	12	0.39	4.68	3200	57.8	3.96	38.6	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912UB-A71GL	BALL	12	0.39	4.68	3200	60	4.15	39.4	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912HX-A70GL	H or S	12	0.25	3	2700	50	2.93	33.7	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912HB-A70GL	BALL	12	0.25	3	2900	52.5	3.32	35	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912MX-A70GL	H or S	12	0.17	2.04	2400	43.5	2.34	31.3	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912MB-A70GL	BALL	12	0.17	2.04	2600	47.2	2.69	32.7	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912LX-A70GL	H or S	12	0.12	1.44	2100	37.9	1.87	26.5	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912LB-A70GL	BALL	12	0.12	1.44	2300	41.6	2.18	29.8	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924UX-A71GL	H or S	24	0.21	5.04	3200	57.8	3.96	38.6	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924UB-A71GL	BALL	24	0.21	5.04	3300	60	4.15	39.4	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924HX-A70GL	H or S	24	0.15	3.6	2700	50	2.93	33.7	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924HB-A70GL	BALL	24	0.15	3.6	2900	52.5	3.32	35	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924MX-A70GL	H or S	24	0.12	2.88	2400	43.5	2.34	31.3	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924MB-A70GL	BALL	24	0.12	2.88	2600	47.2	2.69	32.7	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924LX-A70GL	H or S	24	0.08	1.92	2100	37.9	1.87	26.5	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924LB-A70GL	BALL	24	0.08	1.92	2300	41.6	2.18	29.8	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
120 X 120 X 25	AD1212UX-A71GL	H,S,or X	12	0.5	6	2500	98.6	4.48	43.3	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1212HX-A71GL	H or S	12	0.44	5.28	2200	85.2	3.45	39.1	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1212HB-A71GL	BALL	12	0.37	4.44	2200	85.2	3.45	39.1	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1212MX-A71GL	H or S	12	0.34	4.08	2050	80.5	2.97	38	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1212MB-A71GL	BALL	12	0.33	3.96	2050	80.5	2.97	38	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8

B= Ball H= Hypro S= Sleeve

**ADDA USA CORP. ALL RIGHTS RESERVED**

All specifications subject to change without notice.

**ADDA USA  
DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow	Pressure (mmAq)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
120 X 120 X 25	AD1212LX-A71GL	H,S,or X	12	0.24	2.88	1800	72	2.41	34.4	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1224HX-A71GL	H or S	24	0.24	5.76	2200	85.2	3.45	39.1	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1224HB-A71GL	BALL	24	0.19	4.56	2200	85.2	3.45	39.1	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1224MX-A71GL	H or S	24	0.2	4.8	2050	80.5	2.97	38	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1224MB-A71GL	BALL	24	0.17	4.08	2050	80.5	2.97	38	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1224LX-A71GL	H,S,or X	24	0.14	3.36	1800	72	2.41	34.4	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 38	AD1212HB-F51	H,S,or X	12	0.5	6	2800	104.8	6.86	42.8	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212MX-F51	H,S,or X	12	0.35	4.2	2540	94	6.2	41	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212LX-F51	H,S,or X	12	0.24	2.88	1950	72.3	3.43	32.9	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224UB-F51	H,S,or X	24	0.35	8.4	3200	125.1	9.5	48.1	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224HB-F51	BALL	24	0.34	8.16	2800	104.8	6.86	42.8	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224HX-F51	H or S	24	0.32	7.68	2800	104.8	6.86	42.8	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248HX-F51	H,S,or X	48	0.2	9.6	2800	104.8	6.86	42.8	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248MB-F51	H,S,or X	48	0.14	6.72	2540	94	6.2	41	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248LB-F51	H,S,or X	48	0.1	4.8	1950	72.3	3.43	32.9	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66

<http://www.addausa.com/>

HOME