



A

$$2.54 \times (\text{No. of Contacts}/2) + 7.5 \pm 0.30$$





A

B

B

C

C





D

D

E

E



Current Rating: 3 Amps  
 Insulator Resistance: 5000 Megohms min  
 Dielectric Withstanding: AC 1000V  
 Operating Temperature: - 40° ~ +105° C  
 Max Processing Temp: 230° C for 60 seconds  
 Contact Material: Copper Alloy  
 Insulator Material: Polyester, UL 94V-0  
                           Standard: PA6T  
 Underplate: Nickel  
 Contact Area: 1u"~30u" Selective Gold  
 Solder Tails Area: 100u" Tin/Lead Free(Brighten Tin/Matte Tin)

F

F

RECOMMENDED P.C.B LAYOUT  
 TOLERANCES: ±0.05mm

Tolerance: ±0.2

Unit: MM

G

G

Scale	1:1						Name	Item No.
TOLERANCE								
X.X	±0.40							Title Box Header, Pitch 2.54MM, SMT Type, PCB Mount
X.XX	±0.25					Approved		
X.XXX	±0.15							Drawing No.
Angle	±3°							
								Replace
		Modification	Date	Name				



rev00

Sheet

H

H