


◀40X40X10mm Series▶



Spot cooling, also suitable for small space requirements, laptops PC and notebook, etc.,.

**External Dimensions**



Frame: Plastic (UL:94v-0)  
 Impeller: Plastic (UL:94v-0)  
 Bearing: Hydro bearing  
 Lead wire: UL1571AWG28  
 OPERATING TEMP\*: -10C~70C  
 VOLTAGE AVAILABLE: 5V, 12V  
 \*: -10C~60C for fans with sleeve/ball combination bearings.

**Specifications (Nominal)**

\*: Noise is measured at the distance of one (1) meter from the axis of intake.







Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (v)	Rated Current (A)	Rated Power (W)	Rated Speed (rpm)	Bearing type: =Ball =Sleeve =1B1S =Hydro bearing				Weight (g)	
							Maximum AirFlow (CMM)	Maximum AirFlow (CFM)	Maximum Pressure (InAq)	Maximum Pressure (mmAq)		Noise Level (dB/A)
40x40x10	AP0405MX-G70		5	0.14	0.700	8000	0.133	4.70	0.111	2.78	28.0	19.2
	AP0405HX-G73		5	0.13	0.650	9000	0.139	4.90	0.150	3.75	35.0	
	AP0412LX-G70		12	0.07	0.840	6500	0.099	3.50	0.063	1.58	19.0	
	AP0412MX-G70		12	0.08	0.960	8000	0.133	4.70	0.111	2.78	28.0	

Specifications subject to change without notice.

\*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓	✓		✓							

\*Safety approvals

					
				✓	

