

INTRODUCTION:

Adam Tech right angle PCB mount .318" footprint D-Sub connectors are a popular interface for many I/O applications. Offered in 9, 15, 25 and 37 positions they are a good choice for a low cost industry standard connection. These connectors are manufactured with precision stamped contacts offering a choice of contact plating and a wide selection of mating and mounting options.

FEATURES:

- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech D-Subminiatures and all industry standard D-Subminiature connectors.

SPECIFICATIONS:

Material:

Standard insulator: PBT, 30% glass reinforced, rated UL94V-0
 Optional Hi-Temp insulator: Nylon 6T
 Insulator color: Black
 Contacts: Phosphor Bronze
 Shell: Steel, Tin or Zinc plated
 Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
 Current rating: 5 Amps max.
 Contact resistance: 20 mΩ max. initial
 Insulation resistance: 5000 MΩ min.
 Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:


Insertion force: 0.75 lbs max
 Extraction force: 0.44 lbs min
 Temperature Rating:
 Operating temperature: -55°C to +105°C
 Soldering process temperature:
 Standard insulator: 235°C
 Hi-Temp insulator: 260°C

Packaging:

Anti-ESD plastic trays

Approvals and Certifications:

UL Recognized File no. E224053



ORDERING INFORMATION

DB25

SL

2

4

SHELL SIZE/ POSITIONS

DE09 = 9 Position
 DA15 = 15 Position
 DB25 = 25 Position
 DC37 = 37 Position

CONTACT TYPE

PL = Plug, .318" Footprint
 SL = Socket, .318" Footprint

MATING FACE MOUNTING OPTIONS

3 = #4-40 fixed jackscrews
 4 = #4-40 flush threaded inserts
 5 = #4-40 flush threaded inserts with removable jackscrews installed
 6 = .120" non-threaded mounting holes

* See Mounting Option diagrams pg. 66

PCB MOUNTING OPTIONS

1 = Wrap around ground straps with thru holes
 2 = Forked board locks
 3 = Top side only ground straps with thru holes
 4 = Top side only ground straps with #4-40 threaded screw holes

* See Mounting Option diagrams pg. 66

OPTIONS:

Add designator(s) to end of part number

15 = 15 μin gold plating in contact area

30 = 30 μin gold plating in contact area

EMI = Ferrite filtered version for EMI/RFI suppression

LPJ = Loose packed jackscrews



F = Superior retention 4 prong boardlocks

HT = Hi-Temp insulator for Hi-Temp soldering processes up to 260°C

R = Round jackscrews





PLUG




DB25-PL-25

SOCKET



DB25-SL-24




Recommended PCB Layout

Unit: Inch [mm]

Pos.	PLUG	SOCKET	DIMENSIONS	
	A	A	B	C
9	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]
15	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]
25	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]
37	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]


MATING FACE & PCB MOUNTING OPTIONS

OPTION 23




* Standard Stocked Item

OPTION 24



* Standard Stocked Item

OPTION 25




* Standard Stocked Item

OPTION 23-R


#4-40 Rivited Round Jackscrew (Shown)

OPTION 27


#4-40 Rivited Hex Jackscrew (Not Shown)




OPTION 24-F




OPTION 26




OPTION 33




OPTION 34




OPTION 35



OPTION 36



OPTION 43



INTRODUCTION:

Adam Tech right angle PCB mount .590" footprint D-Sub connectors are a popular interface for many I/O applications. Offered in 9, 15, 25 and 37 positions they are an excellent choice for a low cost industry standard connection. They are available with full or half size PCB side mounting flanges. Adam Tech connectors are manufactured with precision stamped contacts offering a choice of contact plating and a wide selection of mating and mounting options.

FEATURES:

Half or Full flange options
Industry standard compatibility
Durable metal shell design
Precision formed contacts
Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech D-Subminiatures and all industry standard D-Subminiature connectors.

SPECIFICATIONS:

Material:

Standard insulator: PBT, 30% glass reinforced, rated UL94V-0
Optional Hi-Temp insulator: Nylon 6T
Insulator Color: Black
Contacts: Phosphor Bronze
Shell: Steel, Tin or Zinc plated
Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
Current rating: 5 Amps max.
Contact resistance: 20 mΩ max. Initial
Insulation resistance: 5000 MΩ min.
Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
Extraction force: 0.44 lbs min

Temperature Rating:

Operating temperature: -55°C to +105°C
Soldering process temperature:
Standard insulator: 235°C
Hi-Temp insulator: 260°C

PACKAGING:

Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053



ORDERING INFORMATION

DB25

SQ

SA

4

SHELL SIZE/ POSITIONS

DE09 = 9 Position
DA15 = 15 Position
DB25 = 25 Position
DC37 = 37 Position

CONTACT TYPE

PQ = Plug,
.590" Footprint
SQ = Socket,
.590" Footprint

MATING FACE MOUNTING OPTIONS

3 = #4-40 fixed jack screws
4 = #4-40 flush threaded
inserts
5 = #4-40 flush threaded
inserts with removable
jack screws installed
6 = .120" non-threaded
mounting holes

* See Mounting Option
diagrams page 64

PCB MOUNTING OPTIONS

SA = Wrap around
ground straps
with thru holes
on half flange

SB = Wrap around
ground straps
with thru holes
on full flange

SC = Top side only
ground straps
with thru holes
on half flange

SD = Top side only
ground straps
with thru holes
on full flange

F = Forked boardlocks
on half flange

R = Forked boardlocks
on full flange

* See Mounting Option
diagrams page 64

OPTIONS:

Add designator(s) to end of part number

15 = 15 μin gold plating in
contact area

30 = 30 μin gold plating in
contact area

EMI = Ferrite filtered version
for EMI/RFI suppression



LPJ = Loose packed jackscrews
F = Superior retention 4 prong
boardlocks

HT = Hi-Temp insulator for
Hi-Temp soldering
processes up to 260°C

R = Round jackscrews



PLUG

See pg. 64 for Mounting Options



DB25-PQ-SB4

SOCKET




DB25-SQ-R5


Unit: Inch [mm]

Pos.	PLUG	SOCKET	DIMENSIONS	
	A	A	B	C
9	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]
15	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]
25	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]
37	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]

Half Flange PCB Layout for PCB mounting options (SA, SC, F)



















Full Flange PCB Layout for PCB mounting options (SB, SD, R)



PCB Edge

Mating Face & PCB Mounting Options

<p>OPTION SC3</p>  <p>#4-40 Fixed Jackscrew</p> <p>Top Side Ground Strap, Half Flange</p> <p>ø.126 Thru Hole</p>	<p>OPTION SC4</p>  <p>#4-40 Threaded Insert</p> <p>Top Side Ground Strap, Half Flange</p> <p>ø.126 Thru Hole</p>	<p>OPTION SC5</p>  <p>#4-40 Threaded Insert with Removable Jackscrew</p> <p>Top Side Ground Strap, Half Flange</p> <p>ø.126 Thru Hole</p>
<p>OPTION SC6</p>  <p>ø.120 Thru Hole</p> <p>Top Side Ground Strap, Half Flange</p>	<p>OPTION SD3</p>  <p>#4-40 Fixed Jackscrew</p> <p>Top Side Ground Strap, Half Flange</p> <p>ø.126 Thru Hole</p>	<p>OPTION SD4</p>  <p>#4-40 Threaded Insert</p> <p>Top Side Ground Strap, Half Flange</p> <p>ø.126 Thru Hole</p>
<p>OPTION SD5</p>  <p>#4-40 Threaded Insert with Removable Jackscrew</p> <p>Top Side Ground Strap, Half Flange</p> <p>ø.126 Thru Hole</p>	<p>OPTION SD6</p>  <p>ø.120 Thru Hole</p> <p>Top Side Ground Strap, Half Flange</p> <p>ø.126 Thru Hole</p>	<p>OPTION F3</p>  <p>Forked Board Lock</p> <p>#4-40 Fixed Jackscrew</p> <p>Half Flange</p>
<p>OPTION F4</p>  <p>Forked Board Lock</p> <p>#4-40 Threaded Insert</p> <p>Half Flange</p>	<p>OPTION F5</p>  <p>Forked Board Lock</p> <p>#4-40 Threaded Insert with Removable Jackscrew</p> <p>Half Flange</p>	<p>OPTION F6</p>  <p>Forked Board Lock</p> <p>ø.120 Thru Hole</p> <p>Half Flange</p>
<p>OPTION R3</p>  <p>Forked Board Lock</p> <p>#4-40 Fixed Jackscrew</p> <p>Full Flange</p>	<p>OPTION R4</p>  <p>Forked Board Lock</p> <p>#4-40 Threaded Insert</p> <p>Full Flange</p>	<p>OPTION R5</p>  <p>Forked Board Lock</p> <p>#4-40 Threaded Insert with Removable Jackscrew</p> <p>Full Flange</p>
<p>OPTION R6</p>  <p>Forked Board Lock</p> <p>ø.120 Thru Hole</p> <p>Full Flange</p>		

INTRODUCTION:

Adam Tech Combination Signal/Coax D-Sub connectors are a popular interface for many mixed signal I/O applications. Offered in five shell sizes they are a good choice for a low cost industry standard connection that requires utilization of standard signal and high performance, low impedance signals either in signal-coax or signal -power choices. Adam Tech connectors are manufactured with precision stamped standard signal contacts and precision turned coax contacts. These connectors are manufactured with precision stamped contacts offering a choice of contact plating and a wide selection of mating and mounting options.

Electrical:


Operating voltage: 250V AC / DC max.
Signal Current rating: 5 Amps max.
High Power contact current rating: 20 or 40 Amps.
Coaxial Impedance: 50Ω (75Ω optional)
Contact resistance: 20 mΩ max. initial
Insulation resistance: 5000 MΩ min.
Dielectric withstanding voltage: 1000V AC for 1 minute

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053



SHELL CONFIGURATIONS



ORDERING INFORMATION

D13W3

SLP

1

2

SHELL

CONFIGURATIONS

D1W1, D2W2, D3W3,
D5W1, D5W5, D7W2,
D8W8, D9W4N,
D11W1, D13W3,
D13W6, D17W2,
D17W5, D21W1,
D21W4, D24W7,
D25W3, D27W2,
D36W4, D43W2

STYLE

SIGNAL - COAX

1 = 50 Ohm

2 = 75 Ohm

SIGNAL - POWER

3 = 10 Amps

4 = 20 Amps

5 = 30 Amps

6 = 40 Amps

7 = 50 Amps

TYPE

SIGNAL-COAX

PT = Plug, Straight PCB

ST = Socket, Straight PCB

PL = Plug, Right Angle PCB

SL = Socket, Right Angle PCB

PD = Plug, Solder Cup

SD = Socket, Solder Cup

SIGNAL-POWER

PPT = Plug, Straight PCB,
Power Contacts

STP = Socket, Straight PCB,
Power Contacts

PLP = Plug, Right Angle PCB,
Power Contacts

SLP = Socket, Right Angle
PCB, Power Contacts

PDP = Plug, Solder Cup
Power Contacts

SDP = Socket, Solder Cup
Power Contacts

MOUNTING RIGHT ANGLE

1 = 120" non-threaded
mounting holes,
no bracket

2 = Short Bracket with
#4-40 flush threaded
inserts in mounting
holes

2A = Short Bracket with
#4-40 flush threaded
inserts in mounting
holes Jack Screws
installed

3 = Long Bracket with
#4-40 flush threaded
inserts in mounting
holes

3A = Long Bracket with
#4-40 flush threaded
inserts in mounting
holes Jack Screws
installed


MOUNTING STRAIGHT

JS = Riveted #4-40 Jack
Screws on top of flange


SL = Riveted #4-40 clinch
nuts on bottom of flange

BL = Riveted Board Locks


PLUG - RIGHT ANGLE PCB MOUNT SIGNAL-COAX




SOCKET - RIGHT ANGLE PCB MOUNT SIGNAL-COAX




PLUG - STRAIGHT PCB MOUNT SIGNAL-COAX




SOCKET - STRAIGHT PCB MOUNT SIGNAL-COAX




PLUG - STRAIGHT SOLDER CUP SIGNAL-COAX




SOCKET - STRAIGHT SOLDER CUP SIGNAL-COAX




PLUG - RIGHT ANGLE PCB MOUNT SIGNAL-POWER




SOCKET - RIGHT ANGLE PCB MOUNT SIGNAL-POWER




PLUG - STRAIGHT PCB MOUNT SIGNAL-POWER




SOCKET - STRAIGHT PCB MOUNT SIGNAL-POWER



PLUG - STRAIGHT SOLDER CUP SIGNAL-POWER



SOCKET - STRAIGHT SOLDER CUP SIGNAL-POWER



INTRODUCTION:

Adam Tech Right Angle Slimline PCB tail D-Sub connectors are a popular interface for many I/O applications. Offered in 9, 15 and 25 positions they are an excellent choice for a low cost industry standard connection and are ideal for low profile design requirements. Adam Tech connectors are manufactured with precision stamped contacts offering a choice of contact plating and a wide selection of mating and mounting options.

FEATURES:

- Short profile space saving design
- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech D-Subminiatures and all industry standard D-Subminiature connectors.

SPECIFICATIONS:

Material:

Standard insulator: PBT, 30% glass reinforced, rated UL94V-0
 Optional Hi-Temp insulator: Nylon 6T
 Insulator Color: Black
 Contacts: Phosphor Bronze
 Shell: Steel, Tin or Zinc plated
 Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
 Current rating: 5 Amps max.
 Contact resistance: 20 mΩ max. initial
 Insulation resistance: 5000 MΩ min.
 Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
 Extraction force: 0.44 lbs min

Temperature Rating:

Operating temperature: -55°C to +105°C
 Soldering process temperature:
 Standard insulator: 235°C
 Hi-Temp insulator: 260°C

PACKAGING:

Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053



ORDERING INFORMATION

DB25

SN

24

SHELL SIZE/ POSITIONS

DE09 = 9 Positions
DB25 = 25 Positions
HD15 = High Density
 15 Positions

MOUNTING OPTIONS

24 = Forked Boardlocks
 for PCB Retention and
 #4-40 threaded inserts
 in mounting holes
25 = Forked Boardlocks
 for PCB retention and
 #4-40 threaded inserts
 in mounting holes with
 installed jackscrews





CONTACT / TYPE

PN = Plug, .197" Slimline
SN = Socket, .197" Slimline

OPTIONS:





Add designator(s) to end of part number
15 = 15 μin gold plating in contact area
30 = 30 μin gold plating in contact area
LPJ = Loose packed jackscrews
HT = Hi-Temp insulator for Hi-Temp soldering
 processes up to 260°C
R = Round jackscrews installed

PLUG



Recommended PCB Layout

SOCKET



Recommended PCB Layout

Unit: Inch [mm]

Positions	PLUG	SOCKET	DIMENSIONS	
	A	A	B	C
9	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]
15	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]
25	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]

INTRODUCTION:

Adam Tech Right Angle SMT Slimline D-Sub connectors are a popular interface for many I/O applications. Offered in 9, 15 and 25 positions they are an excellent choice for a low cost industry standard connection and are ideal for low profile design requirements. Adam Tech connectors are manufactured with precision stamped contacts offering a choice of contact plating and a wide selection of mating and mounting options.

FEATURES:

- Short profile space saving design
- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech D-Subminiatures and all industry standard D-Subminiature connectors.

SPECIFICATIONS:

Material:

Insulator: Hi-Temperature thermoplastic, rated UL94V-0
 Insulator Color: Black
 Contacts: Phosphor Bronze or Brass
 Shell: Steel, Tin or Zinc plated
 Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
 Current rating: 1 Amp max.
 Contact resistance: 20 mΩ max. initial
 Insulation resistance: 5000 MΩ min.
 Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
 Extraction force: 0.44 lbs min

Temperature Rating:

Operating temperature: -55°C to +105°C
 Soldering process temperature: 260°C

PACKAGING:


Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053



ORDERING INFORMATION





OPTIONS:

Add designator(s) to end of part number
15 = 15 μin gold plating in contact area
30 = 30 μin gold plating in contact area
R = Round jackscrews



9P PLUG



Recommended PCB Layout





DE09-SS-24



DE09-PS-25

HD15 SOCKET





Recommended PCB Layout



HDL15-SS-25

25P PLUG



DB25-PS-24

INTRODUCTION

Adam Tech Right Angle .283" footprint D-Sub connectors with Screw Machine Contacts are a popular interface for many I/O applications. Offered in 9, 15, 25 and 37 positions they are a good choice for a high reliability industry standard connection. These connectors are manufactured with precision machine turned contacts and offer an exceptional high reliability connection. They are available in a choice of contact plating and a wide selection of mating and mounting options.

FEATURES:

- Exceptional Machine Contact connection
- Industry standard compatibility
- Durable metal shell design
- Precision turned screw machined contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech D-Subminiatures and all industry standard D-Subminiature connectors.

SPECIFICATIONS:

Material:

Standard insulator: PBT, 30% glass reinforced, rated UL94V-0
Optional Hi-Temp insulator: Nylon 6T rated UL94V-0
Insulator Colors: White (Black optional)
Contacts: Phosphor Bronze
Shell: Steel, Tin plated
Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
Current rating: 5 Amps max.
Contact resistance: 20 mΩ max. initial
Insulation resistance: 5000 MΩ min.
Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
Extraction force: 0.44 lbs min

Temperature Rating:

Operating temperature: -55°C to +105°C
Soldering process temperature:
Standard insulator: 235°C
Hi-Temp insulator: 260°C

PACKAGING:

Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053




DB25-PH-C-3-AM

DB25-SH-C-2-B

DB25-PH-C-1-C


ORDERING INFORMATION




OPTIONS:

Add designator(s) to end of part number
15 = 15 μin gold plating in contact area
30 = 30 μin gold plating in contact area
BK = Black insulator
HT = Hi-Temp insulator for Hi-Temp soldering processes up to 260°C


PLUG




PCB MOUNTING OPTIONS



Option 1: Without Bracket




Option 2: Bracket with Board Lock




Option 3: Bracket with .120" Mounting Hole


SOCKET




MATING FACE MOUNTING OPTIONS




Option C: .120" Mounting Hole




Option D: #4-40 Rear Clinch Nut



Option E: #4-40 Threaded Insert with removable Jack Screws



Recommended PCB Layout 9, 15, 25 & 37 Position



Recommended PCB Layout 50 Position

Unit: Inch / mm

Positions	PLUG	SOCKET	DIMENSIONS		
	A	A	B	C	D
9	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.436 [11.08]
15	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	.763 [19.39]
25	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.310 [33.24]
37	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	1.963 [49.86]
50	2.790 [52.80]	2.016 [52.34]	2.402 [61.00]	2.646 [67.20]	1.744 [44.32]

INTRODUCTION:

Adam Tech Flat Cable IDC D-Sub connectors are a popular interface for many I/O and cable assembly applications. Offered in 9, 15, 25, 37 and 50 positions they are an excellent choice for a low cost industry standard connection that terminates .050" flat cable quickly, easily and compactly. These connectors are manufactured with precision stamped contacts offering a choice of contact plating and a wide selection of mating and mounting options.

FEATURES:

- Quickly terminates to flat cable
- Industry standard compatibility
- Durable metal shell design
- Integral strain relief available
- Precision formed contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech D-Subminiatures and all industry standard D-Subminiature connectors.

SPECIFICATIONS:

Material:

Insulator: PBT, 30% glass reinforced, rated UL94V-0
Insulator Colors: Black (Blue optional)
Contacts: Phosphor Bronze
Shell: Steel, Tin or Zinc plated
Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
Current rating: 5 Amps max.
Contact resistance: 20 mΩ max. initial
Insulation resistance: 5000 MΩ min.
Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
Extraction force: 0.44 lbs min
Recommended cable size: 28 to 30 Awg.

Temperature Rating:

Operating temperature: -55°C to +105°C

PACKAGING:


Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053




ORDERING INFORMATION




OPTIONS:

Add designator(s) to end of part number
15 = 15 μin. gold in contact area
30 = 30 μin. gold in contact area
BU = Blue color insulator

PLUG



SOCKET



Unit: Inch [mm]

Positions	PLUG	SOCKET	DIMENSIONS		
	A	A	B	C	D
9	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.883 [22.44]
15	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	1.213 [30.81]
25	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.755 [44.57]
37	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	2.414 [61.32]

INTRODUCTION:

Adam Tech Solder Cup D-Sub connectors are a popular interface for many I/O applications. Offered in 9, 15, 25, 37 and 50 positions, they are an excellent choice for a low cost industry standard connection. These connectors are manufactured with precision stamped contacts, and offer a wide selection of mating and mounting options. Adam Tech Solder Cup connectors can be soldered to cable ends or mounted directly to a PCB card edge.

FEATURES:

- Cable or edge card mounting
- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Mating and mounting options

MATING CONNECTORS:

Adam Tech D-Subminiatures and all industry standard D-Subminiature connectors.

SPECIFICATIONS:

Material:

Insulator: PBT, 30% glass reinforced, rated UL94V-0
 Insulator Colors: Black (White optional)
 Contacts: Phosphor Bronze
 Shell: Steel, Tin or Zinc plated
 Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
 Current rating: 5 Amps max.
 Contact resistance: 20 mΩ max. initial
 Insulation resistance: 5000 MΩ min.
 Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
 Extraction force: 0.44 lbs min

Temperature Rating:

Operating temperature: -55°C to +105°C

PACKAGING:

Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053



ORDERING INFORMATION

DB25

PD

SL

SHELL SIZE/ POSITIONS

DE09 = 9 Position
DA15 = 15 Position
DB25 = 25 Position
DC37 = 37 Position
DD50 = 50 Position

MOUNTING OPTIONS

BLANK = .120" Mounting Holes
SL = Bottom Side Riveted, #4-40 clinch nuts
JS = Top Side Riveted, #4-40 Jack Screws

CONTACT TYPE

PD = Solder Cup, Plug
SD = Solder Cup, Socket

OPTIONS:


Add designator(s) to end of part number

15 = 15 μin gold plating in contact area


30 = 30 μin gold plating in contact area

WT = White Color Insulator


PLUG




SOCKET



MOUNTING OPTIONS



SL Option
Bottom side riveted #4-40
Clinch Nuts



JS Option
Top side riveted #4-40
Jack Screws

Unit: Inch [mm]

Positions	PLUG	SOCKET	DIMENSIONS		
	A	A	B	C	D
9	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.756 [19.20]
15	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	1.091 [27.70]
25	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.618 [41.10]
37	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	2.256 [57.30]
50	2.079 [52.81]	2.064 [52.43]	2.406 [61.11]	2.637 [67.00]	2.169 [55.10]

INTRODUCTION:

Adam Tech Crimp and Poke D-Sub connectors are a popular interface for many I/O applications. Offered in 9, 15, 25, 37 and 50 positions they are a low cost alternative to soldering a connector to cable. Contacts are crimped onto discrete wires and pushed into the connector body. The connector is comprised of a metal shell and plastic insulator and is available with a variety of mating options. The contacts are precision stamped and are available in a variety of platings.

FEATURES:

- Low cost no solder alternative
- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech D-Subminiatures and all industry standard D-Subminiature connectors.

SPECIFICATIONS:

Material:

Insulator: PBT, 30% glass reinforced, rated UL94V-0
 Insulator Color: Black
 Contacts: Phosphor Bronze
 Shell: Steel, Tin or Zinc plated
 Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
 Current rating: 5 Amps max.
 Contact resistance: 20 mΩ max. initial
 Insulation resistance: 5000 MΩ min.
 Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
 Extraction force: 0.44 lbs min

Temperature Rating:

Operating temperature: -55°C to +105°C

PACKAGING:

Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053



ORDERING INFORMATION HOUSING

DB25

SR

SL

SHELL SIZE/ POSITIONS

DE09 = 9 Position
DA15 = 15 Position
DB25 = 25 Position
DC37 = 37 Position
DD50 = 50 Position

BLANK = .120" diameter mounting holes

SL = Riveted #4-40 clinch nuts
JS = Riveted #4-40 jackscrews

CONTACT TYPE

PR = Plug, Crimp and Poke
SR = Socket, Crimp and Poke

CONTACTS

DCP

01

R

CONTACT WIRE RANGE

DCP = Plug Contact
DCS = Socket Contact

CONTACT TYPE

01 = 24-26 AWG
02 = 20-22 AWG
03 = 28-30 AWG


PACKAGING
R = 10,000 piece reel

OPTIONS:


Add designator(s) to end of part number

15 = 15 μin gold plating in contact area on crimp contacts
30 = 30 μin gold plating in contact area on crimp contacts

PLUG HOUSING




MOUNTING OPTIONS



SL Option

Bottom side riveted #4-40
Clinch Nuts




JS Option


Top side riveted #4-40
Jack Screws

See Dimension table pg. 77


SOCKET HOUSING



PLUG CRIMP CONTACTS



SOCKET CRIMP CONTACTS



INTRODUCTION:

Adam Tech Flush Mount Straight PCB tail D-Sub connectors are a popular interface for many limited space I/O applications. Offered in 9, 15 and 25 positions they are an excellent choice for a low cost industry standard connection and are ideal for low profile design requirements. Adam Tech connectors are manufactured with precision stamped contacts offering a choice of contact plating and a wide selection of mating and mounting options.

FEATURES:

- Low profile space saving design
- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech D-Subminiatures and all industry standard D-Subminiature connectors.

SPECIFICATIONS:

Material:

Standard insulator: PBT, 30% glass reinforced, rated UL94V-0
 Optional Hi-Temp insulator: Nylon 6T
 Insulator Color: Black
 Contacts: Phosphor Bronze
 Shell: Steel, Tin or Zinc plated
 Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
 Current rating: 5 Amps max.
 Contact resistance: 20 mΩ max. Initial
 Insulation resistance: 5000 MΩ min.
 Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
 Extraction force: 0.44 lbs min

Temperature Rating:

Operating temperature: -55°C to +105°C
 Soldering process temperature:
 Standard insulator: 235°C
 Hi-Temp insulator: 260°C

PACKAGING:

Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:


UL Recognized File no. E224053



D-SUBMINIATURE

FLUSH MOUNT STRAIGHT PCB TAIL

DPA & DSA SERIES



ORDERING INFORMATION

DB25

SA

M2

SHELL SIZE/ POSITIONS

DE09 = 9 Position
DA15 = 15 Position
DB25 = 25 Position
DC37 = 37 Position

CONTACT TYPE

PA = Plug, Flush mount,
Straight PCB Tail
SA = Socket, Flush Mount,
Straight PCB Tail

MOUNTING OPTIONS


M1 = Thru Hole Mounting
M2 = #4-40 Threaded
mounting holes
M1-R3 = Round Jackscrews
on top side
M2-R-BL = Round Jackscrews
on top side with
Boardlocks
underneath
M2-JS = #4-40 Threaded
Holes with removable
Jackscrews
M2-BL = Riveted #4-40
Internal Threaded
Standoffs with
Boardlocks
M2-BL-JS = Removable
Jackscrews with
Boardlocks

OPTIONS:


Add designator[s] to end of part number
15 = 15 μin gold plating in contact area
30 = 30 μin gold plating in contact area
PF = Press Fit Pins
HT = Hi-Temp insulator for hi-temp soldering
processes up to 260°C

MOUNTING OPTIONS

PLUG




SOCKET




M1 Option

Thru-Hole
Mounting




M2 OPTION

Threaded Hole
Mounting




M2-JS

Threaded Hole
Mounting with
removable
Jack Screws




M1-R3

Round
Jackscrews




M2-R-BL

Round Jackscrews
with Boardlock




M2-BL

#4-40 Threaded
Insert with Boardlock




M2-BL-JS

Removable Jackscrew
with Boardlock




Press Fit PCB Tail Option



Unit: Inch [mm]

Positions	PLUG	SOCKET	DIMENSIONS	
	A	A	B	C
9	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]
15	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]
25	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]



Recommended PCB Layout

INTRODUCTION:

Adam Tech Straight PCB tail D-Sub connectors are a popular interface for many I/O applications. Offered in 9, 15, 25, 37 and 50 positions they are an excellent choice for a low cost, sturdy, full metal body industry standard connection. These connectors are manufactured with precision stamped or machined turned contacts offering a choice of contact plating and a wide selection of mating and mounting options.

FEATURES:

- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech D-Subminiatures and all industry standard D-Subminiature connectors.

SPECIFICATIONS:

Material:

Standard insulator: PBT, 30% glass reinforced, rated UL94V-0
 Optional Hi-Temp insulator: Nylon 6T
 Insulator Colors: Black (White optional)
 Contacts: Phosphor Bronze
 Shell: Steel, Tin or Zinc plated
 Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
 Current rating: 5 Amps max.
 Contact resistance: 20 mΩ max. initial
 Insulation resistance: 5000 MΩ min.
 Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
 Extraction force: 0.44 lbs min

Temperature Rating:


Operating temperature: -55°C to +105°C
 Soldering process temperature:
 Standard insulator: 235°C
 Hi-Temp insulator: 260°C

PACKAGING:

Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053



ORDERING INFORMATION

DB25	ST	1	SL
SHELL SIZE/ POSITIONS DE09 = 9 Position DA15 = 15 Position DB25 = 25 Position DC37 = 37 Position DD50 = 50 Position	CONTACT TYPE PT = Plug, Straight PCB Tail, Standard Profile ST = Socket, Straight PCB Tail, Standard Profile PE = Plug, Straight PCB Tail, High Profile SE = Socket, Straight PCB Tail, High Profile	TAIL LENGTH 1 = Standard tail length for .062"-.125" PCB's (E = .189") 2 = Wire wrap tail (E = .512")	MOUNTING OPTIONS BLANK = .120" Mounting Holes SL = Bottom side riveted #4-40 Clinch Nuts JS = Top side riveted #4-40 Jackscrews BL = Riveted #4-40 Internal Threaded Standoffs with Boardlocks R = Riveted Round Jack Screws JSL = Bottom side riveted #4-40 Clinch Nuts with Jack Screws installed

OPTIONS:

Add designator(s) to end of part number


EMI = Ferrite filtered version for EMI / RFI suppression (Page 114)

HT = Hi-Temp insulator for hi-temp soldering processes up to 260°C





MOUNTING OPTIONS


PLUG




SOCKET




SL Option
Bottom side riveted #4-40
Clinch Nuts



JS Option
Top side riveted #4-40
Jack Screws




BL Option
#4-40 Threaded Boardlocks



Wire Wrap Tail Option
Tail length 2
wire wrap tail

Unit: Inch [mm]


Positions	PLUG	SOCKET	DIMENSIONS		
	A	A	B	C	D
9	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.756 [19.20]
15	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	1.091 [27.70]
25	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.618 [41.10]
37	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	2.256 [57.30]
50	2.079 [52.81]	2.064 [52.43]	2.406 [61.11]	2.637 [67.00]	2.169 [55.10]






Recommended PCB Layout

MOUNTING OPTIONS

PLUG




DB25-PE-1




SL Option

Bottom side riveted #4-40
Clinch Nuts



JS Option


Top side riveted #4-40
Jack Screws






BL OPTION

#4-40 Threaded Boardlocks

SOCKET



DB25-SE-1



Recommended PCB Layout

Unit: Inch [mm]

Positions	PLUG	SOCKET	DIMENSIONS		
	A	A	B	C	D
9	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.756 [19.20]
15	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	1.091 [27.70]
25	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.618 [41.10]
37	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	2.256 [57.30]
50	2.079 [52.81]	2.064 [52.43]	2.406 [61.11]	2.637 [67.00]	2.169 [55.10]

INTRODUCTION:

Adam Tech Dual Port D-Sub connectors are a popular space saving interface for many I/O applications. Offered in 9, 15, 25, 37 and 50 positions they are a good choice for a low cost industry standard connection and are ideal for PCB space saving applications. These connectors are manufactured with precision stamped contacts and are available in a number of connector combinations including same and mixed gender, mixed density and mixed interface. Options include a choice of contact plating and a variety of mating, mounting and grounding options.

FEATURES:

- Stacked space saving design
- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech D-Subminiatures and all industry standard D-Subminiature connectors.

SPECIFICATIONS:

Material:

Insulator: PBT, 30% glass reinforced, rated UL94V-0
 Insulator Color: Black
 Contacts: Phosphor Bronze
 Shell: Steel, Tin or Zinc plated
 Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
 Current rating: 5 Amps max.
 Contact resistance: 20 mΩ max. initial
 Insulation resistance: 5000 MΩ min.
 Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
 Extraction force: 0.44 lbs min

Temperature Rating:

Operating temperature: -55°C to +105°C

PACKAGING:


Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053






ORDERING INFORMATION



OPTIONS:


Add designator(s) to end of part number
 15 = 15 μin gold plating in contact area
 30 = 30 μin gold plating in contact area
 JS = #4-40 Jackscrews installed
 R = Rear boardlocks only

DUAL PORT, RIGHT ANGLE




Unit: Inch [mm]


Positions	PLUG	SOCKET	DIMENSIONS			
	A	A	B	C	D	E
9	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]	PORT HEIGHTS 1.119 [28.42] 1.244 [31.60] 1.394 [35.41]	PORT TO PORT CENTERLINE .900 [22.86] .750 [19.05] .625 [15.88]
15	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]		
25	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]		
37	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]		
50	2.079 [52.81]	2.064 [52.43]	2.406 [61.11]	2.637 [67.00]		




15P HD D-Sub over 15P HD D-Sub




15P HD D-Sub Elevated




15P HD D-Sub over Dual Mini DINs




15P D-Sub over 9P D-Sub




25P D-Sub over 9P D-Sub




15P D-Sub over Ganged Stereo Jacks




25P D-Sub over HD 15P D-Sub




25P D-Sub over 9P D-Sub & HD 15P D-Sub




25P D-Sub Elevated



25P D-Sub over 9P D-Sub & HD 15P D-Sub



44P HD D-Sub over 44P HD D-Sub



25P D-Sub over 50P SCSI II

INTRODUCTION:

Adam Tech Solder Cup High Density D-Sub connectors are a popular interface for many I/O applications. Offered in 15, 26, 44, 62 and 78 positions, they are a good choice for a low cost industry standard high density connection. Adam Tech connectors are manufactured with precision stamped contacts offering a choice of contact plating and a wide selection of mating and mounting options.

FEATURES:

- High Density pin count in standard size shell
- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Mating and mounting options

MATING CONNECTORS:

Adam Tech high density D-Subminiatures and all industry standard high density D-Subminiature connectors.

SPECIFICATIONS:

Material:

Insulator: PBT, 30% glass reinforced, rated UL94V-0

Insulator Colors: Black (White optional)

Contacts: Phosphor Bronze

Shell: Steel, Tin or Zinc plated

Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.

Current rating: 5 Amps max.

Contact resistance: 20 mΩ max. initial

Insulation resistance: 5000 MΩ min.

Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max

Extraction force: 0.44 lbs min

Temperature Rating:


Operating temperature: -55°C to +105°C

PACKAGING:


Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053



ORDERING INFORMATION



OPTIONS:

Add designator(s) to end of part number

15 = 15 μin gold plating in contact area

30 = 30 μin gold plating in contact area


WT = White color insulator

SL = Bottom side Riveted #4-40 Clinch Nuts


JS = Top side riveted #4-40 Jack Screws




PLUG



SOCKET




MOUNTING OPTIONS



SL Option

Bottom side riveted #4-40
Clinch Nuts



JS Option

Top side riveted #4-40
Jack Screws

Unit: Inch [mm]

Positions	PLUG	SOCKET	DIMENSIONS		
	A	A	B	C	D
15	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.759 [19.28]
26	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	1.083 [27.51]
44	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.626 [41.30]
62	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	2.271 [57.70]
78	2.079 [52.81]	2.064 [52.43]	2.406 [61.11]	2.635 [66.93]	2.099 [55.32]

INTRODUCTION:

Adam Tech Straight PCB tail High Density D-Sub connectors are a popular interface for many I/O applications. Offered in 15, 26, 44, 62 and 78 positions they are a good choice for a low cost industry standard high density connection. Adam Tech connectors are manufactured with precision stamped contacts offering a choice of contact plating and a wide selection of mating and mounting options.

FEATURES:

- High Density pin count in standard size shell
- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech high density D-Subminiatures and all industry standard high density D-Subminiature connectors.

SPECIFICATIONS:

Material:

Standard insulator: PBT, 30% glass reinforced, rated UL94V-0
 Optional Hi-Temp insulator: Nylon 6T rated UL94V-0
 Insulator Colors: Black (White optional)
 Contacts: Phosphor Bronze
 Shell: Steel, Tin or Zinc plated
 Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
 Current rating: 5 Amps max.
 Contact resistance: 20 mΩ max. initial
 Insulation resistance: 5000 MΩ min.
 Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
 Extraction force: 0.44 lbs min

Temperature Rating:

Operating temperature: -55°C to +105°C
 Soldering process temperature:
 Standard insulator: 235°C
 Hi-Temp insulator: 260°C

PACKAGING:


Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053



ORDERING INFORMATION



OPTIONS:

Add designator(s) to end of part number

WT = White color insulator

HT = Hi-Temp insulator for Hi-Temp soldering processes up to 260°C


SL = Riveted #4-40 Clinch Nuts

JS = Riveted #4-40 Jackscrews


BL = Riveted #4-40 Internal Threaded Standoffs with Boardlocks

EMI = Ferrite filtered version for EMI / RFI suppression (Page 98)


PLUG



SOCKET




MOUNTING OPTIONS




SL Option

Bottom side riveted #4-40 Clinch Nuts




JS Option

Top side riveted #4-40 Jack Screws



BL Option

Bottom side riveted #4-40 Clinch Nuts with PCB Boardlocks



Recommended PCB Layout

Unit: Inch [mm]

Positions	PLUG	SOCKET	DIMENSIONS		
	A	A	B	C	D
15	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.759 [19.28]
26	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	1.083 [27.51]
44	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.626 [41.30]
62	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	2.271 [57.70]
78	2.079 [52.81]	2.064 [52.43]	2.406 [61.11]	2.635 [66.93]	2.099 [55.32]

INTRODUCTION:

Adam Tech right angle PCB mount High Density D-Sub connectors are a popular interface for many I/O applications. Offered in 15, 26, 44, 62 and 78 positions they are a good choice for a low cost industry standard high density connection. Adam Tech connectors are manufactured with precision stamped contacts offering a choice of contact plating and a wide selection of mating and mounting options.

FEATURES:

- High Density in standard size shell
- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech high density D-Subminiatures and all industry standard high density D-Subminiature connectors.

SPECIFICATIONS:

Material:

Standard insulator: PBT, 30% glass reinforced, rated UL94V-0

Optional Hi-Temp insulator: Nylon 6T rated UL94V-0

Insulator Colors: HDL Series: Black

HDVG Series: Blue

Contacts: Phosphor Bronze

Shell: Steel, Tin or Zinc plated

Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.

Current rating: 5 Amps max.

Contact resistance: 20 mΩ max initial

Insulation resistance: 5000 MΩ min.

Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max

Extraction force: 0.44 lbs min

Temperature Rating:

Operating temperature: -55°C to +105°C

Soldering process temperature:

Standard insulator: 235°C

Hi-Temp insulator: 260°C

PACKAGING:

Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:

UL Recognized File no. E224053



ORDERING INFORMATION

HDL

15

SL

B

SERIES INDICATOR

HDL = High Density D-Sub

HDVG = High Density VESA connector with recessed #9 pin and blue insulator

POSITIONS

15, 26, 44, 62, 78

CONTACT TYPE

PL = Plug, Right Angle Mount

SL = Socket, Right Angle Mount

MOUNT OPTIONS

A = #4-40 Jackscrews and forked boardlocks

B = #4-40 Flush threaded inserts and forked boardlocks

C = #4-40 Flush threaded inserts with removable jackscrews and forked boardlocks

D = Topside ground straps with screw holes

OPTIONS:

Add designator(s) to end of part number

15 = 15 μin gold plating in contact area

30 = 30 μin gold plating in contact area




EMI = Ferrite filtered version for EMI / RFI suppression (Page 98)

F = Retention 4 prong boardlocks


HT = Hi-Temp insulator for Hi-Temp soldering processes up to 260°C

R = Round Riveted Jackscrews

PLUG






HDL15-PL-B




15 Position PCB Layout

SOCKET




HDL15-SL-B



26, 44, 62 Position PCB Layout

Hi Density Video Graphics Connector



HDVG-15-SL-B

Unit: Inch [mm]

Positions	PLUG	SOCKET	DIMENSIONS			
	A	A	B	C	D	E
15	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.277 [7.04]	.090 [2.29]
26	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	.277 [7.04]	.090 [2.29]
44	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	.277 [7.04]	.090 [2.29]
62	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	.276 [7.00]	.095 [2.41]
78	2.079 [52.81]	2.064 [52.43]	2.406 [61.11]	2.635 [66.93]	.300 [7.63]	.095 [2.41]

INTRODUCTION:

Adam Tech Crimp and Poke High Density D-Sub connectors are a popular interface for many I/O applications. Offered in 15, 26, 44, 62 and 78 positions they are a low cost alternative to soldering a high density connector to cable. Contacts are crimped onto discrete wires and pushed into the connector body. The connector is comprised of a metal shell and plastic insulator and is available with a variety of mating options. The contacts are precision stamped and are available in a variety of platings.

FEATURES:

- High Density in standard size shell
- Low cost no solder alternative
- Industry standard compatibility
- Durable metal shell design
- Precision formed contacts
- Variety of Mating and mounting options

MATING CONNECTORS:

Adam Tech high density D-Subminiatures and all industry standard high density D-Subminiature connectors.

SPECIFICATIONS:

Material:

Insulator: PBT, 30% glass reinforced, rated UL94V-0
 Insulator Colors: Black (White optional)
 Contacts: Phosphor Bronze
 Shell: Steel, Tin or Zinc plated
 Hardware: Brass, Nickel plated

Contact Plating:

Gold over Nickel underplate on contact area.

Electrical:

Operating voltage: 250V AC / DC max.
 Current rating: 5 Amps max.
 Contact resistance: 20 mΩ max. initial
 Insulation resistance: 5000 MΩ min.
 Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Insertion force: 0.75 lbs max
 Extraction force: 0.44 lbs min
 Recommended wire size: 22 to 28 Awg
 Temperature Rating:
 Operating temperature: -55°C to +105°C

PACKAGING:


Anti-ESD plastic trays

APPROVALS AND CERTIFICATIONS:


UL Recognized File no. E224053



ORDERING INFORMATION HOUSING




CRIMP CONTACT




OPTIONS:

Add designator(s) to end of part number
15 = 15 μin gold plating in contact area
30 = 30 μin gold plating in contact area
WT = White color insulator.
SL = Riveted #4-40 Clinch Nuts
JS = Riveted #4-40 Jackscrews


PLUG




Plug Contact



SOCKET




Socket Contact




Unit: Inch [mm]


Positions	PLUG	SOCKET	DIMENSIONS		
	A	A	B	C	D
15	.666 [16.92]	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.759 [19.28]
26	.994 [25.25]	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	1.083 [27.51]
44	1.534 [38.96]	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.626 [41.30]
62	2.182 [55.43]	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	2.271 [57.70]
78	2.079 [52.81]	2.064 [52.43]	2.406 [61.11]	2.635 [66.93]	2.099 [55.32]




DE09-HD-PN-(SS OR TS)




DA15-HD-PN-(SS OR TS)



DB25-HD-PN-(SS OR TS)



DC37-HD-PN-(SS OR TS)




DD50-HD-PN-(SS OR TS)


ORDERING INFORMATION

choose one from each category as shown in sample below


DE09-HD	PY	TS
Hood Size	Hood Color	Hardware
DE09-HD - 9P Hood	PY - Gray Plastic	SS - Short Screw
DA15-HD - 15P Hood	PB - Black Plastic	TS - Thumb Screw
DB25-HD - 25P Hood	PN - Bright Chrome Plated Plastic	
DC37-HD - 37P Hood	AL - Aluminum Cast	
DD50-HD - 50P Hood		



Jackscrews




JACKSCREW DIMENSIONS		
PART NUMBER	A	B
JS-01	.416 [10.60]	.226 [5.70]
JS-02	.467 [11.86]	.270 [6.86]
JS-03	.500 [12.70]	.313 [7.95]
JS-04	.465 [11.81]	.226 [5.70]




HDW-031

Set includes 2 #4-40 female jackscrews




HDW-023

Set includes 2 #4-40 female jackscrews 2 flat washers, 2 split washers and 2 hex nuts




HDW-029

Screw lock kit includes 2 screw locks and 2 retainer screws




HDW-043A

Slide lock post set includes 2 posts, 2 washers and 2 lock-washers




HDW-043-XX

Slide lock assembly kit includes slide lock, screws and washers, Specify 9, 15, 25 or 37 position



HDW-024

Set includes 2 #4-40 female jackscrews and 2 hex nuts




HDW-028

Screw retainer clip set includes 2 screw retainer clips and 2 retainer screws




HDW-044

Sliding lock posts
Set of 2



HDW-045

Slide lock post kit includes 2 posts, washers and hex nuts



HDW-041


Spring latch set includes 1 pair of spring latches with holding hardware and 1 pair of notch clips with holding hardware

INTRODUCTION:

Adam Tech EMI filtered D-Sub option includes the addition of a high performance Ferrite Filter which surrounds each contact and provides a low cost EMI answer for high frequency interference. Our ferrite filtered D-Subs are direct drop-in replacements with our standard unfiltered D-Subs with the same footprint.

FEATURES:

Direct replacement for standard non-filtered parts
Low cost alternative to passive component types
Significant reduction of noise at high frequencies




See pgs. 59, 62, 82, 90, 92, for ordering information

AdamTech offers a complete range of ferrite filtered D-Subs to satisfy EMI/RFI emissions in most applications. This series offers filtered connectors in a multitude of terminations, mating and mounting options.

- Drop in replacement for standard D-Subs
- Low applied cost
- Significant reduction of noise at high frequencies

Typical Performance



* Consult factory for specific part number impedance performance.

FREQ (MHZ)

	1	5	10	25	30	40	50	100	200
XC-									
XL-	5.4	15	18	23	25	26	28	34	51
R-	0.656	11	18	29	32	37	40	50	64

	300	400	500	600	700	800	900	1000
XC-					1.27	0.807	0.856	0.977
XL-	73	101	122	57				
R-	84	121	199	342	344	170	77	40

25 Position

FREQ (MHZ)

	1	5	10	25	30	40	50	100	200
XC-									
XL-	4	14	18	22	24	26	27	35	55
R-	0.309	8.4	15	26	29	33	36	46	59

	300	400	500	600	700	800	900	1000
XC-					0.983	0.762	0.851	0.986
XL-	81	115	147	65				
R-	79	119	210	394	356	150	65	34

FREQ (MHZ)

	1	5	10	25	30	40	50	100	200
XC-									
XL-	3.6	15.9	19	24	25	27	28	36	54
R-	0.116	8.4	16	28	31	35	39	49	62

	300	400	500	600	700	800	900	1000
XC-					0.998	0.78	0.864	0.996
XL-	80	112	138	48				
R-	83	124	215	389	339	147	64	33

37 Position

FREQ (MHZ)

	1	5	10	25	30	40	50	100	200
XC-									
XL-	4.9	16	20	25	27	28	30	36	53
R-	0.45	8.4	15	26	29	33	36	46	59

	300	400	500	600	700	800	900	1000
XC-					1.082	0.814	0.879	1
XL-	76	105	122	29				
R-	80	122	224	424	332	131	56	29