




Rev	AWO #	Description	Date	Appr
-		RELEASED	6/13/07	

APPROVED: _____
 DATE: _____ TITLE: _____



2 thru 24 Poles Available
 A = # of Poles X .150" [3.81mm]
 B = # of Poles - 1 X .150" [3.81mm]

SPECIFICATIONS:

- Material:** Insulator: Thermoplastic, rated UL 94V-0
- Insulator color: Green
- Wire Guard: Phosphor Bronze, Tin plated
- Terminal Body: Brass, Zinc plated
- Screw: Steel, Zinc plated
- Electrical:** Operation voltage: 300V max
- Current rating: 8 Amps max per Pole
- Insulation resistance: 5000 Mohms min @ 1000V
- Dielectric withstanding voltage: 1600 VAC for 1 minute
- Mechanical:** Recommended Screw Torque: 1.7 Lb-in
- Wire Range: Solid Wire: 16 - 28 Awg
- Stranded Wire: 16 - 28 Awg
- Recommended Wire Strip = .236"-.275" [6-7mm]
- Environmental:** Operating temperature: -30°C to +105°C
- Lead free, RoHS compliant.
- Recommended soldering temp: 235°C for 5 seconds



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLE
.X ± .10	± .10
.XX ± .020	± .015
.XXX ± .015	± .010
APPROVALS	DATE
DRAWN	SS
CHECKED	
APPROVED	

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: EURO BLOCK, 3.81mm PLUGGABLE
 2 THRU 24 POLES

SIZE: X PART NO.: EBR-XX-B
 REF: SCALE: NTS SHEET 1 OF 1

